

FEATURES

- -40~+85°C operating temperature range
- Low operating and threshold current
- Output Power: 1.6mW (Min.)
- Long life and high reliability


APPLICATIONS

- Digital Signal Transmission
- Telecommunication
 - Local loop
 - Interoffice and intraoffice
- Data communication
- LAN

DESCRIPTION

FLD3C5KM/LK-B is a Fabry-perot laser diode module in a small coaxial type package for single mode fiber including a PIN monitor photodiode, designed for use in data links and local area networks in the 1.3 μ m wavelength region. The laser diode is specially designed to ensure low current and stable operation over a wide temperature range. This assures long life and high reliability. The module can operate from -40 to +85°C. The monitor photodiode which receives emission power from the rear facet of the laser diode, can be used to control the optical power coupled into the fiber. This module employs a highly stable optical coupling system that couples the laser output into a single mode fiber pigtail.

KM



LK



ABSOLUTE MAXIMUM RATINGS

Parameter	Symbol	Ratings	Unit
Optical Output Power	P_{fmax}	3.0	mW
Forward Current (LD)	I_{Fmax}	150	mA
Reverse Voltage (LD)	V_{rmax}	2	V
Photodiode Reverse Voltage	V_{DRmax}	20	V
Soldering Temperature	T_{solder}	260 (t<10 sec., d>2.5mm)	°C
Storage Temperature	T_{stg}	-40 to +90	°C
Operating Case Temperature	T_{op}	-40 to +85	°C
Storage Humidity (Note 1)	X_{stg}	85	%
Operating Humidity (Note 1)	X_{op}	85	%

Note 1: Storage or operating within 500 hours maximum.

OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_c=25^\circ\text{C}$)

Parameter	Symbol	Conditions	Limits			Unit
			Min.	Typ.	Max.	
Fiber Output Power	P_f	CW	1.6	-	-	mW
Threshold Current	I_{th}	CW	5	8	15	mA
Operating Current	I_{op}	CW, $P_f=1.6\text{mW}$	20	-	40	mA
Forward Voltage	V_F	CW, $P_f=1.6\text{mW}$	-	1.2	1.5	V
Series Resistance	R_s	CW, $P_f=1.6\text{mW}$	-	5	8	Ω
Threshold Output Power	P_{th}	CW, $I_f=I_{th}$	-	20	40	μW
Slope Efficiency	S	CW, $P_f=1.6\text{mW}$	60	-	120	$\mu\text{W}/\text{mA}$
Linearity of dL/dI	S_{var}	CW, 0.16 to 2.0mW	-	-	± 15	%
Saturation of dL/dI	S_{sat}	CW, 0.16 to 2.0mW	-30	-	-	%
Center Wavelength	λ_c	CW, $P_f=1.6\text{mW}$	1,290	-	1,330	nm
Spectral Width (RMS)	σ	CW, $P_f=1.6\text{mW}$	-	2.0	3.0	nm
Monitor Current	I_m	CW, $P_f=1.6\text{mW}$, $V_{DR}=5\text{V}$	0.2	-	0.8	mA
Monitor Dark Current	I_D	$V_{DR}=5\text{V}$	-	1.0	50	nA
Linearity of P_f-I_m	-	CW, 0.16 to 2.0mW, $V_{DR}=5\text{V}$	-	-	± 10	%

OPTICAL AND ELECTRICAL CHARACTERISTICS (T_c= -40 to +85°C unless otherwise specified)

Parameter	Symbol	Conditions	Limits			Unit
			Min.	Typ.	Max.	
Fiber Output Power	P _f	CW	1.6	-	-	mW
Threshold Current	I _{th}	CW	2	-	35	mA
Threshold Current Ratio	I _{th} (T _c)/I _{th} (25)		0.25	-	4.5	-
Forward Voltage	V _F	CW, P _f =1.6mW	-	1.2	1.5	V
Series Resistance	R _s	CW, P _f =1.6mW	2	-	10	Ω
Threshold Output Power	P _{th}	CW, I _f =I _{th}	-	-	80	μW
Slope Efficiency	S	CW, P _f =1.6mW	30	-	200	μW/mA
Slope Efficiency Ratio	S(T _c)/S(25)		0.5	-	1.6	-
Linearity of dL/dI	S _{var}	CW, 0.16 to 2.0mW	-	-	±20	%
Saturation of dL/dI	S _{sat}	CW, 0.16 to 2.0mW	-30	-	-	%
Center Wavelength	λ _c	CW, P _f =1.6mW	1,260	-	1,360	nm
Spectral Width (RMS)	σ	CW, P _f =1.6mW	-	-	3.0	nm
Laser Rise Time	T _r	I _b =I _{th} , P _{pk} =1.6mW, 10 to 90%	-	0.2	0.4	ns
Laser Fall Time	T _f	I _b =I _{th} , P _{pk} =1.6mW, 10 to 90%	-	0.3	0.5	ns
Monitor Current	I _m	CW, P _f =1.6mW, V _{DR} =5V	0.15	-	1.0	mA
Monitor Dark Current	I _D	V _{DR} =5V	-	-	500	nA
Monitor Capacitance	C _t	V _{DR} =5V, f=1MHz	-	6	10	pF
Linearity of P _f -I _m	-	CW, 0.16 to 2.0mW, V _{DR} =5V	-	-	±10	%
Tracking Error	TE	T _c = -40 to 85°C, P _f =1.6mW at T _c =25°C, APC with monitor PD	-	-	±1.0	dB

Fig. 1 Optical Output Power and Monitor Current vs. Forward Current




Fig. 2 Forward Current vs. Forward Voltage




Fig. 3 Temperature Dependence of Threshold Current




Fig. 4 Lasing Spectrum




Fig. 5 Temperature Dependence of Center Wavelength




Fig. 6 Tracking Characteristics




Fig. 7 Pulse Response







Fig. 8 Frequency Response





"KM" PACKAGE

UNIT: mm



"LK" PACKAGE

UNIT: mm



For further information please contact:

Eudyna Devices USA Inc.

2355 Zanker Rd.
San Jose, CA 95131-1138, U.S.A.
TEL: (408) 232-9500
FAX: (408) 428-9111
www.us.eudyna.com

Eudyna Devices Europe Ltd.

Network House
Norreys Drive
Maidenhead, Berkshire SL6 4FJ
United Kingdom
TEL: +44 (0) 1628 504800
FAX: +44 (0) 1628 504888

Eudyna Devices Asia Pte Ltd.

Hong Kong Branch
Rm. 1101, Ocean Centre, 5 Canton Rd.
Tsim Sha Tsui, Kowloon, Hong Kong
TEL: +852-2377-0227
FAX: +852-2377-3921

Eudyna Devices Inc.

Sales Division
1, Kanai-cho, Sakae-ku
Yokohama, 244-0845, Japan
TEL: +81-45-853-8156
FAX: +81-45-853-8170

CAUTION

Eudyna Devices Inc. products contain **gallium arsenide (GaAs)** which can be hazardous to the human body and the environment. For safety, observe the following procedures:

- Do not put this product into the mouth.
- Do not alter the form of this product into a gas, powder, or liquid through burning, crushing, or chemical processing as these by-products are dangerous to the human body if inhaled, ingested, or swallowed.
- Observe government laws and company regulations when discarding this product. This product must be discarded in accordance with methods specified by applicable hazardous waste procedures.

Eudyna Devices Inc. reserves the right to change products and specifications without notice. The information does not convey any license under rights of Eudyna Devices Inc. or others.

© 2004 Eudyna Devices USA Inc.
Printed in U.S.A.