



NOTES:

- 1. TORQUE REQUIRED: 120 OZ-IN MIN. (VARIABLE) MEASURED IN A CLOCKWISE DIRECTION AT RATED SPEED AND VOLTAGE.
- 2. LEADS: #22 AWG, STRANDED AND TOPCOATED, BLACK, 9±1/2" LONG WITH 3/16±1/32" STRIP.
- 3. OUTPUT SHAFT ENDPLAY: .002 TO .022.
- 4. THIS PRODUCT AND ITS COMPONENTS MUST BE ROHS COMPLIANT PER EU DIRECTIVES 2002/95/EC AND 2003/11/EC.



CUSTOMER SIGN-OFF:

NAME: _____

DATE: _____

LABEL INFO:
150-1535A 1 RPM CW
115V 60Hz 4W (YYMMDD)
708-150-1535A

(DATE CODE-YYMMDD)

AUTOTROL CORPORATION

| | | | | | |
|-----------|----------|-------------|-----|--------------|-------|
| DRAWN BY: | AEV | SCALE: | 1/1 | APPROVED BY: | |
| DATE: | 08/23/07 | CHECKED BY: | | E.R.N. # | 11026 |

TITLE: MOTOR

| | | | | | |
|-----------|--------------------|------------|-------------------------------------|-----------|-----------|
| CUSTOMER: | MOUSER ELECTRONICS | TOLERANCE: | DECIMALS ± .002 FRACTIONS ± .008 | PART NO.: | 150-1535A |
| | 708-150-1535A | | | | |

| REVISIONS | | | | | |
|-----------|--|--|--|--|--|
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Autotrol:](#)

[150-1535A](#)