





REVISIONS					
REV	DATE	DESCRIPTION	BY	CHK	APP
R	11JUL2016	REV PER ECO-16-009924	DS	SY	



RECOMMENDED P.C. BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
R. K. SEIFRIED
CHK
F. KIBLER
APP'D

04/09/90
8-17-92
-

DIMENSIONS:
mm [INCHES]

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES

± -
± -
± -
± 0.13 [.005]
± -
± -

MATERIAL

1
2

3

TOLERANCES UNLESS OTHERWISE SPECIFIED:

PRODUCT SPEC
APPLICATION SPEC

0
A1

TE Connectivity

NAME
HDI, 2 ROW, PIN ASSEMBLY,
4.83 [.190] LONG SOLDER PINS

SIZE
A1

CAGE CODE
00779

DRAWING NO
532430

RESTRICTED TO

CUSTOMER DRAWING

SCALE
4:1

SHEET
1

OF
2

REV
R

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

1

HOUSING MATERIAL: THERMOPLASTIC, COLOR-NATURAL.

2

CONTACT MATERIAL: PHOSPHOR BRONZE.

3

FINISH:
MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108-9063; BASED ON TELCORDIA DR-1217-CORE APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
TIN-LEAD PLATED POSTS.

4

SOLDER PIN POST RECOMMENDED P.C. BOARD HOLE SIZES ARE 0.94-1.09 [.037-.043]; RECOMMENDED PAD DIA IS 1.52 [.060].

5

DIMENSIONS IN BRACKETS ARE IN INCHES.

6

PART NUMBER IS OBSOLETE.

7

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

8

FINISH:
CONTACT FINISH: .00127-.00254 [.000050-.000100] NICKEL UNDERPLATE ALL OVER; .000762 [.000030] GOLD PLATE IN CONTACT AREA, TIN-LEAD PLATED POSTS.

8	124.46 [4.900]	49	128.27 [5.050]	138.43 [5.450]	146.05 [5.750]	100	3-532430-9
8	73.66 [2.900]	29	77.47 [3.050]	87.63 [3.450]	95.25 [3.750]	60	3-532430-5
6	251.46 [9.900]	99	255.27 [10.050]	265.43 [10.450]	273.05 [10.750]	200	1-532430-9
6	238.76 [9.400]	94	242.57 [9.550]	252.73 [9.950]	260.35 [10.250]	190	1-532430-8
6	226.06 [8.900]	89	229.87 [9.050]	240.03 [9.450]	247.65 [9.750]	180	1-532430-7
6	213.36 [8.400]	84	217.17 [8.550]	227.33 [8.950]	234.95 [9.250]	170	1-532430-6
6	200.66 [7.900]	79	204.47 [8.050]	214.63 [8.450]	222.25 [8.750]	160	1-532430-5
	187.96 [7.400]	74	191.77 [7.550]	201.93 [7.950]	209.55 [8.250]	150	1-532430-4
6	175.26 [6.900]	69	179.07 [7.050]	189.23 [7.450]	196.85 [7.750]	140	1-532430-3
6	162.56 [6.400]	64	166.37 [6.550]	176.53 [6.950]	184.15 [7.250]	130	1-532430-2
6	149.86 [5.900]	59	153.67 [6.050]	163.83 [6.450]	171.45 [6.750]	120	1-532430-1
	137.16 [5.400]	54	140.97 [5.550]	151.13 [5.950]	158.75 [6.250]	110	1-532430-0
	124.46 [4.900]	49	128.27 [5.050]	138.43 [5.450]	146.05 [5.750]	100	532430-9
6	111.76 [4.400]	44	115.57 [4.550]	125.73 [4.950]	133.35 [5.250]	90	532430-8
6	99.06 [3.900]	39	102.87 [4.050]	113.03 [4.450]	120.65 [4.750]	80	532430-7
6	86.36 [3.400]	34	90.17 [3.550]	100.33 [3.950]	107.95 [4.250]	70	532430-6
	73.66 [2.900]	29	77.47 [3.050]	87.63 [3.450]	95.25 [3.750]	60	532430-5
6	60.96 [2.400]	24	64.77 [2.550]	74.93 [2.950]	82.55 [3.250]	50	532430-4
	48.26 [1.900]	19	52.07 [2.050]	62.23 [2.450]	69.85 [2.750]	40	532430-3
	35.56 [1.400]	14	39.37 [1.550]	49.53 [1.950]	57.15 [2.250]	30	532430-2
6	22.86 [.900]	9	26.67 [1.050]	36.83 [1.450]	44.45 [1.750]	20	532430-1
E	D	C	B	A	POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC

± -
± -
± -
± 0.13 [.005]
± -

ANGLES
FINISH

PRODUCT SPEC
APPLICATION SPEC

SIZE
WEIGHT

04/09/90
8-17-92

R. K. SEIFRIED
F. KIBLER

TE Connectivity

HDI, 2 ROW, PIN ASSEMBLY,
4.83 [.190] LONG SOLDER PINS

00779532430

CUSTOMER DRAWING

SCALE 4:1

SHEET 2 OF 2

REV R

4805 (1/15)