

SlimFix
SF 5/21 MC SDR V2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Similar to illustration

SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	SF 5/21 MC SDR V2
Order No.	1919110000
Version	SlimFix, Conductor and cable markers, 4.8 - 7.4 mm, 21 x 7.4 mm, To customer specification
GTIN (EAN)	4032248555437
Qty.	32 pc(s).
compatible printer	1324380000 2438520000 2438510000

SlimFix
SF 5/21 MC SDR V2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data
Dimensions and weights

Width	7.4 mm	Width (inches)	0.291 inch
Height	21 mm	Height (inches)	0.827 inch
Depth	8 mm	Depth (inches)	0.315 inch
Net weight	1.03 g		

General data

Advice label	Colour based on customer requirements (Please send M-Print PRO file)	Colour	To customer specification
Colour of printing	black	Halogen	No
Material	Polyamide 66	Operating temperature range	-40...100 °C
Orientation of print	horizontal	Printed characters	Based on customer requirements (Please send M-Print PRO file)
Printing method	MC Laser	Size of labelling field	21 x 7.4 mm
Type of printing	To customer specification	UL 94 flammability rating	V-2
Width	7.4 mm		

Conductor and cable markers

Conductor O.D.	4.8 - 7.4 mm	Conductor O.D., max.	7.4 mm
Conductor O.D., min.	4.8 mm	Conductor cross-section, max.	10 mm ²
Conductor cross-section, min.	6 mm ²	Halogen	No

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
eClass 9.0	27-40-04-01	eClass 9.1	27-40-04-01
eClass 10.0	27-40-04-01	UNSPSC	44-12-17-08

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
------------------	------------------------------