

UE series

Chip Type, Vibration Resistance



For SMD



Long Life

Anti-Solvent
Feature

- Chip type with load life of 2000 to 5000 hours at 125°C.
- Suited for automobile electronics where heavy duty services are indispensable.
- Compliant to the RoHS directive (2002/95/EC).




Specifications


Item	Performance Characteristics						
Category Temperature Range	-55 to +125°C (φ12.5 to 20) -40 to +125°C (φ8, φ10)						
Rated Voltage Range	10 to 50V						
Rated Capacitance Range	33 to 4700μF						
Capacitance Tolerance	±20% at 120Hz, 20°C						
Leakage Current	After 1 minute's application of rated voltage, leakage current is not more than 0.03CV or 4 (μA), whichever is greater.						
Tangent of loss angle (tan δ)	For capacitance of more than 1000μF, add 0.02 for every increase of 1000μF.						
	Rated voltage (V)		10	16	25	35	50
	tan δ (MAX)		φ8 · φ10	0.26	0.20	0.16	0.14
Stability at Low Temperature	Rated voltage (V)		10	16	25	35	50
	Impedance ratio Z-40°C / Z+20°C (MAX)		φ8 · φ10	10	8	6	4
			φ12.5 to φ20	8	6	4	3
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 5000 hours (2000 hours for φD=8 and 10) at 125°C.						
Shelf Life	After storing the capacitors under no load at 125°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.						
Marking	Black print on the case top.						

Chip Type

(φ8 to φ10)



Type numbering system (Example : 50V 330μF)



φD	8	10	12.5	16	18	20
A	2.9	3.2	4.8	5.4	6.4	6.2
B	8.3	10.3	13.6	17.1	19.1	21.1
C	8.3	10.3	13.6	17.1	19.1	21.1
E	3.1	4.5	4.0	6.3	6.3	8.8
H	1.1 to 1.5	1.1 to 1.5	1.0 to 1.4	1.0 to 1.4	1.0 to 1.4	1.3 to 1.7

Dimensions

Cap.(μF)	Code	10 1A	16 1C	25 1E	35 1V	50 1H
33	330					8×10 90
47	470					10×10 130
100	101		8×10 140	8×10 140	10×10 150	12.5×13.5 500
220	221	8×10 140	10×10 190	10×10 190	12.5×13.5 550	16×16.5 850
330	331	10×10 190	12.5×13.5 750	12.5×13.5 750	16×16.5 1000	16×16.5 850
470	471	12.5×13.5 750	12.5×13.5 750	16×16.5 1000	16×16.5 1000	18×16.5 950
680	681	12.5×16 900	16×16.5 1000	18×16.5 1200	18×16.5 1200	
1000	102	12.5×16 900	18×16.5 1200	18×21.5 1200	20×21.5 1400	
2200	222	18×16.5 1200	18×16.5 1200			
3300	332	18×16.5 1200				
4700	472	18×21.5 1550				

* In this case, [6] will be put at 12th digit of type numbering system, "▲"

Rated ripple current (mA rms) at 125°C 100kHz

Frequency coefficient of rated ripple current

φD	Cap.(μF)	50 Hz	120 Hz	300 Hz	1 kHz	10 kHz or more
φ8 · φ10	33 to 330	0.47	0.67	0.78	0.91	1.00
φ10 to 680	100 to 680	0.53	0.67	0.82	0.89	1.00
φ12.5 to φ20	1000 to 4700	0.74	0.87	0.96	0.98	1.00

- Taping specifications are given in page 23.
- Recommended land size, soldering by reflow are given in page 18, 19.
- Please refer to page 3 for the minimum order quantity.