



BAV19WS
THRU
BAV21WS

Features

- Silicon Epitaxial Planar Diodes
- For General Purpose
- This diode is also available in other case.
- Lead Free Finish/RoHS Compliant ("P" Suffix designates RoHS Compliant. See ordering information)

Mechanical Data

- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1
- Marking code: BAV19WS=A8
BAV20WS=T2
BAV21WS=T3

Maximum Ratings


Symbol	Parameters	Rating	Unit
V_R	Continuous Reverse Voltage	BAV19WS	100
		BAV20WS	150
		BAV21WS	200
V_{RRM}	Repetitive Peak Reverse Voltage	BAV19WS	120
		BAV20WS	200
		BAV21WS	250
I_{FSM}	Non-Repetitive Peak Forward Surge Current @ $t=1\mu s$ @ $t=1s$	2.5 0.5	A
I_{FM}	Forward Continuous Current (Note1)	400	mA
I_0	Average Rectified Output Current (Note1)	200	mA
I_{FRM}	Repetitive Peak Forward Current at $f>50Hz$, $T_{amb}=25^\circ C$ ⁽¹⁾	625	mA
P_{tot}	Power Dissipation at $T_{amb}=25^\circ C$ ⁽¹⁾	250	mW
R_{thJA}	Thermal Resistance Junction to Ambient Air	500	KW
T_J	Operating Junction Temperature	-65 to +150	$^\circ C$
T_{STG}	Storage Temperature	-65 to +150	$^\circ C$

Electrical Characteristics @ 25°C Unless Otherwise Specified


Symbol	Parameter	Min	Typ	Max	Units
V_F	Forward Voltage ($I_F=100mA$) ($I_F=200mA$)	---	---	1.00 1.25	V
I_R	Leakage Current ($V_R=100V$)	BAV19WS	---	100	nA
	($V_R=100V$, $T_J=100^\circ C$)	BAV19WS	---	15	uA
	($V_R=150V$)	BAV20WS	---	100	nA
	($V_R=150V$, $T_J=100^\circ C$)	BAV20WS	---	15	uA
	($V_R=200V$)	BAV21WS	---	100	nA
	($V_R=200V$, $T_J=100^\circ C$)	BAV21WS	---	15	uA
C_{tot}	Capacitance ($V_R=0$, $f=1.0MHz$)	---	1.5	---	pF
t_{rr}	Reverse Recovery Time ($I=30mA$, $I_R=30mA$) ($I_{rr}=3.0mA$, $R_L=100OHMS$)	---	---	50	ns

Notes: 1. Valid provided that leads are kept at ambient temperature


250mW
Small Signal
Diodes
120 to 250 Volts



DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	.090	.107	2.30	2.70	
B	.063	.071	1.60	1.80	
C	.045	.053	1.15	1.35	
D	.031	.045	0.80	1.15	
E	.010	.016	0.25	0.40	
G	.004	.018	0.10	0.45	
H	.004	.010	0.10	0.25	
J	-----	.006	-----	0.15	




Forward characteristics




Admissible forward current versus ambient temperature

Valid provided that electrodes are kept at ambient temperature




Admissible power dissipation versus ambient temperature


Valid provided that electrodes are kept at ambient temperature




Leakage current versus junction temperature



Dynamic forward resistance
versus forward current



Capacitance
versus reverse voltage



TM

Micro Commercial Components

Ordering Information :

Device	Packing
Part Number-TP	Tape&Reel: 3Kpcs/Reel

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Micro Commercial Components \(MCC\):](#)

[BAV19WS-T](#) [BAV20WS-T](#) [BAV19WS-TP](#) [BAV20WS-TP](#)