








LOC	DIST	REV	DESCRIPTION	DATE	DRW	APVD
A1	-					
C25			REVISED PER ECR-15-010828	28 JUL 2015	NK	FL
C26			ECR-15-011321	30 JUL 2015	KD	RR
C27			ECR-15-013489	14 SEP 2015	KD	RR



SECTION A-A / Schnitt A-A


SECTION B-B / Schnitt B-B

- REMARKS/Bemerkungen**
- 1 CAVITY SUITABLE FOR STANDARD TIMER CONTACTS LISTED IN PROD.SPEC. 108-18049, ITEM 3.3.2
Kammer geeignet für Standard Timer Kontakte gelistet in Prod. Spec. 108-18049, Punkt 3.3.2
 - 2 CONTACT CAVITY NO.
Kontaktkammernummerierung
 - 3 MATING STOP
Tiefenanschlag
 - 4 AREA FOR TE LOGO ACC: TO SPEC 202-36
Bereich für TE Logo nach Spec. 202-36
 - 5 POLARIZATION RIB POSITION "a" AND/OR "b"
Polarisierungsrippe Position "a" und/oder "b"
 - 6 KEYING RIB POSITION "c" AND/OR "d"
Kodierrippe Position "c" und/oder "d"
 - 6a KEYING RIB POSITION "c" AND/OR "d" AT THE END WALLS OF THE HOUSING
Kodierrippe Position "c" und/oder "d" an den Gehäusestirnseiten
 - 7 LOCKING LATCH
Rasthaken
 - 8 TE PART NO (PN)
TE Bestell Nr. (PN)
 - 9 DESIGN OF THE HOUSINGS ACC: TO RAST 5 STANDARD
Gehäuseausführung gemäss RAST 5 Vorgabe
 - 10 GENERAL SUITABLE TAB HEADER SEE RAST 5 PERFORMANCE
Generell passende Flachsteckerwannen siehe RAST 5 Vorgabe
 - 11 PACKAGING: BULK PACKAGING IN CORRUGATED BOX PN 740580-2
2 POS, 2500 PIECES PER BOX / 3 POS, 2000 PIECES PER BOX
Verpackung: Schüttgut in Versandkarton Pn 740580-2
2pol, 2500 Stück per Karton / 3pol, 2000 Stück per Karton
 - 12 DIMENSION A AND DIMENSION B SEE SHEET 2 OF 3
Mass A und Mass B, siehe Blatt 2 of 3
 - 13 MATERIAL CORRESPONDS TO THE REQUIREMENT EN 60335
(INCL. GLOW WIRE TEST 750° WITHOUT FLAME)
Material entspricht den Anforderungen der EN 60335
(inkl. Glühdrahttest 750° ohne Flamme)
 - 14 RATIO NUMBER OF THE KEYING VERSION, INKJET PRINTED. SEE SHEET 2
Kodierungskennnummer, mit Tintenstrahldrucker aufgebracht, siehe Blatt 2
 - 15 PRELIMINARY- NOT RELEASED FOR PRODUCTION




THIS DRAWING IS A CONTROLLED DOCUMENT.		DRW: Kishor M 18-10-07	
DIMENSIONS: mm		CHK: K. Murtz 18-10-07	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: Tm Klenner 18-10-07	NAME: STANDARD TIMER HSG. RAST 5 MARK II Standard Timer Gehäuse RAST 5 Mark II
0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES FINISH *		PRODUCT SPEC: 108-18049 APPLICATION SPEC:	
MATERIAL: SEE TABLE SHEET 2 OF 3		WEIGHT: -	RESTRICTED TO: -
Customer Drawing		SIZE: A1 CAGE CODE: 00779 DRAWING NO: 1241961	SCALE: 5:1 SHEET 1 OF 3 REV: C27

ONLY 5-1241961-7, 1-1241961-9, 7-1241961-7




ALL OTHER DIMENSIONS SEE SHEET 1 OF 3

KEY LAYOUT DESCRIPTION



PAY ATTENTION I
DIFFERENT CAVITY GEOMETRY AND LOCKING LATCHE OVERHANG
Bitte beachten I
Unterschiedliche Kammergeometrie und Rasthakenuberstand.

FOR 2 POS. AND 3 POS.



ALL OTHER DIMENSIONS SEE SHEET 1 OF 3
Alle anderen Masse siehe Seite 1 von 3

SPECIAL MATERIAL						
PRELIMINARY	1955507-4	4	20	15	PA66	NATURAL
PRELIMINARY	9-1955506-2	2	10	5	UL 94 V0	NATURAL

PART NO	POS.	DIM A	DIMM B	MATERIAL	COLOUR /Farbe	REV./Rev.
6-1241961-7	3	15	10	PA 6 UL94V-2	NATURAL	1
4-1241961-7	3	15	10	PA 6 UL94V-2	NATURAL	A
3-1241961-7	3	15	10	PA 6 UL94V-2	NATURAL	A
1-1955422-7	3	15	10	PA 66 UNFILLED UL94 V0	NATURAL	A
5-1955422-7	3	15	10	PA 66 UNFILLED UL94 V0	NATURAL	A
4-1955422-3	2	10	5	PA 66 UNFILLED UL94 V0	NATURAL	A
2-1241817-3	3	15	10	PA 66 UL94 V-2	Green	E
0-1955422-6	3	15	10	PA 66 UNFILLED UL94 V0	NATURAL	A
8-1241961-8	3	15	10			C
0-1241961-8	3	15	10	PA 6 UL94V-2	natural	A
8-1241961-3	2	10	5			C
3-1241961-1	2	10	5	PA 6 UL94V-2	NATURAL	C
0-1955422-1	2	10	5	PA 66 UNFILLED UL94 V0	NATURAL	A

SPECIAL VERSION: UL94 V0 & GWT 750 NF & CTI 350						
5-1241961-7	3	15	10	PA66	NATURAL	A
1-1241961-9	3	15	10		NATURAL	A
7-1241961-7	3	15	10		NATURAL	1

SPECIAL VERSION: UL94 V2 & GWT 750 NF						
6-2178575-7	3	15	10	PA6 GF15	NATURAL	A

SPECIAL VERSION: UL94 V0 & GWT 750 NF							
PRELIMINARY	3-2178412-7	3	15	10	PA66 UL94 V0 & GWT 750 NF	NATURAL	1
PRELIMINARY	4-2178412-7	3	15	10		NATURAL	1
PRELIMINARY	8-2178412-2	2	10	5		NATURAL	1

LOC		DIST		REVISIONS			
AI	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
SEE SHEET-01							

0-1241959-5	5	25	20	PA 6 UL94V-2	Natural/natur	B
4-1241959-4	4	20	15			A
2-1241959-4	4	20	15			B
0-1241959-4	4	20	15			
2-1241817-5	5	25	20	PA 6.6 UL94V-2	Natural/natur Black/schwarz Violet/violett Grey/grau Natural/natur	C
0-1241817-5		25	20			
3-1241817-4		20	15			
2-1241817-4		20	15			
0-1241817-4	4	20	15			
2-1241817-4		20	15			
2-1241983-2	2	10	5	PA 6 UL94V-2	Green/grün Violet/violett TARGET RAL 4001 Yellow/gelb Black/schwarz Blue/blau Red/rot	C
1-1241983-2		10	5			
0-1241983-2		10	5			
8-1241983-2		10	5			
5-1241983-3		10	5			
6-1241983-2		10	5			
9-1241961-8	3	15	10	PA 6 UL94V-2	Natural/natur	C
6-1241961-8		15	10			
5-1241961-8		15	10			
4-1241961-8		15	10			
7-1241961-8		15	10			
1-1241961-8		15	10			
3-1241961-8		15	10			
2-1241961-8		15	10			
2-1241961-7		15	10			
1-1241961-7		15	10			
9-1241961-9	15	10				
0-1241961-6	15	10				
3-1241961-3	10	5				
2-1241961-2	10	5				
5-1241961-2	10	5				
4-1241961-3	10	5				
7-1241961-2	10	5				
7-1241961-3	10	5				
6-1241961-3	10	5				
3-1241961-2	10	5				
5-1241961-3	10	5				
6-1241961-2	10	5				
0-1241961-3	10	5				
8-1241961-2	10	5				
9-1241961-2	10	5				
0-1241961-1	10	5				
9-969484-9	3	15	10	PA 6.6 UL94V-2	Yellow/gelb	
2-969484-8	15	10				
0-969484-8	15	10				
8-969484-7	15	10				
7-969484-7	15	10				
6-969484-7	15	10				
5-969484-7	15	10				
4-969484-7	15	10				
3-969484-7	15	10				
2-969484-7	15	10				
1-969484-7	15	10				
0-969484-7	15	10				
9-969484-6	15	10				
8-969484-6	15	10				
7-969484-6	15	10				
6-969484-6	15	10				
5-969484-6	15	10				
4-969484-6	15	10				
3-969484-6	15	10				
2-969484-6	15	10				
1-969484-6	15	10				
0-969484-6	15	10				
7-969484-3	10	5		PA 6.6 UL94V-2	Natural/natur	H
6-969484-3	10	5				
5-969484-3	10	5				
4-969484-3	10	5				
3-969484-3	10	5				
2-969484-3	10	5				
1-969484-3	10	5				
0-969484-3	10	5				
9-969484-2	10	5				
8-969484-2	10	5				
7-969484-2	10	5				
6-969484-2	10	5				
5-969484-2	10	5				
4-969484-2	10	5				
3-969484-2	10	5				
2-969484-2	10	5				
1-969484-2	10	5				
0-969484-2	10	5				
9-969484-1	10	5				
8-969484-1	10	5				
7-969484-1	10	5				
6-969484-1	10	5				
5-969484-1	10	5				
4-969484-1	10	5				
3-969484-1	10	5				
2-969484-1	10	5				
1-969484-1	10	5				
0-969484-1	10	5				

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±0.2
1 PLC	±0.2
2 PLC	±0.2
3 PLC	±0.2
4 PLC	±0.2
ANGLES	±0.1
FINISH	±0.1

MATERIAL: SEE TABLE SHEET 2 OF 3

WEIGHT: -

Customer Drawing

SCALE: 5:1

SHEET 2 OF 3

REV. C 27

TE Connectivity

STANDARD TIMER HSG. RAST 5 MARK II
Standard Timer Gehäuse RAST 5 Mark II

SIZE: A1

CAGE CODE: 00779

DRAWING NO: 1241961

RESTRICTED TO: -

