

D2684. DECEMBER 1982—REVISED SEPTEMBER 1987


- description**

The SN54HC73 is characterized for operation over the full military temperature range of -55°C to 125°C . The SN74HC73 is characterized for operation from -40°C to 85°C .

INPUTS				OUTPUTS	
CLR	CLK	J	K	Q	$\bar{Q}$
L	X	X	X	H	L
H	I	L	L	Q ₀	$\bar{Q}_0$
H	I	H	L	H	L
H	I	L	H	L	H
H	I	H	H	TOGGLE	
H	H	X	X	Q ₀	$\bar{Q}_0$

1CLK	1	14	1J
1 $\overline{\text{CLR}}$	2	13	1 $\overline{\text{Q}}$
1K	3	12	1Q
V _{CC}	4	11	GND
2CLK	5	10	2K
2 $\overline{\text{CLR}}$	6	9	2Q
2J	7	8	2 $\overline{\text{Q}}$

logic symbol†



Pin numbers shown are for D, J, and N packages.

TEXAS
INSTRUMENTS

POST OFFICE BOX 655012 • DALLAS, TEXAS 75265

Copyright © 1982, Texas Instruments Incorporated

2-97

2

HCMS Devices

SN54HC73, SN74HC73 **DUAL J-K FLIP-FLOPS WITH CLEAR**

absolute maximum ratings over operating free-air temperature range†

Supply voltage, V_{CC}	−0.5 V to 7 V
Input clamp current, I_{IK} ($V_I < 0$ or $V_I > V_{CC}$)	±20 mA
Output clamp current, I_{OK} ($V_O < 0$ or $V_O > V_{CC}$)	±20 mA
Continuous output current, I_O ($V_O = 0$ to V_{CC})	±25 mA
Continuous current through V_{CC} or GND pins	±50 mA
Lead temperature 1,6 mm (1/16 in) from case for 60 s: J package	300 °C
Lead temperature 1,6 mm (1/16 in) from case for 10 s: D or N package	260 °C
Storage temperature range	−65 °C to 150 °C

† Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

recommended operating conditions

		SN54HC73			SN74HC73			UNIT
		MIN	NOM	MAX	MIN	NOM	MAX	
V_{CC} Supply voltage		2	5	6	2	5	6	V
V_{IH} High-level input voltage	$V_{CC} = 2$ V	1.5			1.5			V
	$V_{CC} = 4.5$ V	3.15			3.15			
	$V_{CC} = 6$ V	4.2			4.2			
V_{IL} Low-level input voltage	$V_{CC} = 2$ V	0	0.3		0	0.3		V
	$V_{CC} = 4.5$ V	0	0.9		0	0.9		
	$V_{CC} = 6$ V	0	1.2		0	1.2		
V_I Input voltage		0	V_{CC}		0	V_{CC}		V
V_O Output voltage		0	V_{CC}		0	V_{CC}		V
t_t Input transition (rise and fall) times	$V_{CC} = 2$ V	0	1000		0	1000		ns
	$V_{CC} = 4.5$ V	0	500		0	500		
	$V_{CC} = 6$ V	0	400		0	400		
T_A Operating free-air temperature		−55	125		−40	85		°C

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS	V_{CC}	$T_A = 25$ °C			SN54HC73		SN74HC73		UNIT
			MIN	TYP	MAX	MIN	MAX	MIN	MAX	
V_{OH}	$V_I = V_{IH}$ or V_{IL} , $I_{OH} = -20$ μ A	2 V	1.9	1.998		1.9		1.9		V
		4.5 V	4.4	4.499		4.4		4.4		
		6 V	5.9	5.999		5.9		5.9		
	$V_I = V_{IH}$ or V_{IL} , $I_{OH} = -4$ mA	4.5 V	3.98	4.30		3.7		3.84		
V_{OL}	$V_I = V_{IH}$ or V_{IL} , $I_{OL} = 20$ μ A	6 V	5.48	5.80		5.2		5.34		V
		2 V		0.002	0.1		0.1		0.1	
		4.5 V		0.001	0.1		0.1		0.1	
		6 V		0.001	0.1		0.1		0.1	
	$V_I = V_{IH}$ or V_{IL} , $I_{OL} = 4$ mA	4.5 V		0.17	0.26		0.4		0.33	
I_I	$V_I = V_{CC}$ or 0	6 V		±0.1	±100		±1000		±1000	nA
		6 V			4		80		40	μ A
C_i	$V_I = V_{CC}$ or 0, $I_O = 0$	2 to 6 V		3	10		10		10	pF

SN54HC73, SN74HC73 **DUAL J-K FLIP-FLOPS WITH CLEAR**

2
HCMOS Devices

timing requirements over recommended operating free-air temperature range (unless otherwise noted)

		V _{CC}	T _A = 25°C			SN54HC73		SN74HC73		UNIT
			MIN	TYP	MAX	MIN	MAX	MIN	MAX	
f _{clock}	Clock frequency	2 V	0		6	0	4.2	0	5	MHz
		4.5 V	0		31	0	21	0	25	
		6 V	0		36	0	25	0	29	
t _w	Pulse duration	2 V	80			120		100		ns
		4.5 V	16			24		20		
		6 V	14			20		17		
	CLR low	2 V	80			120		100		ns
		4.5 V	16			24		20		
		6 V	14			20		17		
t _{su}	Setup time, CLR inactive or data before CLK↓	2 V	100			150		125		ns
		4.5 V	25			35		30		
		6 V	20			30		25		
t _h	Hold time, data after CLK↓	2 V	0			0		0		ns
		4.5 V	0			0		0		
		6 V	0			0		0		

switching characteristics over recommended operating free-air temperature range (unless otherwise noted), C_L = 50 pF (see Note 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	V _{CC}	T _A = 25°C			SN54HC73		SN74HC73		UNIT
				MIN	TYP	MAX	MIN	MAX	MIN	MAX	
f _{max}			2 V	6	11		4.2		5		MHz
			4.5 V	31	54		21		25		
			6 V	36	64		25		29		
t _{PHL}	CLR	Q	2 V		78	155		250		194	ns
			4.5 V		16	31		47		39	
			6 V		13	26		40		32	
t _{PLH}	CLR	Q̄	2 V		78	155		250		194	ns
			4.5 V		16	31		47		39	
			6 V		13	26		40		32	
t _{pd}	CLK	Q or Q̄	2 V		63	126		185		160	ns
			4.5 V		13	25		37		32	
			6 V		11	21		32		27	
t _t		Any	2 V		38	75		110		95	ns
			4.5 V		8	15		22		19	
			6 V		6	13		19		16	

C _{pd}	Power dissipation capacitance per flip-flop	No load, T _A = 25°C	30 pF typ
-----------------	---	--------------------------------	-----------

NOTE 1: Load circuit and voltage waveforms are shown in Section 1.