




THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
GP		00		P	LTR	DESCRIPTION	DATE
				K		REVISED PER ECC-08-007327	27JAN2009
				ZMR		WLM	



1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
2. ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED.
3. MATERIAL:
HOUSING - THERMOPLASTIC (BLACK)
TERMINALS - HIGH STRENGTH COPPER ALLOY PLATED WITH EITHER .000030 MIN GOLD OR GOLD FLASH OVER PALLADIUM NICKEL .000030 MIN TOTAL, ON CONTACT MATING SURFACE. .000050 MIN NICKEL UNDERPLATE OVER ENTIRE TERMINAL.
4. WIRE SIZE: 22 AWG SOLID OR 22 AWG 7 STRANDS OF COPPER CONDUCTORS. MAX INSULATION DIAMETER OF .045 IS ACCEPTABLE FOR MOST APPLICATIONS.
5. CORING MAY OR MAY NOT APPEAR AND IS AT THE DISCRETION OF TYCO ELECTRONICS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DRN STEPHEN DOSS 1-2-80	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		CHK V.E. SLACK 1-3-80	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPROV B.G. WARD 1-3-80	PRODUCT SPEC	
0 PLC ± .005		APPLICATION SPEC	SIZE CASE CODE DRAWING NO	
1 PLC ± .005		WEIGHT	A2 00779 C=552305	
2 PLC ± .005		CUSTOMER DRAWING	RESTRICTED TO	
3 PLC ± .005			SCALE NTS SHEET 1 OF 1 REV K	
4 PLC ± .005				
ANGLES ± .005				
FINISH				