


4

3

2


1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HQ	00		C	Updated pin length/tolerances	10JUL2007	DJL	MAH
			D	Modified silkscreen and notes	13MAR2009	VG	MAH
			DI	Modified notes	26MAR2009	VG	MAH
			E	Updated dims / logo, and notes	20AUG2009	APV	MAH



NOTES: UNLESS OTHERWISE SPECIFIED.

- FABRICATED TO MEET IPC - 6012, CLASS 2.
INSPECT TO MEET IPC - A - 600, CLASS 2.
- MATERIAL: GETEK 4 PLY (7628) 0.71 THK.
P/N ML200D, 1/2 OZ. COPPER BOTH SIDES
DIELECTRIC CONSTANT @ 1MHz 4.2 ± 0.1 .
- FINISH:
A: SOLDERMASK OVER BARE COPPER (SMOBC).
B: MASK BOTH SIDES OF PCB WITH LPI SOLDERMASK.
SOLDERMASK COLOR: NATURAL GREEN.
C: TOP AND BOTTOM OF TABS E.N.I.G PLATING
- TWO PLACE TOLERANCES: ± 0.23
- PACKAGING: SINGULATED PARTS TO BE VACUUM PACKED
IN BULK.
- PARTS ARE COMPLIANT TO ROHS STANDARDS PER TYCO
ELECTRONICS STANDARD TEC-138-702.
- CONSULT TYCO ELECTRONICS DATA SHEET DSI513353
- CONTACT TYCO ELECTRONICS ENGINEERING
PRIOR TO DESIGNING INTO AN APPLICATION
- PRIMARY AND SECONDARY SIDES SHOWN.



DETAIL A
SCALE 10:1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN DJL	14DEC2006	Tyco Electronics Rochester, New York 14623		
DIMENSIONS: mm		CHK -	-	NAME 2.4 GHz PCB Antenna		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	-			
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		PRODUCT SPEC -	-	SIZE A3		
MATERIAL -		APPLICATION SPEC -	-	CAGE CODE 00779		
FINISH -		WEIGHT -	-	DRAWING NO C-1513353		
CUSTOMER DRAWING				RESTRICTED TO -		
				SCALE 5:1	SHEET 1	OF 1
				REV E		