

# Material Safety Data Sheet

<b>Revision Date</b> June 25, 2008	<b>Prepared by</b> Patti Rogers	<b>Technical Information</b> 1-800-201-8822 or <a href="mailto:support@mgchemicals.com">support@mgchemicals.com</a>
<b>Head Office</b> 9347 - 193 Street, Surrey, B.C., V4N 4E7		<b>Emergency</b> Phone Canutech (613) 996-6666 Collect 24 hrs

For updates please download from [www.mgchemicals.com](http://www.mgchemicals.com) or fax requests to 1-800-708-9888

## Section 1: Product Identification

**MSDS Code: 824 - liquid**

**Name: Isopropyl Alcohol**

**Related Part Numbers: 824-100ML; 824-500ML; 824-1L; 824-4L; 824-20L; 824-1G; 824-Wx25, 824-Wx50, 824-Wx500**

Use: Multipurpose solvent.

## Section 2: Hazardous Ingredients

CAS#	Chemical Name	Percentage by weight	ACGIH TWA	Osha Pel	Osha Stel
67-63-0	2-propanol	>99%	400ppm	400ppm	500ppm

## Section 3: Hazards Identification

**WHMIS Codes:** B2, D2B

**NFPA Ratings:** Health 1 Flammability 3 Reactivity 0

**HMIS Ratings:** Health 1 Flammability 3 Physical Hazard 0

**Eyes:** May cause eye irritation, characterized by a burning sensation, redness, tearing, inflammation, and possible corneal injury.

**Skin:** May cause skin irritation with pain and stinging, especially if skin is abraded.

**Inhalation:** May cause respiratory tract irritation. Inhaling high concentrations may cause central nervous system effects characterized by headache, and dizziness.

**Ingestion:** Harmful if swallowed. May cause gastrointestinal irritation with nausea, vomiting, and diarrhea. May cause central nervous system depression.

**Chronic:** Skin contact over a long period of time may cause dermatitis.

## Section 4: First Aid Measure

**Eyes:** Remove contact lenses. Flush eyes with plenty of water. Get medical aid if irritation persists.

**Skin:** Wash skin with plenty of soap and water. Get medical aid if symptoms persist. Remove contaminated clothing.

**Inhalation:** Immediately remove from exposure to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get medical aid.

**Ingestion:** Do not induce vomiting. Give milk or water. Get medical aid immediately.

## Section 5: Fire Fighting Measures

**Autoignition Temperature:** 425°C

**Flash Point:** 12°C

**LEL / UEL:** 2 / 12

**Extinguishing Media:** Use water spray, dry chemical, carbon dioxide, or chemical foam.

**General Information:** Will burn if involved in a fire. Vapors can travel to a source of ignition and flash back. This product is an explosion hazard.

## Section 6: Accidental Release Measures

**Spill Procedure:** Remove all sources of ignition. Provide adequate ventilation. Wear appropriate personal protection. Sprinkle absorbent compound onto spill, then sweep into a plastic or metal container. Wipe up further residue with paper towel and place in container. Wash spill area with soap and water.

## Section 7: Handling and Storage

**Handling:** Extinguish pilot lights, cigarettes and turn off other sources of ignition prior to use. Avoid breathing vapors and prolonged or repeated contact with skin. Vapors may accumulate and travel to distant ignition sources and flashback. Provide adequate ventilation.

**Storage:** Keep away from sources of ignition. Store in a cool, dry, well-ventilated area, away from incompatible substances.

## Section 8: Exposure Controls

**Routes of entry:** Eyes, ingestion, inhalation, and skin.

**Ventilation:** Use adequate general or local exhaust ventilation to keep airborne concentrations below exposure limits.

**Personal Protection:** Wear appropriate protective eyeglasses or chemical safety goggles. Wear appropriate protective clothing to prevent skin contact. Use a NIOSH approved respirator when adequate ventilation or local exhaust ventilation to keep airborne concentrations below exposure limits cannot be achieved. Wear impervious gloves, viton or nitrile.

## Section 9: Physical and Chemical Properties

<b>Physical State:</b>	Liquid	<b>Odor:</b>	Alcohol	<b>Solubility:</b>	Miscible	<b>Evaporation Rate:</b>	1.5 (ether=1)
<b>Boiling Point:</b>	82°C	<b>Specific Gravity:</b>	0.787	<b>Vapor Pressure:</b>	40mmHg @23.8°C	<b>Vapor Density:</b>	2.1 (Air=1) <b>pH:</b> N/a

## Section 10: Stability and Reactivity

**Stability:** Stable at normal temperatures and pressures.

**Conditions to avoid:** Temperatures over 40°C, ignition sources, and incompatible substances.

**Incompatibilities:** Strong oxidizers, acetaldehyde, chlorine, ethylene oxide, acids and isocyanates, hydrogen + palladium, nitroform, oleum, phosgene, oxygen, aluminum, aluminum triisopropoxide, trinitromethane, barium perchlorate, tetrafluoroborate, chromium trioxide, sodium dichromate + sulfuric acid.

**Polymerization:** Will not occur.

**Decomposition:** Carbon monoxide, carbon dioxide, acid smoke and fumes.

## Section 11: Toxicological Information

<b>Sensitization:</b> (effects of repeated exposure)		Repeated skin contact may cause defatting of the skin resulting in dermatitis.				
<b>Carcinogenicity:</b> (risk of cancer)		No				
<b>Teratogenicity:</b> (risk of malformation in an unborn fetus)		No				
<b>Reproductive Toxicity:</b> (risk of sterility)		No				
<b>Mutagenicity:</b> (risk of heritable genetic effects)		No				
<b>Lethal Exposure Concentrations:</b>	<b>Ingestion (LD50):</b>	3600mg/kg (rat)	<b>Inhalation (LC50):</b>	16000 ppm/4h (rat)	<b>Skin (LD50):</b>	5030-7900 mg/kg

## Section 12: Ecological Information

**General Information:** Avoid runoff into storms and sewers, which lead into waterways. Water runoff can cause environmental damage.

**Environmental Impact Data:** (percentage by weight)

CFC: 0      HFC: 0      Cl.Solv: 0      VOC: 100      HCFC: 0      ODP: 0

## Section 13: Disposal Information

**General Information:** Dispose of in accordance with all local, provincial, state, and federal regulations. Water runoff can cause environmental damage.

## Section 14: Transportation Information

**Ground Canada:** (1 Liter and smaller)

Classified as **Consumer Commodity**.

**Refer to TDG regulations** (Canadian Transportation of Dangerous Goods regulations). **Recommend Shipper be trained and certified.**

**Ground USA:** (1 Liter and smaller)

Classified as **ORM-D**. Refer to USA CFR 49 Regulations.

**Recommend Shipper be trained and certified.**

**Ground Canada and USA:** - (1 gallon sizes and larger)

**Shipper must be trained and certified. Refer to CFR 49 (USA), and TDG regulations (Canada).**

Shipping Name: **ISOPROPANOL**, UN number: **1219**, Class: **3**, Packing Group: **II**, Flash Point: 12°C.

Subsidiary Risk – nil, Recommend using original MG Chemicals UN Certified outer cartons. Tape all seams on the carton. Hazard Label required – Flammable Liquid. A double arrow orientation label is required and is already printed on the original outer carton.

**Air:**

**Shipper must be trained and certified. Refer to IATA Dangerous Goods Regulations.**

Shipping Name: **ISOPROPANOL**, UN number: **1219**, Class: **3**, Packing Group: **II**, Flash Point: 12°C.

Subsidiary Risk – nil, Recommend using original MG Chemicals certified outer cartons. Tape all seams on the carton. Hazard Label required – Flammable Liquid. A double arrow orientation label is required and is already printed on the original outer carton.

**Sea - All Sizes:**

**Shipper must be trained and certified. Refer to IMDG regulations.**

Shipping Name: **ISOPROPANOL**, UN number: **1219**, Class: **3**, Packing Group: **II**, Flash Point: 12°C.

## Section 15: Regulatory Information

**This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations and the MSDS contains all of the information required by the Controlled Products Regulations.**

**SARA** (Superfund Amendments and Reauthorization Act of 1986, USA, 40 CFR 372.4)

This product contains >99% % of 2-propanol (CAS# 67-63-0), a toxic chemical subject to the reporting requirements.

**EPCRA** (Emergency Planning and Right to Know Act, USA, 40 CFR 372.45)

This product does contain >99% of 2-propanol (CAS# 67-63-0) a chemical subject to the reporting requirements of section 313 Title III of the SARA of 1986 and 40 CFR part 372.

**TSCA** (Toxic Substances Control Act of 1976, USA)

All substances are TSCA listed.

**CAA** (Clean Air Act, USA)

This product does not contain any class 1 ozone depleting substances.

This product does not contain any class 2 ozone depleting substances.

This product does not contain any chemicals listed as hazardous air pollutants.

**California Proposition 65** (Chemicals known to cause cancer or reproductive toxicity, May 1, 1997 revision, USA)

This product does not contain any chemicals listed.

**Health Canada**

Labeling and containers used in this product are listed in compliance with Consumer Chemicals and Container regulations.

**Environment Canada**

Chemicals in this product are listed on the Domestic Substances List in the Canadian Environmental Protection Act

This product does not contain any ozone depleting substances.

**Industry and Science Canada**

Labeling, product identity, net quantity declaration, minimum printing type size heights, and packaging of this product is in compliance with the Consumer Packaging and Labeling Act and Regulations. This product is not slack filled in accordance to chapter 4 prohibitions.

**RoHS** (The restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2004).

This product is RoHS compliant.

## Section 16: Other Information

**Definitions:** N/a = not applicable, n/e = not established

**Disclaimer:** This material safety data sheet is provided as an information resource only. M.G. Chemicals believes the information contained herein is accurate and compiled from reliable sources. It is the responsibility of the user to verify its validity. The buyer assumes all responsibility of using and handling the product in accordance with federal, state, and local regulations.