



THIS DOCUMENT IS THE PROPERTY OF APEM COMPONENTS AND SHALL NOT BE COPIED, REPRODUCED, DISCLOSED OR USED AS THE BASIS FOR MANUFACTURING OR SALE WITHOUT PERMISSION OF A DULY AUTHORIZED REPRESENTATIVE OF APEM COMPONENTS INC.



DESCRIPTION: DPDT ON-ON RIGHT ANGLE ROCKER SWITCH
SPECIFICATIONS:
CURRENT/VOLTAGE RATINGS WITH RESISTIVE LOADS:
3A 250VAC,
6A 125VAC,
4A 30VDC
INITIAL CONTACT RESISTANCE: 10mΩ MAX.
INSULATION RESISTANCE: 1,000MΩ MIN. AT 500VDC
DIELECTRIC STRENGTH:
1,000vrms 50Hz MIN. BETWEEN TERMINALS,
1,500vrms 50Hz BETWEEN TERMINALS AND FRAME
1,500vrms 50Hz BETWEEN POLES
CONTACT BOUNCE: 2ms MAX.
ELECTRICAL LIFE AT FULL LOAD: 50,000 CYCLES
OPERATING TEMPERATURE: -40°C TO +85°C

MATERIALS:
CASE: DAP OR HIGH TEMP. PLASTIC MATERIAL
ACTUATOR: POLYAMIDE
BUSHING: NICKEL PLATED BRASS
HOUSING: STAINLESS STEEL OR TIN PLATED STEEL
CONTACTS: SILVER
TERMINAL SEAL: EPOXY

ROHS COMPLIANT



Q.A. INSPECT:		DESIGNER'S INITIAL:		TOLERANCES (UNLESS AS NOTED) .XX = ±.02 [0.5] .XXX = ±.008 [0.20] .XXXX = ±.0008 [0.02] ANGLE = ±0.5°	
DATE		SHEET		SIZE	
12/18/08		1 OF 1		B	
DRAWING NO.		SCALE		THIRD ANGLE PROJECTION	
57946WAX433VDEUCSA		3:1		PJD	
REV		TITLE		VDE APPROVED	
A		ROCKER SWITCH		ROCKER SWITCH	

DATE	SYM	REVISION RECORD	DWN.	CK.