

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

By

ALL RIGHTS RESERVED.

LOC

CM

DIST

0

REVISONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
D		REVISED PER ECR-15-010337	24JUL2015	RK	SC

26.39

9.83

6

5

4

3

2

1

12

11

10

9

8

7

13.49

0.76

12

11

10

9

8

7

AMP

HOUSING

PIN CONTACT
12 REQUIRED

1.000±0.051

5.08 MIN
LOCALIZED GOLD
PLATE AREA

3.68±0.25

5.08 MIN
LOCALIZED MATTE TIN PLATE
OR TIN-LEAD PLATE AREA

Ø3.17

-A-

4.45

4.14

4.14

Ø1.40±0.08

⊕ Ø0.13 (M) A (M)

12 PLC INDIVIDUALLY

RECOMMENDED MOUNTING HOLE PATTERN
FOR 1.57 THICK P.C. BOARD

BRASS, GOLD	NYLON, 94V-0, WHITE	1-794066-1
BRASS, TIN	NYLON, 94V-0, WHITE	1-794066-0
BRASS, GOLD	NYLON, 94V-0, WHITE	794066-2
BRASS, TIN LEAD	NYLON, 94V-0, WHITE	794066-1
PIN CONTACT MATERIAL AND FINISH	HOUSING MATERIAL AND COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

0

1

2

3

4

PLC
PLC
PLC
PLC
PLC

± -
± -
± 0.13
± -
± -

ANGLES
SEE TABLE

DWN
K. WHITAKER

CHK
R. SWING

APVD
R. ORSTAD

6-12-95

6-12-95

6-13-95

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

HEADER ASSEMBLY, 12 CIRCUIT,
DOUBLE ROW VERTICAL,
MINI-UNIVERSAL MATE-N-LOK

A100779

794066

SCALE 8:1

SHEET 1 OF 1

REV D