



VPO
Visual Persistence Oscilloscope

The GDS-2000A Series DSO comes along with a high-value design framework, including 2G Sa/s sampling rate, 2M points record length, 2 or 4 input channels and a large screen color LCD display, to perform very fast waveform acquisition and procession at 80,000 wfms/s update rate utilizing VPO (Visual Persistence Oscilloscope) technology.

The GDS-2000A Series, carrying bandwidths of 300MHz, 200MHz, 100MHz and 70MHz and inputs of 2 and 4 channels, makes up a family of 8 in the whole series. The 2M points record length not only enables the long time waveform storage but also plays the role as a huge database of the input signals for the post-storage waveform analysis. Two powerful functions, Waveform search and segmented memory are available of the GDS-2000A Series to facilitate the search for the waveforms of interest from the long record length. Waveform search defines the waveform types for the search whereas segmented memory divides the whole record length into a number of segments as to speed up the waveform search by looking into only the segments containing the waveforms of interest.

The ping-pong waveform acquisition design and the advanced VPO-technology-based waveform procession system, greatly enhance the speed and the quality of waveform display of GDS-2000A Series at a very fast update rate of 80,000 waveforms per second.

The optional logic analyzer function allows the signal acquisition through logic triggering and enables the logic waveforms and the analog waveforms to be shown on the same screen for comparison and time correlation analysis. This Mixed Signal Oscilloscope (MSO) function is field-installable with a plug-in module, containing either 8 or 16 input channels, at the rear panel. The MSO function supports the I²C / SPI / UART serial bus trigger and decoding.

The GDS-2000A Series is equipped with all the features that a high-tech DSO should have today. The RS-232C interface, USB ports, and Go-NoGo output are provided as standard, and the Ethernet port, SVGA Video output and GPIB port are available as options for user's free selection. At a moderate cost, GDS-2000A Series is a DSO to provide high customer-value with innovative design.

GDS-2000A Series

FEATURES

- 300/200/100/70MHz Bandwidth, 2 or 4 Input Channels
- 2GSa/s Real-Time Sampling Rate and 100GSa/s Equivalent Time Sampling Rate
- 2Mpoints Record length
- VPO Technology to Display Less-Frequently-Occurred Signals
- Fastest Update Rate of 80,000 Waveform Per Second
- Segmented Memory Acquisition and Waveform Search Function
- Optional 8 or 16 Additional Digital Channels with Logic Analyzer (MSO) & Serial Bus I²C/SPI/UART Trigger and Decode Software
- Optional Function Generator
- Flexible Remote Control Connectivity (Standard : USB ; Optional : LAN/ GPIB)



Front



Rear Panel

APPLICATIONS

- Industrial and Educational R&D Labs
- Product Testing and Quality Assurance
- Embedded System and Mix Signal Design
- System Integration & Debugging
- Maintenance & Repair Service

SPECIFICATIONS

		GDS-2072A	GDS-2074A	GDS-2102A	GDS-2104A	GDS-2202A	GDS-2204A	GDS-2302A	GDS-2304A	
VERTICAL	Channels	2Ch+EXT	4Ch+EXT	2Ch+EXT	4Ch+EXT	2Ch+EXT	4Ch+EXT	2Ch+EXT	4Ch+EXT	
	Bandwidth	DC~70MHz(-3dB)		DC~100MHz(-3dB)		DC~200MHz(-3dB)		DC~300MHz(-3dB)		
	Rise Time	5ns		3.5ns		1.75ns		1.17ns		
	Bandwidth Limit	20MHz		20MHz		20M/100MHz		20M/100M/200MHz		
	Vertical Resolution	8 bits@1M : 1mV*~10V (* : When the vertical scale is set to 1mV/div, the bandwidth limit will be set to 20MHz automatically)								
	Input Coupling	AC, DC, GND								
TRIGGER	Input Impedance	1MΩ// 16pF approx.								
	DC Gain Accuracy(**)	±(5% X Readout + 0.1div + 1mV) when 1mV/div is selected ; ±(3% X Readout + 0.1div + 1mV) when 2mV/div or greater is selected + , - , x , ÷ , FFT , FFTrms (** : The measurement type is average of ≥16 waveforms with vertical position at zero)								
	Polarity	Normal , Invert								
	Maximum Input Voltage	300V (DC+AC Peak), CAT I								
	Offset Position Range	1mV/div ~ 20mV/div : ±0.5V ; 50mV/div ~ 200mV/div : ±5V ; 500mV/div ~ 2V/div : ±25V ; 5V/div~10V/div : ±250V								
	Waveform Signal Process	FFT : Spectral magnitude. Set FFT Vertical Scale to Linear RMS or dBV RMS, and FFT Window to Rectangular, Hamming, Hanning, or Blackman-Harris								
	Source	Ch1 ,CH2, CH3*, CH4*, Line, EXT, D0-D15 : *four channel models only								
	Trigger Mode	Auto (Supports Roll Mode for 100 ms/div and slower), Normal, Single								
	Trigger Type	Edge, Pulse Width, Video, Pulse Runt, Rise & Fall, Alternate, Event-Delay(1~65,535 events), Time-Delay(10ns~10s), Logic*, Bus* , *with DS2-LAD option								
	EXT TRIGGER	Trigger Holdoff Range	10ns ~ 10s							
Coupling		AC, DC, LF rej. , Hf rej. , Noise rej.								
Sensitivity		DC ~ 100MHz Approx. 1div or1.0mV ; 100MHz ~ 200MHz Approx.1.5div or 15mV ; 200MHz ~ 300MHz Approx.2div or 20mV								
Coupling		AC,DC,LF rej. ,Hf rej. ,Noise rej.								
Sensitivity		DC ~ 100MHz Approx. 1div or 1.0mV ; 100MHz ~ 200MHz Approx. 1.5div or 15mV ; 200MHz ~ 300MHz Approx. 2div or 20mV								
Range		±15V								
Sensitivity		DC ~ 100MHz Approx. 100mV								
Input Impedance		100MHz ~ 200MHz Approx. 150mV ; 200MHz ~ 300MHz Approx. 150mV 1MΩ±3%, ~16pF								
HORIZONTAL		Time Base Range	1ns/div ~ 100s/div (1-2-5 increments); ROLL : 100ms/div ~ 100s/div							
		Pre-trigger	10 div maximum							
	Post-trigger	1,000 div max (depend on time base)								
	Accuracy	±20 ppm over any ≥ 1 ms time interval								
	Real Time Sample Rate	Max. : 2GSa/s								
	ET Sample Rate	100GSa/s maximum for all models								
	Record Length	Max. : 2Mpts								
	Acquisition Mode	Normal, Average, Peak Detect, Single								
	Peak Detection	2ns (typical)								
	Average	Selectable from 2 to 256								
X-Y MODE	X-Axis Input	Channel 1 ; Channel 3* (* : four channel models only)								
	Y-Axis Input	Channel 2 ; Channel 4* (* : four channel models only)								
CURSORS AND MEASUREMENT	Phase Shift	±3° at 100kHz								
	Cursors	Amplitude, Time, Gating Available; Unit : Seconds(S), Hz(1/S), Phase (Degrees), Ratio(%)								
	Automatic Measurement	36 sets: Pk-Pk, Max, Min, Amplitude, High, Low, Mean, Cycle Mean, RMS, Cycle RMS, Area, Cycle Area, ROVShoot, FOVShoot, RPREShoot, FPREShoot, Frequency, Period, RiseTime, FallTime, +Width, -Width, Duty Cycle, +Pulses, -Pulses, +Edges, -Edges, FRR, FRF, FFR, FFF, LRR, LRF, LFR, LFF, Phase								
	Control Panel Function	Cursors measurement								
	Auto Counter	6 digits, range from 2Hz minimum to the rated bandwidth								
	Autoset	Single-button, automatic setup of all channels for vertical, horizontal and trigger systems, with undo Autoset								
DISPLAY SYSTEM	Save Setup	20set								
	Save Waveform	24set								
	TFT LCD Type	8" TFT LCD SVGA color display(LED Back-light)								
	Display Resolution	800 horizontal x 600 vertical pixels (SVGA)								
	Interpolation	Sin(x)/x & Equivalent time sampling								
	Waveform Display	Dots, Vectors, Variable persistence(16ms~10s), Infinite persistence								
INTERFACE	Waveform Update Rate	80,000 waveforms per second, maximum								
	Display Graticule	8 x 10 divisions								
	RS-232C	DB-9 male connector								
	USB Port	2 sets USB 2.0 high-speed host port ;1 set USB high-speed 2.0 device port								
	Ethernet Port	RJ-45 connector, 10/100Mbps with HP Auto-MDIX (option)								
	SVGA Video Port	SVGA output (option)								
LOGIC ANALYZER (OPTION)	GPIO	GPIO module (Optional)								
	Go/NoGo BNC	5V Max/10mA TTL open collector output								
	Kensington Style Lock	Rear-panel security slot connects to standard Kensington-style lock								
	Sample Rate	500MSa/s								
	Bandwidth	200MHz								
	Record Length	2M max								
	Input Channels	16 Digital (D15 - D0) or 8 Digital (D7~D0)								
	Trigger Type	Edge, Pattern, Pulse Width, Serial bus (I²C, SPI, UART)								
	Thresholds	Quad-D0 ~ D3, D4 ~ D7. . . . Thresholds								
	Threshold Selections	TTL, CMOS, ECL, PECL, User Defined								
User-defined Threshold Range	±10V									
Maximum Input Voltage	±40V									
Minimum Voltage Swing	±500mV									
Vertical Resolution	1 bit									
POWER SOURCE MISCELLANEOUS	Line Voltage Range	AC 100V ~ 240V, 48Hz ~ 63Hz, auto selection								
	Multi-Language Menu	Available								
	On-Line Help	Available								
	Time clock	Time and date, provide the date/time for saved data								
DIMENSIONS & WEIGHT	380(W) X 220(H) X 145(D)mm, Approx. 4.2 kg									

Note : Three-year warranty, excluding probes & LCD display panel.

Specifications subject to change without notice.

DS-2000AGD1DH

ORDERING INFORMATION

GDS-2304A	300MHz, 4-Channel, Visual Persistence DSO
GDS-2302A	300MHz, 2-Channel, Visual Persistence DSO
GDS-2204A	200MHz, 4-Channel, Visual Persistence DSO
GDS-2202A	200MHz, 2-Channel, Visual Persistence DSO
GDS-2104A	100MHz, 4-Channel, Visual Persistence DSO
GDS-2102A	100MHz, 2-Channel, Visual Persistence DSO
GDS-2074A	70MHz, 4-Channel, Visual Persistence DSO
GDS-2072A	70MHz, 2-Channel, Visual Persistence DSO

ACCESSORIES

Use manual x 1 ,Power cord x 1 , CD x 1
GTP-070A-4 :70MHz (10:1/1:1) Switchable passive probe for GDS-2072A/2074A(one per channel)
GTP-150A-2 :150MHz (10:1/1:1) Switchable passive probe for GDS-2102A/2104A(one per channel)
GTP-250A-2 :250MHz (10:1/1:1) Switchable passive probe for GDS-2202A/2204A(one per channel)
GTP-350A-2 :350MHz (10:1/1:1) Switchable passive probe for GDS-2302A/2304A(one per channel)

OPTION

DS2-LAN	Ethernet & SVGA output
DS2-GPIB	GPIB Interface
DS2-FGN	DDS Function Generator
DS2-8LA	8-Channel Logic Analyzer : includes 8-Channel Logic Analyzer Card(GLA-08)and 8-Channel Logic Analyzer Probe (GTL-08LA)
DS2-16LA	16-Channel Logic Analyzer includes 16 Channel Logic Analyzer Card(GLA-16) and 16-Channel Logic Analyzer Probe (GTL-16LA)

OPTION ACCESSORIES

GTL-08LA	8-Channel Logic Analyzer Testing Probe
GTL-16LA	16-Channel Logic Analyzer Testing Probe
GLA-08	8-Channel Logic Analyzer Card
GLA-16	16-Channel Logic Analyzer Card

FREE DOWNLOAD

PC Software	FreeWave software	Driver	USB driver ; LabView driver
--------------------	-------------------	---------------	-----------------------------

Global Headquarters

GOOD WILL INSTRUMENT CO., LTD.

No.7-1, Jhongsing Road, Tucheng Dist., New Taipei City 236, Taiwan

T +886-2-2268-0389 F +886-2-2268-0639

E-mail: marketing@goodwill.com.tw

China Subsidiary

GOOD WILL INSTRUMENT (SUZHOU) CO., LTD.

NO. 69, Lushan Road, Snd, Suzhou Jiangsu 215011 China

T +86-512-6661-7177 F +86-512-6661-7277

E-mail: marketing@instek.com.cn

Malaysia Subsidiary

GOOD WILL INSTRUMENT (M) SDN. BHD.

27, Persiaran Mahsuri 1/1, Sunway Tunas,

11900 Bayan Lepas, Penang, Malaysia

T +604-6309988 F +604-6309989

E-mail: sales@goodwill.com.my

U.S.A. Subsidiary

INSTEK AMERICA CORP.

3661 Walnut Avenue Chino, CA 91710, U.S.A.

T +1-909-5918358 F +1-909-5912280

E-mail: sales@instekamerica.com

Japan Subsidiary

INSTEK JAPAN CORPORATION

4F, Prosper Bldg, 1-3-3 Iwamoto-Cho Chiyoda-Ku,

Tokyo 101-0032 Japan

T +81-3-5823-5656 F +81-3-5823-5655

E-mail: info@instek.co.jp

Korea Subsidiary

GOOD WILL INSTRUMENT KOREA CO., LTD.

Room No.805, Ace Hightech-City B/D 1Dong,

Mulla-Dong 3Ca 55-20, Yeongduengpo-Gu, Seoul, Korea

T +82-2-3439-2205 F +82-2-3439-2207

E-mail: gwinstek@gwinstek.co.kr

GW INSTEK

Simply Reliable

www.gwinstek.com