



20 19 18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1





CARRIER VIEW




NOTES:

1. MATERIAL:
(0.20)/.008 THICK BRASS
2. FINISH:
122 - OVERALL TIN: (0.00381)/.000150 MIN. TIN OVER
(0.00076)/.000030 MIN NICKEL
154 - OVERALL TIN: (0.00254)/.000100 MIN. TIN OVER
(0.00127)/.000050 MIN NICKEL
P909 - OVERALL HOT TIN DIP: (0.00254)/.000100 MIN.
550 - SELECT GOLD: (0.000381)/.000015 MIN.
OVERALL GOLD FLASH: (0.00005)/.000002 MIN.
OVERALL NICKEL UNDERPLATE: (0.00076)/.000030 MIN.
555- SELECT GOLD (0.000381)/.000015 MIN.
OVERALL NICKEL UNDERPLATE: (0.00076)/.000030
558 - SELECT GOLD: (0.00076)/.000030 MIN.
OVERALL GOLD FLASH: (0.00005)/.000002 MIN.
OVERALL NICKEL UNDERPLATE: (0.00127)/.000050 MIN.
3. PRODUCT SPEC: PS-10-07
4. PACKAGING SPECIFICATION: LOOSE TERMINALS: PER PK-2759-001
CHAIN FORM TERMINALS: PER PK-2759-002
5. CRIMP IS FOR 22-30 GA WIRE WITH (1.57)/.062 DIA INSULATION MAX.
6. INSERTION FORCE OF TERMINAL INTO (2.54)/.100 CENTERLINE CONNECTOR IS 2.5 LBS. MAX
7. TERMINAL RETENTION IN HOUSING IS 26.7N / 6LBS MIN. WHEN PULLED AT THE RATE OF (25.4MM) / 1 INCH PER MINUTE.
8. DIMENSIONS GIVEN ACROSS CENTERLINES ARE SYMMETRICAL ABOUT THOSE CENTERLINES WITHIN HALF THE TOTAL TOLERANCE.
9. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.


SELECT GOLD LOCATION



CRIMP DETAIL



CRIMPED TERMINAL 2759-IP909IC IS USED WITHOUT WIRE AND IS INSERTED INTO HOUSING TO PROVIDE TENSION WHEN ASSEMBLED TO HEADERS DURING SHIPMENT.



SECTION A-A
BACKGROUND OMITTED

SECTION B-B
BACKGROUND OMITTED

2759-*****)

FORM

L=LOOSE

C=LOOSE CRIMPED

A=CHAIN, PER WINDING DETAIL "A"

B=CHAIN, PER WINDING DETAIL "B"

PLATING


SEE NOTE 2

ADD WINDING DETAIL EC NO: UCP2014-4131 DRWN:KIPER 2014/04/07 CHKD:NGUYEN 2014/04/08 APPR:FSM TH 2014/04/21 AW2		QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION	
						MM/IN			INCH		
▽=0			mm	INCH	DRAWN BY	DATE	TITLE				
▽=0			4 PLACES ± .010	± .010	SAMIEC	07/28/87	CRIMP TERMINAL				
▽=0			3 PLACES ± .010	± .010	CHECKED BY	DATE	22-30 GA WIRE				
▽=0			2 PLACES ± 0.25	± .014	PATEL	07/28/87					
▽=0			1 PLACE ± 0.36	± .014	APPROVED BY	DATE					
			0 PLACE ± .010	± .010	FSMITH	2012/03/20					
			ANGULAR ±1/2°			MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE CHART		SD-2759		1 OF 2	
						SIZE D		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			


20 19 18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1

2759-(***)*		
	PART NO.	ENG. NO.
	08-55-0101	2759-(555)B
	08-55-0102	2759-(555)L
	08-55-0126	2759-(555)A
	08-56-0109	2759-(550)B
	08-56-0110	2759-(550)L
	08-50-0113	2759-(P909)B
	08-50-0114	2759-(P909)L
	08-50-0124	2759-(P909)C
	08-51-0108	2759-(122)B
		2759-(122)L
	08-50-0274	2759-(P909)B
	08-50-0273	2759-(P909)A
	08-55-0130	2759-(558)B
	08-55-0131	2759-(558)L
	08-50-0160	2759-(154)L
	08-50-0159	2759-(154)B

WINDING DETAIL "A"



WINDING DETAIL "B"



SEE SHEET 1 SEC NO.: UCP2014-431 DRAWN BY: IPFER 2014/04/08 CHKD BY: NGUYEN 2014/04/08 APPR: FSMITH 2014/04/21	REV DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION
					MM/IN		1:1	INCH	
					DRAWN BY	DATE	TITLE		
			4 PLACES ±.005 ±.005		SAMIEC	07/28/87	CRIMP TERMINAL		
			3 PLACES ±.010 ±.010		CHECKED BY	DATE	22-30 GA WIRE		
			2 PLACES ±0.25 ±.014		PATEL	07/28/87			
			1 PLACE ±0.36 ±.014		APPROVED BY	DATE			
			0 PLACE ±.005 ±.005		FSMITH	2012/03/20			
			ANGULAR ±1/2°		MATERIAL NO.		DOCUMENT NO.		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-2759		
AW2	REV	DESCRIPTION	SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SHEET NO.		
			D				2 OF 2		