

SmartPro 3kVA 2880W Line Interactive Sine Wave UPS, Hot-Swappable, Extended-run & SNMP options, 2U Rack/Tower, USB, RS232, EPO, 120V

MODEL NUMBER: SMART3000RMOD2U



Description

3000VA / 3kVA 120V modular line interactive 2U rack / tower UPS for networks offers complete network-grade power protection with full support for hot-replacement of separate internal battery and electronics modules. High .96 power factor supports loads up to 2880 watts. High efficiency rating of 95% reduces electrical operating cost and BTU emissions. Offers selectable 110/120/127V 50/60Hz operation. Maintains battery derived sine wave AC output during power failures. Line-interactive dual-boost, single cut automatic voltage regulation (AVR) provides regulated 110/120/127V nominal output during brownouts and overvoltages. Includes NEMA L5-30P input plug and 7 UPS-supported output receptacles (6 x 5-15R, 1 x L5-30R). Includes two individually controllable load banks, for advanced remote-reboot and load-shedding applications. Network-grade AC surge and noise suppression. Network management interfaces support simultaneous communications via USB, DB9 serial and card slot for optional SNMPWEBCARD and other card accessories. HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. Supports detailed monitoring of equipment load levels, self-test data and utility power conditions via all three network interfaces at once. Advanced LED indicators offer 5-stage metering of UPS load and battery charge levels, plus single-LED status indicators for utility power, voltage regulation, on-battery, overload, replace battery and site wiring fault conditions. Audible alarms provide notification of on-battery, low-battery and overload conditions. Includes PowerAlert auto-shutdown and management software for complete monitoring, reporting and logging of all site and UPS operational conditions, plus support for advanced configurations involving load-shedding, remote-reboot and redundant dual-UPS applications. Internal batteries offer runtime of 11 minutes half load (1440 watts) and 4 minutes at full load (2880 watts). Runtime is expandable with optional BP72V15-2U (limit 1), BP72V28RT-3U (limit 4) and BP72V18-2US (limit 2) external battery packs. Supports installation in 4 post racks with included accessories. 2 post rackmount, wallmount and tower stand accessories sold separate.

Features

- 3000VA / 3kVA 120V modular line interactive 2U rack / tower UPS for networks

Highlights

- 3kVA / 3000VA / 2880W line interactive 2U rack/tower UPS, Sine Wave
- 100/120/127V output, Corrects brownouts and overvoltages 90 to 146V
- 0.96 Power Factor, Front panel status LEDs
- Hot-swappable internal UPS power module
- Extended runtime options up to 2880W
- 4 post compatible mounting
- 95% line-mode efficiency, 2 switched load banks
- USB, RS232, EPO and slot for SNMPWEBCARD option
- 120V NEMA L5-30P input, 6 NEMA 5-15/20R & 1 L5-30R outlets
- This product is ENERGY STAR qualified for its ability to save customers money while helping to protect the environment

Applications

DISTRIBUTED SERVER ROOMS;
NETWORK CLOSETS; SMALL
BUSINESS NETWORKS; SMALL
BUSINESS PHONE SYSTEM

Package Includes

- UPS chassis pre-loaded with hot-swappable UPS electronics module and internal battery module
- PowerAlert Software with USB, DB9 and EPO cabling
- 4 post rackmount installation accessories
- Owner's manual

- Hot-swappable power module and internal battery packs enables full UPS maintenance with zero-downtime
- High power factor of .96 offers support for loads to 2880 watts
- High efficiency line power operation of 95% reduces UPS electrical operating cost and BTU emissions
- Supports selectable 110, 120 and 127V nominal voltage operation at 50/60 Hz
- Sine wave AC output in AC and battery modes
- Line-interactive UPS with Automatic Voltage Regulation (AVR)
- L5-30P input plug connects to 120V 30A utility receptacle
- Includes 7 UPS supported outlets (6 5-15R and 1 L5-30R)
- L5-30R outlet is ideal for the connection of a 120V 30A PDU to distribute the full UPS capacity to rack equipment
- 5-15R outlets are arranged in two separately breaker, individually controllable loading banks to support remote reboot or automated load shedding of less critical items (bank 1 has 2 outlets, bank 2 has 4 outlets).
- Network-grade 800 joule AC surge suppression
- USB, DB9 serial and card-slot accessory are all available for simultaneous use in advanced network configurations
- HID compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- Includes PowerAlert auto-shutdown and management software for complete monitoring, reporting and logging of all site and UPS operational conditions, plus support for advanced configurations involving load-shedding, remote-reboot and redundant dual-UPS applications
- Advanced LED indicators offer 5-stage metering of UPS load and battery charge levels, plus single-LED status indicators for utility power, voltage regulation, on-battery, overload, replace battery and site wiring fault conditions.
- Audible alarms provide notification of on-battery, low-battery and overload conditions.
- Internal batteries offer runtime of 11 minutes half load (1440 watts) and 4 minutes at full load (2880 watts).
- Runtime is expandable with optional BP72V15-2U (limit 1), BP72V28RT-3U (limit 4) and BP72V18-2US (limit 2) external battery packs
- Some external battery configurations require the use of Tripp Lite's External Battery Configuration Software (see manual)
- Supports 4 post rackmount installation with included accessories; add 2POSTRMKITWM for 2 post and wallmount applications; add 2-9USTAND accessory for upright tower support
- This product is ENERGY STAR qualified for its ability to save customers money while helping to protect the environment

Specifications

| General Info | |
|-------------------------------------|----------------------------------------------------------|
| Product Group | UPS SYSTEMS |
| OUTPUT | |
| Output Capacity Details | 2400W max capacity with external battery packs connected |
| Output Volt Amp Capacity (VA) | 3000 |
| Output kVA Capacity (kVA) | 3 |
| Output Watt Capacity (Watts) | 2880 |
| Output kW Capacity (kW) | 2.9 |
| Power Factor | 1 |
| Nominal Output Voltage(s) Supported | 110V; 120V; 127V |
| Nominal Voltage Details | 120V default |

| | |
|--------------------------------------------|-------------------------------------------------------------------------------------------------------------|
| Frequency Compatibility | 50 / 60 Hz |
| Output Voltage Regulation (Line Mode) | 120V: -7% +9%, 110V: -8% + 11%, 127V: -9% +9% |
| Output Voltage Regulation (Battery Mode) | +/-5% |
| UPS Output Receptacles | 6 5-15R outlet(s); 1 L5-30R outlet(s) |
| Output Receptacles | Two switchable load banks - bank one consists of 2 5-15R outlets, bank 2 consists of 4 5-15R outlets |
| Output Circuit Breakers | 15A (x2) - breaker 1 covers 2 5-15R outlets, breaker 2 covers 4 5-15R outlets, L5-30R outlet is unbreakered |
| Output AC Waveform (AC Mode) | Pure Sine wave |
| Output AC Waveform (Battery Mode) | Pure Sine wave |
| INPUT | |
| Rated input current (Maximum Load) | 24A |
| Nominal Input Voltage(s) Supported | 110V AC; 120V AC; 127V AC |
| UPS Input Connection Type | L5-30P |
| UPS Input Cord Length (ft.) | 10 ft. |
| UPS Input Cord Length (m) | 3.05 |
| Recommended Electrical Service | 30A 120V |
| Input Cord Length (ft.) | 10 |
| Input Cord Length (m) | 3 |
| Input Phase | Single-Phase |
| BATTERY | |
| Full Load Runtime (min.) | 4 min. (2880w) |
| Half Load Runtime (min.) | 11 min. (1440w) |
| Expandable Battery Runtime | Extended runtime supported via optional external battery packs |
| External Battery Pack Compatibility | BP72V15-2U (limit 1); BP72V28RT-3U (multi-pack compatible); BP72V18-2US (multi-pack compatible) |
| DC System Voltage (VDC) | 72 |
| Battery Recharge Rate (Included Batteries) | Less than 4 hours to 90% (typical, full load discharge) |
| Internal UPS Replacement Battery Cartridge | RBC96-RMOD2U |
| Battery Access | Front panel battery access door |
| Battery Replacement Description | Hot-swappable, replaceable batteries |
| VOLTAGE REGULATION | |
| Voltage Regulation Description | Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 90 to 146 |
| Overvoltage Correction | Input voltages between 132 and 146 are reduced by 12% |

| | |
|---------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Undervoltage Correction | Input voltages between 101 and 110 are boosted by 15% |
| Severe Undervoltage Correction | Input voltages between 90 and 100 are boosted by 30% |
| LEDS ALARMS & SWITCHES | |
| LED Indicators | 14 LEDs indicate line power, power fail, avr, fault, overload, replace battery and site wiring fault conditions; includes 5 LED load and battery charge meter |
| Site Wiring Fault Indication | Includes site wiring fault LED |
| Audible Alarm | Audible alarm indicates on battery, low battery and overload warnings |
| Alarm Cancel Operation | Power-fail alarm can be silenced by pressing the on/test/mute switch |
| Switches | 2 Switches control off/on power status and alarm-cancel/self-test operation |
| SURGE / NOISE SUPPRESSION | |
| UPS AC Suppression Joule Rating | 800 joules |
| EMI / RFI AC Noise Suppression | Yes |
| AC Suppression Joule Rating | 800 |
| AC Suppression Response Time | Instantaneous |
| PHYSICAL | |
| Installation Form Factors Supported with Optional Accessories | 2 post rackmount (2POSTRMKITWM); Wallmount (2POSTRMKITWM); Tower (2-9USTAND) |
| Primary Form Factor | Rackmount |
| UPS Power Module Dimensions (hwd, in.) | 3.5 x 17.5 x 24 |
| UPS Power Module Dimensions (hwd, cm) | 8.9 x 44.4 x 61 |
| Rack Height | 2U |
| Secondary Form Factor | Tower (requires 2-9USTAND) |
| UPS Power Module Weight (lbs.) | 87 |
| UPS Power Module Weight (kg) | 39.5 |
| UPS Shipping Dimensions (hwd / in.) | 9.2 x 23.8 x 39.8 |
| UPS Shipping Dimensions (hwd / cm) | 23.4 x 60.5 x 101.1 |
| Shipping Weight (lbs.) | 103.9 |
| Shipping Weight (kg) | 47.2 |
| Cooling Method | Fan |
| UPS Housing Material | Steel |
| ENVIRONMENTAL | |
| Operating Temperature Range | +32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius |

| | |
|-------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| Storage Temperature Range | +5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius |
| Relative Humidity | 0 to 95%, non-condensing |
| AC Mode BTU / Hr. (Full Load) | 515.4 |
| Battery Mode BTU / Hr. (Full Load) | 1594 |
| AC Mode Efficiency Rating (100% Load) | 95% |
| COMMUNICATIONS | |
| Communications Interface | USB (HID enabled); DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface |
| Network Monitoring Port Description | Supports detailed monitoring of UPS and site power conditions |
| PowerAlert Software | Included |
| Communications Cable | USB, DB9 and EPO cabling included |
| LINE / BATTERY TRANSFER | |
| Transfer Time | 10 ms (line to battery) / 4 ms (battery to line) |
| Low Voltage Transfer to Battery Power (Setpoint) | 90 |
| High Voltage Transfer to Battery Power (Setpoint) | 146 |
| SPECIAL FEATURES | |
| Cold Start (Startup in Battery Mode During a Power Failure) | Cold-start operation supported |
| High Availability UPS Features | Hot swappable internal UPS power module; Hot swappable batteries |
| Green Energy-Saving Features | Individually controllable load banks |
| CERTIFICATIONS | |
| UPS Certifications | ENERGY STAR Qualified; Meets FCC Part 15 Category A (EMI); Tested to CSA (Canada); Tested to NOM (Mexico); Tested to UL1778 (USA) |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 2-year warranty, 3 year with registration. Note: Registration is required for 3-year warranty. |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$250,000 Ultimate Lifetime Insurance |

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.