



LOC	DIST	REVISIONS					
CE	16	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A2	ADDED P/N -99	12MAR07	JWD	JD

- 1

MAXIMUM CONNECTOR INSERTION LOSS IS 0.80dB PLUS CABLE ATTENUATION OF 1.5dB/km AT 1300nm (SEE TABLE)
2.

PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702



FIBER PATH SCHEMATIC

0.96	304.8±3.0 [1200.0±120.0]	9-5503994-9
0.81	6.00±0.08 [236.2±3.0]	5503994-6
0.81	10.00±0.15 [394±6]	5503994-5
0.81	5.00±0.08 [197±3]	5503994-4
0.80	3.00±0.05 [118±2]	5503994-3
0.80	2.00±0.05 [79±2]	5503994-2
0.80	1.00±0.05 [39±2]	5503994-1
MAX IL (dB)	L METERS [INCHES]	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN C.S.VASU 01 FEB 06	Tyco Electronics Corporation		
			CHK J.DUNCAN 01 FEB 06	Harrisburg, PA 17105-3608		
			APVD J.DUNCAN 01 FEB 06	NAME		
DIMENSIONS: METERS [INCHES]			PRODUCT SPEC	CABLE ASSEMBLY, FIBER OPTIC, 62.5/125 um ZIPCORD RISER, POLYMER COMPOSITE OVERMOLDED 2.5mm BAYONET, OPTIMATE		
			APPLICATION SPEC			
			WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C-5503994
			CUSTOMER DRAWING	SCALE NTS	SHEET 1 OF 1	REV A2