

NTE1343 Integrated Circuit Module, Hybrid, Dual Audio Power Amp, 10W/Ch

Applications:

- Designed for Outdoor Stereo and Radio Cassette Tape Recorder Use.

Absolute Maximum Ratings: ($T_A = +25^\circ\text{C}$ unless otherwise specified)

Supply Voltage, $V_{CC\text{max}}$	50V
Operating Case Temperature, T_C	-20° to $+105^\circ\text{C}$
Storage Temperature Range, T_{stg}	-20° to $+125^\circ\text{C}$
Turn-On Time ($V_{CC} = 31\text{V}$, $R_L = 4\Omega$, $P_O = 10\text{W}$, $f = 1\text{kHz}$), t_S	2sec

Recommended Operating Conditions: ($T_A = +25^\circ\text{C}$ unless otherwise specified)

Supply Voltage, V_{CC}	31V
Load Resistance, R_L	4Ω

Electrical Characteristics: ($T_A = +25^\circ\text{C}$, $V_{CC} = 31\text{V}$, $R_L = 4\Omega$, $R_g = 600\Omega$, $V_G = 40\text{dB}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Idle Current	I_{CCO}	$V_{CC} = 36\text{V}$	—	60	120	mA
Power Output	P_O	$V_{CC} = 13.2\text{V}$, THD = 10%, $f = 1\text{kHz}$	5.0	5.5	—	W
		THD = 10%, $f = 1\text{kHz}$	10	11.4	—	W
		THD = 1%, $f = 70\text{Hz}$ to 15kHz	—	20	—	W
Total Harmonic Distortion	THD	$V_{CC} = 9\text{V}$, $P_O = 0.1\text{W}$, $f = 1\text{kHz}$	—	0.5	0.8	%
		$P_O = 0.1\text{W}$, $f = 1\text{kHz}$	—	0.07	—	%
Frequency Range	f_L, f_H	$V_{CC} = 26.4\text{V}$, $P_O = 0.1\text{W}$, $+0\text{dB}$	40 to 50k			Hz
Input Resistance	r_i	$V_{CC} = 26.4\text{V}$, $P_O = 0.1\text{W}$	—	21	—	$k\Omega$
Noise Voltage	V_{NO}	$V_{CC} = 36\text{V}$	—	—	0.8	mV_{rms}

Pin Connection Diagram (Front View)

15	Input Rt Ch
14	Decouple
13	GND
12	GND
11	Output Rt Ch
10	Feedback Rt Ch
9	Ripple Filter
8	GND
7	V _{CC}
6	Feedback Lt Ch
5	Output Lt Ch
4	GND
3	GND
2	Decouple
1	Input Lt Ch

