




LOC		DIST		REVISIONS					
CM		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
			G	EC 0G3B 0215 05			20SEP05	BSV	RCJ



SECTION A—A
SCALE 10:1

- 1

0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN-LEAD IN TIN-LEAD PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
2.

WIRE RANGE: 3–6mm² [12–10 AWG].
3.

DIMENSIONS IN BRACKETS ARE IN INCHES.
- 4

0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN IN TIN PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
5.

THIS CONTACT HAS NO INSULATION BARREL.

GOLD 4	0.30 [.012] PH BRZ	1–770004–0
GOLD 1	0.30 [.012] PH BRZ	770004–4
PRE–TIN	0.30 [.012] PH BRZ	770004–3
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER	02APR04	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
		CHK C. JONES	02APR04				
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		APVD C. JONES	02APR04	-			
		PRODUCT SPEC		SOCKET, UNIVERSAL MATE-N-LOK(TM) II			
		APPLICATION SPEC		-			
		-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL		FINISH		A2	00779	C=770004	-
				CUSTOMER DRAWING			
				SCALE	4:1		SHEET
						1 of 1	REV
							G

