


THIS DRAWING IS A CONTROLLED DOCUMENT
C-1907569



Fiber Path

Blue - - - - - B

Orange/Natural - - - - - A

Right Side

Connector(s): LC-Duplex

Mode: SM

Housing Color: Blue

Geom. Spec: N/A

- Notes:
- 1 IL and RL tested at 1310nm.
 - 3 Label 2 will not be present on any cable assembly less than 5 meters long.
 - 4 Includes dust caps (not shown on print).

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSONS OR ENTITIES WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

	A	Rev Per EC#	RELEASE	9/28/2009	-	DK			
P	LTR	REVISION RECORD		DATE	DN	APVD			

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
meters	
	0 P.L.C. ± .
	1 P.L.C. ± .
	2 P.L.C. ± .
	3 P.L.C. ± .
	4 P.L.C. ± .

Restricted To:

DIN Cable Assy Configurator		MATERIAL -	HEAT TREAT	
DK Doug Kirsch		AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
APVD Doug Kirsch				
NAME FO C/A - 2 fiber, SM, OFNR (Riser) jacket, Pigtail - (1.6 to 2.0mm) to LC-Duplex				
SCALE NTS	SIZE A2	DRAWING NO C- 1907569	SHEET 1 of 3	REV A

8 7 6 5 4 3 2 1

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	A	Rev Per EC#	RELEASE	8/28/2009	-	D	
P	LTR	REVISION RECORD		DATE	DIN	AP	

Qty	U of M	Description	Item No
2	piece	Trace Label	6
2	piece	Eyeteel/Shrink tube assembly - Yellow	5
AR	meter	2 fiber, SM, 2.0mm, Twinzip, Yellow, OFNR (Riser)	4
2	piece	LC Connector Assy, SM	3
1	piece	LC Duplex clip, black	2
2	piece	LC, SC, FC Straight Boot, Blue	1

DIMENSIONS: meters		TOLERANCES UNLESS OTHERWISE SPECIFIED		DWN Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
				DW Doug Kirsch		 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
		APVD Doug Kirsch		NAME FO C/A - 2 fiber, SM, OFNR (RISER) jacket, Pigtail - (1.6 to 2.0mm) to LC-Duplex				SHEET 2 of 3	
		Restricted To:							

A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

8 7 6 5 4 3 2 1

	A	Rev Per EC#	RELEASE	9/28/2009	-	DK	
P	LTR	REVISION RECORD		DATE	DIN	APVD	

DIMENSIONS: meters	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 P.L.C. ± - 1 P.L.C. ± - 2 P.L.C. ± - 3 P.L.C. ± - 4 P.L.C. ± -

Restricted To:

DIN Cable Assy Configurator		MATERIAL -	HEAT TREAT	
OK Doug Kirsch				
APVD Doug Kirsch				
NAME FO CIA - 2 fiber, SM, OFNR (Riser) jacket, Pigtail - (1.6 to 2.0mm) to LC-Duplex				
SCALE NTS	SIZE A2	DRAWING NO C- 1907569	SHEET 3 of 3	REV A

Label 1

Per specification 107-1645-1



- Trace # - Bar Code
- Trace # - Human Readable
- Part Number
- Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



- Trace # - Bar Code
- Trace # - Human Readable
- Part Number
- Country of Origin

This label is used on all lengths on this drawing.

D
C
B
A