








4		3		2		1																																	
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC		DIST		REVISIONS																															
© COPYRIGHT - By -		ALL RIGHTS RESERVED.		H		—		P		LTR		DESCRIPTION		DATE		DWN		APVD																					
NOTES: Tolerances cable lengths: 0m to 0.5m +30mm 0.5m to 1.0m +50mm 1.0m to 3.0m +100mm < 3.0m +1.5%				L		20mm				A		INITIAL RELEASE		12NOV2013		GSK		BvH																					
										A1		ECR-14-011671		14AUG2014		GSK		BvH																					
		VIEW 'A'		A				PVC CABLE		No./diameter of wires		4 x 0.25 mm²		Wire isolation		PVC (br, wh, bl, bk)		C-track properties																					
										Jacket		PVC (UL/CSA)		Outer diameter		approx. 4.8 mm		Bend radius (moving)		10 x outer diameter		Temperature range (fixed)		-30...+80 °C		Temperature range (mobile)		-5...+80 °C											
<table><tr><td colspan="2">TECHNICAL DATA</td></tr><tr><td>Operating voltage</td><td>max. 30 V AC/DC</td></tr><tr><td>Operating current per contact</td><td>max. 4 A</td></tr><tr><td>Locking of ports</td><td>Screw thread M8 x 1 mm (recommended torque 0.4 Nm) self-securing</td></tr><tr><td>Protection</td><td>IP65 and IP67 when plugged and screwed down (EN 60529)</td></tr></table>		TECHNICAL DATA		Operating voltage	max. 30 V AC/DC	Operating current per contact	max. 4 A	Locking of ports	Screw thread M8 x 1 mm (recommended torque 0.4 Nm) self-securing	Protection	IP65 and IP67 when plugged and screwed down (EN 60529)			Contact Layout Female				Schematic diagram		flexible wire brown (+)		flexible wire white (N/C)		flexible wire black (N/O)		flexible wire blue (-)													
		TECHNICAL DATA																																					
		Operating voltage	max. 30 V AC/DC																																				
		Operating current per contact	max. 4 A																																				
		Locking of ports	Screw thread M8 x 1 mm (recommended torque 0.4 Nm) self-securing																																				
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)																																						
<table><tr><td colspan="2">PUR CABLE</td></tr><tr><td>No./diameter of wires</td><td>4 x 0.25 mm²</td></tr><tr><td>Wire isolation</td><td>PP (br, wh, bl, bk)</td></tr><tr><td>C-track properties</td><td>5 million</td></tr><tr><td>Jacket</td><td>PUR (UL/CSA)</td></tr><tr><td>Outer diameter</td><td>approx. 4.4 mm</td></tr><tr><td>Bend radius (moving)</td><td>10 x outer diameter</td></tr><tr><td>Temperature range (fixed)</td><td>-40...+80 °C</td></tr><tr><td>Temperature range (mobile)</td><td>-25...+80 °C</td></tr></table>		PUR CABLE		No./diameter of wires	4 x 0.25 mm²	Wire isolation	PP (br, wh, bl, bk)	C-track properties	5 million	Jacket	PUR (UL/CSA)	Outer diameter	approx. 4.4 mm	Bend radius (moving)	10 x outer diameter	Temperature range (fixed)	-40...+80 °C	Temperature range (mobile)	-25...+80 °C	4 pos		10mtr		5mtr		3mtr		1.5mtr		PVC		Black		1-2273011-4		4x22AWG PVC 10.0m		8	
		PUR CABLE																																					
		No./diameter of wires	4 x 0.25 mm²																																				
		Wire isolation	PP (br, wh, bl, bk)																																				
		C-track properties	5 million																																				
Jacket	PUR (UL/CSA)																																						
Outer diameter	approx. 4.4 mm																																						
Bend radius (moving)	10 x outer diameter																																						
Temperature range (fixed)	-40...+80 °C																																						
Temperature range (mobile)	-25...+80 °C																																						
1-2273011-3		4x22AWG PVC 5.0m		7																																			
1-2273011-2		4x22AWG PVC 3.0m		6																																			
1-2273011-1		4x22AWG PVC 1.5m		5																																			
4 pos		10mtr		5mtr		3mtr		1.5mtr		PUR		Black		2273011-4		4x22AWG PUR 10.0m		4																					
														2273011-3		4x22AWG PUR 5.0m		3																					
														2273011-2		4x22AWG PUR 3.0m		2																					
														2273011-1		4x22AWG PUR 1.5m		1																					
		LENGTH"L"		MATERIAL		JACKET COLOR		TE PN		DESCRIPTION		ITEM																											
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		12NOV2013		SATHISH KUMAR .G		CHK		12NOV2013		B.VELDHoven		APVD		12NOV2013		A.VAN ZANDVOORT		NAME		M8 X 1.0 ANGLED SOCKET PIGTAIL		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO									
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		mm		0 PLC ± -		1 PLC ± -		2 PLC ± -		3 PLC ± -		4 PLC ± -		ANGLES ± -		FINISH		108-19483		114-32127		A3		00779		C=2273011		SCALE		SHEET		REV					
																				CUSTOMER DRAWING		SCALE		SHEET		REV													