


SURFACE MOUNT 10BASE-T INTERFACE MODULE

Designed for Level One's LXT907



- ⊕ Integrated for adapter, hub, and motherboard applications
- ⊕ Designed to meet IEEE 802.3 10Base-T specifications
- ⊕ Low profile, surface mount package
- ⊕ 235°C peak solder reflow temperature rating

Electrical Specifications @ 25°C — Operating Temperature 0°C to +70°C

Part Number	Insertion Loss to 10MHz (db MAX)	Attenuation (dB MIN) XMIT			Return Loss 5 to 10 MHz (dB MIN)		Crosstalk (dB MIN) 5-10 MHz	Common Mode Rejection (dB MIN) XMIT					Hi-Pot (Vrms MIN)
		30 MHz	50 MHz	70 MHz	100 Ω	98 ± 13 Ω		30 MHz	50 MHz	100 MHz	200 MHz	500 MHz	
E2015	-1.2	-24	-30	-35	-18	-15	-35	-45	-40	-30	-20	-10	1500

U.S. Patent No. 5,015,981




NOTE:

1. For Tape & Reel packaging add a "T" suffix to the part number (i.e.: E2015T).
2. XMIT = Transmit Channel

Mechanical

Schematic

E2015



Weight 1.1 grams
Tape & Reel 600/reel
Tube 40/tube

Dimensions: $\frac{\text{Inches}}{\text{mm}}$

Unless otherwise specified, all tolerances are $\pm \frac{.010}{0,25}$

For More Information :

UNITED STATES (Worldwide)

12220 World Trade Drive
San Diego, CA 92128
Quick-Facts: 619 674 9672
<http://www.pulseeng.com>
TEL: 858 674 8100
FAX: 858 674 8262

UNITED KINGDOM (Northern Europe)

1 & 2 Huxley Road
The Surrey Research Park
Guildford, Surrey GU2 5RE
United Kingdom
TEL: 44 1483 401700
FAX: 44 1483 401701

FRANCE (Southern Europe)

Zone Industrielle
F-39270
Orgelet
France
TEL: 33 3 84 35 04 04
FAX: 33 3 84 25 46 41

SINGAPORE (Southern Asia)

150 Kampong Ampat
#07-01/02
KA Centre
Singapore 368324
TEL: 65 287 8998
FAX: 65 280 0080

TAIWAN, R.O.C. (Northern Asia)

3F-4, No. 81, Sec. 1
HsinTai Wu Road
Hsi-Chih, Taipei Hsien
Taiwan, R.O.C.
Tel: 886 2 2698 0228
FAX: 886 2 2698 0948

DISTRIBUTOR

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other products mentioned herein may be trademarks or registered trademarks of their respective owners.

♻️ Printed on recycled paper. ©1997, Pulse Engineering, Inc.

PRELIMINARY E118.P (11/97)