

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20



COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	05Jan2015	GY	CW
	A1	ECR-15-004309	24Mar2015	GY	CW
	B	ECR-15-013759	10Oct2015	DW	CW
	B1	ECR-16-015492	17NOV2016	QY	CW

NOTES:



- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 500V
RATED CURRENT: 16A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: $0.14mm^2 \sim 4mm^2$ (AWG26-AWG12)
CONTACT TYPE: CRIMP CONTACT
- CONTACTS NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20300X10XX000)

注释:


- 技术参数:
绝缘材料: PC
额定电压: 500V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
脉冲电压: 6KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: $0.14mm^2 \sim 4mm^2$ (AWG26-AWG12)
接线类型: 冷压接
- 端子需要单独订购.
(订货号参考图面: T20300X10XX000)




M4 SCREW, RECOMMENDED
TIGHTENING TORQUE 1.2Nm
M4螺丝, 推荐锁紧力矩1.2Nm



4X M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3螺丝, 推荐锁紧力矩0.5Nm



TYPE-1, T2040244101-000, TE LOGO
类型-1, T2040244101-000, TE LOGO




PANEL CUT FOR INSERTS FOR USING
WITHOUT HOODS/ HOUSINGS
不使用防护外壳时芯件的安装开孔图

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL

FINISH

DWN 19Aug2014

Gino.Yao

CHK 19Aug2014

Chris.Wang

APVD 19Aug2014

Xiang.Xu

PRODUCT SPEC

108-137044

APPLICATION SPEC

114-137044

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME

HE-024-MC

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

T2040244101000

-

SCALE

1:1


SHEET

1 OF 2

REV




B1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




NOTE :
SEE SHEET 1

注释 :
见页 1




TYPE-2 , T2040244101-001 , STAINLESS STEEL SCREW , NO LOGO
类型-2 , T2040244101-001 , 不锈钢螺丝 , 无LOGO



ALL SPEC DIMENSION REFER TO TYPE 1
所有产品规格尺寸参照 TYPE 1

T2040244101-001	HE-024-MC	HE-024 MALE INSERT, CRIMPING, STAINLESS STEEL SCREW, NO LOGO HE-024公插, 冷压针, 不锈钢螺丝, 无LOGO	TYPE-2 类型-2
T2040244101-000	HE-024-MC	HE-024 MALE INSERT, CRIMPING HE-024公插, 冷压针	TYPE-1 类型-1
PART NUMBER 料 号	PART DESCRIPTION 描 述		TYPE 类 型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Gino.Yao 19Aug2014	 TE Connectivity					
		CHK Chris.Wang 19Aug2014						
DIMENSIONS: mm		APVD Xiang.Xu 19Aug2014	NAME HE-024-MC					
		PRODUCT SPEC 108-137044	SIZE A3			CAGE CODE 00779	DRAWING NO C-T2040244101000	RESTRICTED TO -
		APPLICATION SPEC 114-137044						
MATERIAL - -		WEIGHT -						
CUSTOMER DRAWING			SCALE 1:1		SHEET 2 OF 2		REV B1	