

- For Use with Discrete LEDs, Models 200 & PC3 - Mounting Diameter .250" (6.35) - RC200, KN40, LW40, HN40 Mounting Hardware Included

1	Model	Wires
	PS200	W (optional)

2	Bezel Finish
	-B Black
	-S Silver

3	Voltage ^[1]
	-5H
	-12H
	-15H
	-24H
	-28H
	-48H

Voltage/Current	
Design Vf/I _f ^[2]	Max Vf/I _f ^[2]
V/C Table I	
5V/27mA	5.5V/40mA
12V/27mA	14V/35mA
15V/24mA	16.5V/28mA
24V/17mA	26V/20mA
28V/16.5mA	30V/18mA
48V/15mA	50V/16mA


TO ORDER, FOLLOW THE EXAMPLE:

Select one **BOLD** component from each numbered category in the tables below.


1	Model	Wires	2	Bezel Finish	3	Voltage
	PS200	W		-B		-12H

→ Part Number **PS200W-B-12H**

PS200 With Resistor *PC3 LED not Included*



PS200 Without Resistor *Discrete LED not Included*



[1] Ta=25°C. Voltages 5H through 48H are VDC. For AC operation, insert D after Voltage (e.g. 24HD).

D indicates built-in rectifier; not required for 15VAC or less. For a socket without a built-in resistor, omit Voltage (e.g. PS200-B).

[2] Design current will vary depending on LED used.

Standard Wire Leads:

6.0" total length(nominal)/.50" stripped (nominal), red anode/black cathode, 24 AWG TPB UL1061 insulation. Contact factory for other lengths, gauges and colors.

All dimensions are in inches (mm)

Tolerances: .xx"(x) ±.025"(.63) / .xxx"(xx)±.010"(.25)
Specifications are subject to change without notice.