

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

39517-7815

Status:


Active

Overview:

Eurostyle™ Terminal Blocks

Description:

3.81mm Pitch Eurostyle™ Vertical Plug, with Retention Screws and Standard Imprinting, Rear Wire Entry, Green Housing, Gold (Au) Plated, 15 Circuits



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Specification PS-39500-001 \(PDF\)](#)

General

Product Family

Terminal Blocks

Series

39517

Application

N/A

Comments

with Standard Imprinting|Rear Wire Entry

Component Type

Plug

Overview

Eurostyle™ Terminal Blocks

Product Name

ESE, Eurostyle™Pluggable

Type

Euro Block

UPC

822350461641

Physical

Circuits (Loaded)

15

Entry Angle

Horizontal

Lock to Mating Part

Yes

Number of Rows

1

Orientation

Vertical

Panel Mount

No

Pitch - Mating Interface

3.81mm

Pitch - Termination Interface

3.81mm

Polarized to Mating Part

Yes

Stackable

No

Temperature Range - Operating

-40°C to +105°C

Wire Size AWG

16, 18, 20, 22, 24, 26, 28, 30

Wire Size mm²

0.05 - 1.31

Electrical

Current - Maximum per Contact

8A

Voltage - Maximum

300V

Material Info

Reference - Drawing Numbers

Product Specification

PS-39500-001

Sales Drawing

SD-39517-002

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

39517Series

Mates With

Most 3.81mm Pitch Industry Standard PCB Headers, 39515 Vertical PCB Header with Threaded Retention Inserts, 39516 Horizontal PCB Header with Threaded Retention Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39517-7815](#)