




REVISIONS		
LTR	DESCRIPTION	DATE
R	REVISED PER DCR NO R060228	10/13/2006
R1	REVISED PER ECO-09-021510	12SEP09

1 TUBING VFP21 MARKED AS SHOWN IN WHITE CHARACTERS ON SURFACE INDICATED

2 TUBING VFP21 IS UL RECOGNIZED, IS RATED 125°C [257°F], 600 V AND MEETS VW-1 FLAME TEST.

3 TUBING VFP21 IS CSA CERTIFIED AND MEETS VW-1 FLAME TEST.

4 TUBING FP21 IS UNMARKED AND MEETS REQUIREMENTS OF AMS-DTL-23053/5-109-0

1	2 3	111.25 ± 3.05 [4.38 ± .12]	2 2-603329-3
4	4	61 m [200 ft] MINIMUM	1-603329-3
		50.8 ± 1.27 [2.00 ± .05]	1 1-603329-2
		1219.2 ± 12.7 [48.00 ± .50]	1-603329-1
		38.1 ± 1.14 [1.50 ± .05]	6 603329-6
1	2 3	61 m [200 ft] MINIMUM	603329-2
		1219.2 ± 12.7 [48.00 ± .50]	603329-1
MARKING	NOTES	LENGTH L	PART NUMBER

5. WEIGHT PER LINEAR FOOT/304.8 mm:
8.89 g/.0196 lbs.

6. MATERIAL: BLACK POLYOLEFIN

△ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

SPECIFICATION CONTROL DRAWING

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN mm. INCH DIMENSIONS ARE IN BRACKETS. DECIMALS .XX ± .01 [0004 in] .X ± .1 [004 in] ANGLES .X ± 0.5 DEG	DRAWN UNGUYEN	DATE 10/13/2006	Tyco Electronics Corporation 300 Constitution Drive Menlo Park, CA. USA 94025 Raychem	
	RPN		TITLE AMPSULATION VFP21 AND FP21 3/4 INCH ID, BLACK	
	CAD NAME R060228		SIZE B	CODE IDENT. NO. 06090
	THIRD ANGLE PROJECTION		DWG. NO. C-603329	
DO NOT SCALE THIS DRAWING				SHEET 1 OF 1