




- △ ZINC.
- △ STAINLESS STEEL.
- 3. TO ASSEMBLE JACKSCREW REFER TO INSTRUCTION SHEET #1189.
- △ HOLE CENTRALLY LOCATED WITHIN ±0.07 [.003] OF THE 5.54 [.218] DIA AND THE 2.77/2.84 [.109/.112] DIA CENTER LINES.
- △ CHROMATE CONVERSION, CLEAR WITH HEXAVALENT CHROMATE.
- △ CHROMATE CONVERSION, CLEAR W/O HEXAVALENT CHROMATE.

OBSOLETE	△	2.87 [.113]	201910-5
	-	2.11 [.083]	201910-3
	△	2.87 [.113]	201910-1
NOTES		A	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.FOLTZ 05/26/94 CHK R.STONE 06/16/94 APVD -	tyco Electronics Tyco Electronics Corporation Harriaburg, PA 17105-3608
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	NAME
0 PLC ± -	1 PLC ± -	APPLICATION SPEC	JACKSCREW KIT, UNASSEMBLED, FEMALE, M SERIES
2 PLC ± 0.13 [.005]	3 PLC ± -	SIZE	CAGE CODE
4 PLC ± -	ANGLES ± -	DRAWING NO	RESTRICTED TO
MATERIAL JACKSCREW BODY: △	FINISH JACKSCREW BODY: SEE NOTES	WEIGHT	A1 00779 ©=201910
JACKSCREW TIP: △	JACKSCREW PIN: PASSIVATE	CUSTOMER DRAWING	SCALE 4:1 SHEET 1 OF 1 REV L1
JACKSCREW PIN: △			