

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

G

14

R3

REVISED PER ECO-11-004587

07APR11

RK

HMR

11.10 MAX
[.437] WASHER R.

5.00±0.08[.197±.003] DIA
(FOR #10 STUD)

10.95
[.431]

DIMPLED SURFACE

BODY

1

SLEEVE

"B" MAX

"A" MAX

AMP
WIRE RANGE

8 AWG
STRANDED

FILE
E13288

8 AWG
STRANDED

LR7189
Certified

8 AWG
STRANDED

1

STAMP AMP 8* LOCATE APPROX AS SHOWN

2

TONGUE MATERIAL THK 1.02±0.08[.040±.003]

3

SEE TABLE FOR WIRE INSULATION DIA MAX

4

TAPE ITEMS ARE ON 30.48[1.200] CENTERS

9.91 [.390]	33.99 [1.338]	39.52 [1.556]	100	LOOSE PC	52263-5
8.38 [.330]	34.49 [1.358]	40.03 [1.576]	500	ON TAPE	52263-4
9.14 [.360]	33.99 [1.338]	39.52 [1.556]			52263-3
8.38 [.330]	34.49 [1.358]	40.03 [1.576]			52263-2
9.14 [.360]	33.99 [1.338]	39.52 [1.556]	100	LOOSE PC	52263-1
					52263
WIRE INSULATION DIA	"B"	"A"	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

FOR APPLICATION
TOOLING INFORMATION

FOR ORDER ENTRY

PRODUCT INFORMATION CENTER
1-800-522-6752

TOOLING ASSISTANCE CENTER
1-800-722-1111

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
105° C

VOLTAGE RATING:
600 V MAX

CIRCULAR MIL AREA:
6.64-10.54mm²[13,100-20,800]
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.20[.008]

3 PLC ± -

4 PLC ± -

ANGLES ± -

MATERIAL
COPPER PER ASTM B-152
PVC, COLOR: RED

FINISH
TIN PLATE
PER ASTM-B545

DWN
S.S. GOULDEN
CHK
R. HERSEY
APVD
B. BARE
PRODUCT SPEC
NOT AVAILABLE
APPLICATION SPEC
114-2161
WEIGHT
-

9-29-93
9-29-93
9-29-93

STE

TE Connectivity

NAME
TERMINAL, RING TONGUE,
PLASTI-GRIP,
WIRE SIZE: 8 AWG

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-52263

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
4:1

SHEET
1 OF 1

REV
R3

1470-19 (3/11)