




CUTTERS



www.eclipsetools.com


- High grade alloy steel
- Induction hardened cutting edges
- Double leaf springs
- Hot drop forged
- Mirror polished surface
- Oil hardened & tempered
- Hot-formed box joints

4-1/2" Semi-Flush Diagonal Cutter




Description	Application	Part No.
4-1/2" Semi-Flush Diagonal Cutter	Hard steel: 20 AWG, Soft steel: 16 AWG Copper: 12 AWG	200-056

4-1/2" Full-Flush Straight Side Cutter




Description	Application	Part No.
4-1/2" Full-Flush Straight Side Cutter	Hard steel: 20 AWG, Soft steel: 16 AWG Copper: 12 AWG	200-059

4-1/2" Full-Flush Diagonal Cutter




Description	Application	Part No.
4-1/2" Full-Flush Diagonal Cutter	Hard steel: 20 AWG, Soft steel: 16 AWG Copper: 12 AWG	200-057

5" Flush Oblique Cutter Slim Tip



Description	Application	Part No.
5" Flush Oblique Cutter Slim Tip	Hard steel: 20 AWG, Soft steel: 18 AWG Copper: 14 AWG	200-060

4-1/2" Slim Full-Flush Diagonal Cutter




Description	Application	Part No.
4-1/2" Slim Full-Flush Diagonal Cutter	Hard steel: 20 AWG, Soft steel: 16 AWG Copper: 14 AWG	200-058


5" Side Cutting Plier



Description	Application	Part No.
5" Side Cutting Plier	Hard steel: 20 AWG, Soft steel: 14 AWG Copper: 12 AWG	200-067

5" Micro Cutter

Description	Part No.
5" Micro Cutter	902-011


5" Micro Cutter

Unit: inch

Description	Application	Part No.
5" Micro Cutter	Copper 1.3mm	200-092

5" Economy Flush Cutter

- Spring loaded, flush cut
- Cushioned grips
- Diagonal blade orientation
- Good for PC board lead trimming




Unit: inch

Description	Application	Part No.
5" Economy Flush Cutter	Copper: 14 AWG	200-002

5" "ESD Safe" Micro Cutter

- Spring loaded handles
- Cutting copper and other soft leads
- Dissipative handles




Unit: inch

Description	Application	Part No.
5" "ESD Safe" Micro Cutter	Copper: 16 AWG	200-040

5" Precision Flush Cutter

- Micro tips, good for precision work




Unit: inch

Description	Application	Part No.
5" Precision Flush Cutter	Copper: 16 AWG	200-071

5" Heavy Duty "ESD Safe" Cutter


W/Safety clip

- Heavy duty blades and springs
- Spring loaded handles
- Dissipative handles
- Cutting copper and other soft leads
- Safety Clip Prevents Flying Leads



Unit: inch

Description	Application	Part No.
5" Heavy Duty "ESD Safe" Cutter	Copper: 12 AWG	200-041
With safety clip		200-082


5" Micro Cutter

Unit: inch

Description	Application	Part No.
5" Micro Cutter	Copper: 14 AWG, Soft steel: 21 AWG	200-088

5" Clean Cut Micro Nipper

- This nipper is designed for delicate work.




Unit: inch

Description	Application	Part No.
5" Clean Cut Micro Nipper	Cutting capacity: 20 AWG. soft wire	200-083

5" Cutting Plier



New




Unit: inch



Description	Application	Part No.
5" Cutting Plier	Copper: 1.3mm	PM-251

5" Micro Cutting Plier

- Material: SK5
- HRC: 50±3




Unit: inch




Description	Application	Part No.
5" Micro Cutting Plier	Soft steel: AWG 20 Copper: AWG 14	902-075

4 1/2" Precision Cutting Plier

- Material: S60C
- HRC: 55~60 (Cutting edge)




Unit: inch



Description	Application	Part No.
4 1/2" Precision Cutting Plier	Copper: AWG 14	902-078

5" Micro Cutting Plier

- Material: SK5
- HRC: 50±3




Unit: inch



Description	Application	Part No.
5" Micro Cutting Plier	Soft steel: AWG 20 Copper: AWG14	902-076

7" Plastic Cutting Plier

- Material: S55C
- HRC: 58±3 (Cutting edge)




Unit: inch



Description	Application	Part No.
7" Plastic Cutting Plier	only for plastic cutting	902-049

5" Micro Cutting Plier

- Material: SK5
- HRC: 50±3



Unit: inch



Description	Application	Part No.
5" Micro Cutting Plier	Copper: AWG 14	902-077



The pliers are for cutting plastic only. Do not use them to cut any other types of material.

All Purpose Snip



Cut cloth, carpet, linoleum, leather, cardboard, tin plate, branches, foam rubber and more. Stainless steel spring and blades resist rust and corrosion. Positive safety latch.

Description	Part No.
All Purpose Snip	902-082

Flat Cable Cutter



- Material: AISI 420
- Handle: P.P.+T.P.R
- Flat Blade Geometry

Description	Part No.
Flat Cable Cutter	902-083

Round Cable Cutter




Great for Coax and 100 Pair Cable

- Material: AISI 420
- HRC: P.P. + T.P.R
- Rounded Blade Geometry
- Comfort Grip

Description	Part No.
Round Cable Cutter	902-084

2-in-1 Wire Stripper/Cutter



- Great for PC Board and Cable Assy
- OAL: 5"

Description	Application	Part No.
2-in-1 Wire Stripper/Cutter	Stripper 0.4~1.6mm ² (26~14 AWG)	200-080


Round Cable Cutter



- For large wires up to 2/0
- Up to 100 Pair cable
- Return spring
- Insulated handles
- OAL: 8-1/2"

Description	Application	Part No.
Round Cable Cutter	Thick wire up to 2/0 (70mm ²) cable, 100 pair group telephone cable	200-046

4-1/2" Diagonal Cutter




Unit: inch

- Spring loaded handles
- Smooth cushion grip
- Cuts copper & other soft leads

Description	Application	Part No.
4-1/2" Diagonal Cutter	Soft steel: 16 AWG Copper: 14 AWG	200-037


5" Diagonal Cutters-two color



Unit: inch

Description	Application	Part No.
5" Diagonal Cutters-two color	Copper: 1.6mm	200-089


5" Heavy Duty Cutter



Unit: inch

Description	Application	Part No.
5" Heavy Duty Cutter	Piano wire 16 AWG	200-087

6" Diagonal Cutter



Unit: inch

- Smooth Cushion grip
- Cutting copper & other soft leads
- Chrome-Vanadium blades

Description	Application	Part No.
6" Diagonal Cutter	Soft steel: 12 AWG Copper: 10 AWG	200-038


6-1/2" Cable Cutter



- Cuts wire and cable up to 0.40" diameter
- Coaxial cable up to RG-9/U
- Spring loaded
- For copper and aluminum wire only

Description	Application	Part No.
6-1/2" Cable Cutter	Multi-conductor cable up to 0.5"(12.7mm) Stranded wire up to 8 AWG(10mm2)	200-015

6" 8" And 10" Cable Cutter



- Unique jaw shape keeps cable round during cutting
- Forged steel high quality blades

Description	Application		Part No.
	Copper cable	Aluminum cable	
6" Cutter	4 AWG solid, 2 AWG stranded 2/0 flexible	2/0 stranded	200-068
8" Cutter	3 AWG flexible	3 AWG stranded	200-013
10" Cutter	2 AWG flexible	2 AWG stranded	200-069


Wire Rope Cutter



- Cuts metal wires, rods and ropes
- Compare to Klein 63016
- O.A.L.: 7-1/2"

Description	Application	Part No.
Wire Rope Cutter	Cutting capacities: 0.16"(4mm) Wire rope 0.06"(1.5mm) Spring wire	200-063

8" Side Cutting Plier



Unit: inch

Description	Application	Part No.
8" Side Cutting Plier	Cutting edge: HRC55 $\pm$ 3° Material: S55C Hardness: HRC40°~45°	902-246

Ratchet Cable Cutter



Item #: 902-258

New



Item #: 902-259

New




- Cuts cable up to 750MCM
- Quick release knob for easy blade back out
- Handle locks for convenient tool storage
- For copper and Aluminum Cables only not for cutting Steel

Description	Part No.
Ratchet Cable Cutter	902-062
Moving blade for 902-062	902-258
Stationary blade for 902-062	902-259


Heavy Duty Cable Cutter

- Ratcheted w/safety release
- Comfortable handles
- For aluminum and soft Copper cables up to 1.25" - 500 MCM



Description	Application	Part No.
Heavy Duty Cable Cutter	1.25" Copper & Aluminum cable	200-006
Replacement Blade (stationary)		200-035
Replacement Blade (moving)		200-034

Heavy Duty Cable Cutter



- Rubber cushioning in handle
- Heavy duty construction

Description	Application	Part No.
Heavy Duty Cable Cutter	Copper and aluminum cables up to 500 MCM	200-043


Finger Duct Cutter



- For finger duct only.

Description	Part No.
Finger Duct Cutter	200-086

Ratchet PVC Pipe Cutter



- Ratcheted design - Easy on hands

Description	Application	Part No.
Ratchet PVC Pipe Cutter	Cuts up to 1.25" diameter PVC pipe	200-039
Replacement Blade		200-045

Ratchet PVC Pipe Cutter



- Ratcheted

Description	Application	Part No.
Ratchet PVC Pipe Cutter	Cuts up to 2 inch Diameter PVC Pipe	200-076
Replacement Blade		900-211

PVC Pipe Cutter (Economy type)

Best Value

New



Description	Part No.
PVC Cutter(Economy type)	SR-008