



## HEXFRED® Ultrafast Soft Recovery Diode, 15 A

HFA15TB60



TO-220AC

HFA15TB60-1



TO-262

### FEATURES

- Ultrafast recovery
- Ultrasoft recovery
- Very low  $I_{RRM}$
- Very low  $Q_{rr}$
- Specified at operating conditions
- Designed and qualified for industrial level

### BENEFITS

- Reduced RFI and EMI
- Reduced power loss in diode and switching transistor
- Higher frequency operation
- Reduced snubbing
- Reduced parts count

### DESCRIPTION

HFA15TB60 is a state of the art ultrafast recovery diode. Employing the latest in epitaxial construction and advanced processing techniques it features a superb combination of characteristics which result in performance which is unsurpassed by any rectifier previously available. With basic ratings of 600 V and 15 A continuous current, the HFA15TB60 is especially well suited for use as the companion diode for IGBTs and MOSFETs. In addition to ultrafast recovery time, the HEXFRED® product line features extremely low values of peak recovery current ( $I_{RRM}$ ) and does not exhibit any tendency to "snap-off" during the  $t_b$  portion of recovery. The HEXFRED features combine to offer designers a rectifier with lower noise and significantly lower switching losses in both the diode and the switching transistor. These HEXFRED advantages can help to significantly reduce snubbing, component count and heatsink sizes. The HEXFRED HFA15TB60 is ideally suited for applications in power supplies and power conversion systems (such as inverters), motor drives, and many other similar applications where high speed, high efficiency is needed.

### PRODUCT SUMMARY

|                        |                |
|------------------------|----------------|
| $V_R$                  | 600 V          |
| $V_F$ at 15 A at 25 °C | 1.7 V          |
| $I_{F(AV)}$            | 15 A           |
| $t_{rr}$ (typical)     | 19 ns          |
| $T_J$ (maximum)        | 150 °C         |
| $Q_{rr}$               | 84 nC          |
| $di_{(rec)}/dt$        | 188 A/ $\mu$ s |

### ABSOLUTE MAXIMUM RATINGS

| PARAMETER  | SYMBOL         | TEST CONDITIONS       | VALUES        | UNITS |
|--|----------------|-----------------------|---------------|-------|
| Cathode to anode voltage                         | $V_R$          |                       | 600           | V     |
| Maximum continuous forward current               | $I_F$          | $T_C = 100\text{ °C}$ | 15            | A     |
| Single pulse forward current                     | $I_{FSM}$      |                       | 150           |       |
| Maximum repetitive forward current               | $I_{FRM}$      |                       | 60            |       |
| Maximum power dissipation                        | $P_D$          | $T_C = 25\text{ °C}$  | 74            | W     |
|  |                | $T_C = 100\text{ °C}$ | 29            |       |
| Operating junction and storage temperature range | $T_J, T_{Stg}$ |                       | - 55 to + 150 | °C    |

| ELECTRICAL SPECIFICATIONS (T <sub>J</sub> = 25 °C unless otherwise specified) |                 |  |            |      |      |            |
|---|-----------------|--|------------|------|------|------------|
| PARAMETER   | SYMBOL          | TEST CONDITIONS  |            | MIN. | TYP. | MAX. UNITS |
| Cathode to anode breakdown voltage  | V <sub>BR</sub> | I <sub>R</sub> = 100 µA  |            | 600  | -    | - V        |
| Maximum forward voltage   | V <sub>FM</sub> | I <sub>F</sub> = 15 A  | See fig. 1 | -    | 1.3  | 1.7        |
|   |                 | I <sub>F</sub> = 30 A  |            | -    | 1.5  | 2.0        |
|   |                 | I <sub>F</sub> = 15 A, T <sub>J</sub> = 125 °C                       |            | -    | 1.2  | 1.6        |
| Maximum reverse leakage current   | I <sub>RM</sub> | V <sub>R</sub> = V <sub>R</sub> rated                                | See fig. 2 | -    | 1.0  | 10         |
|   |                 | T <sub>J</sub> = 125 °C, V <sub>R</sub> = 0.8 x V <sub>R</sub> rated |            | -    | 400  | 1000 µA    |
| Junction capacitance  | C <sub>T</sub>  | V <sub>R</sub> = 200 V   | See fig. 3 | -    | 25   | 50 pF      |
| Series inductance   | L <sub>S</sub>  | Measured lead to lead 5 mm from package body                         |            | -    | 8.0  | - nH       |

| DYNAMIC RECOVERY CHARACTERISTICS (T <sub>J</sub> = 25 °C unless otherwise specified) |                           |   |   |      |      |            |
|--|---------------------------|---|---|------|------|------------|
| PARAMETER  | SYMBOL                    | TEST CONDITIONS   |   | MIN. | TYP. | MAX. UNITS |
| Reverse recovery time<br>See fig. 5  | t <sub>rr</sub>           | I <sub>F</sub> = 1.0 A, dI <sub>F</sub> /dt = 200 A/µs, V <sub>R</sub> = 30 V |   | -    | 19   | -          |
|  | t <sub>rr1</sub>          | T <sub>J</sub> = 25 °C  | I <sub>F</sub> = 15 A<br>dI <sub>F</sub> /dt = 200 A/µs<br>V <sub>R</sub> = 200 V | -    | 42   | 60 ns      |
|  | t <sub>rr2</sub>          | T <sub>J</sub> = 125 °C   |   | -    | 74   | 120        |
| Peak recovery current<br>See fig. 6  | I <sub>RRM1</sub>         | T <sub>J</sub> = 25 °C  |   | -    | 4.0  | 6.0 A      |
|  | I <sub>RRM2</sub>         | T <sub>J</sub> = 125 °C   |   | -    | 6.5  | 10         |
| Reverse recovery charge<br>See fig. 7  | Q <sub>rr1</sub>          | T <sub>J</sub> = 25 °C  |   | -    | 84   | 180 nC     |
|  | Q <sub>rr2</sub>          | T <sub>J</sub> = 125 °C   |   | -    | 241  | 600        |
| Peak rate of fall of recovery<br>current during t <sub>b</sub><br>See fig. 8         | dI <sub>(rec)M</sub> /dt1 | T <sub>J</sub> = 25 °C  |   | -    | 188  | - A/µs     |
|  | dI <sub>(rec)M</sub> /dt2 | T <sub>J</sub> = 125 °C   |   | -    | 160  | -          |

| THERMAL - MECHANICAL SPECIFICATIONS     |                   |  |              |      |            |                        |
|---|-------------------|--|--------------|------|------------|------------------------|
| PARAMETER                               | SYMBOL            | TEST CONDITIONS                            | MIN.         | TYP. | MAX.       | UNITS                  |
| Lead temperature                        | T <sub>lead</sub> | 0.063" from case (1.6 mm) for 10 s         | -            | -    | 300        | °C                     |
| Thermal resistance, junction to case    | R <sub>thJC</sub> |  | -            | -    | 1.7        | K/W                    |
| Thermal resistance, junction to ambient | R <sub>thJA</sub> | Typical socket mount                       | -            | -    | 80         |                        |
| Thermal resistance, case to heatsink    | R <sub>thCS</sub> | Mounting surface, flat, smooth and gerased | -            | 0.5  | -          |                        |
| Weight                                  |                   |  | -            | 2.0  | -          | g                      |
|   |                   |  | -            | 0.07 | -          | oz.                    |
| Mounting torque                         |                   |  | 6.0<br>(5.0) | -    | 12<br>(10) | kgf · cm<br>(lbf · in) |
| Marking device                          |                   | Case style TO-220AC                        | HFA15TB60    |      |            |                        |
|   |                   | Case style TO-262                          | HFA15TB60-1  |      |            |                        |




Fig. 1 - Maximum Forward Voltage Drop vs. Instantaneous Forward Current




Fig. 2 - Typical Reverse Current vs. Reverse Voltage




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage




Fig. 4 - Maximum Thermal Impedance  $Z_{thJC}$  Characteristics




Fig. 5 - Typical Reverse Recovery Time vs.  $dI_F/dt$




Fig. 7 - Typical Stored Charge vs.  $dI_F/dt$




Fig. 6 - Typical Recovery Current vs.  $dI_F/dt$




Fig. 8 - Typical  $dI_{(rec)M}/dt$  vs.  $dI_F/dt$




Fig. 9 - Reverse Recovery Parameter Test Circuit




Fig. 10 - Reverse Recovery Waveform and Definitions

| LINKS TO RELATED DOCUMENTS |   |
|----------------------------|---|
| Dimensions                 | <a href="http://www.vishay.com/doc?95261">http://www.vishay.com/doc?95261</a> |
| Part marking information   | <a href="http://www.vishay.com/doc?95262">http://www.vishay.com/doc?95262</a> |



### Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.