


SabreLite™ 2000 Zone 1 Flashlight



Yellow Gray

SabreLite™ 2000 Zone 1 Flashlight SPECIFICATIONS

Length	Light Source	Tested Lumen Value	Tested Lux Value (@ 1 meter)
19.8 cm (7.79")	Xenon	33.00	10,000

Batteries	Battery Burn Time	Battery Pack Charging Time
3 C Alkaline (Not included)	5 hrs.	N/A

Voltage	Weight w/Batteries	Weight w/o Batteries
4.5	0.36 kg (12.8 oz.)	0.15 kg (5.31 oz.)

Same features as the SabreLite™ 2000 with static-dissipation materials body. SabreLite™ 2000Z1 is ATEX certified safe for use in hazardous Zone 1 (Category 2) locations, and is perfect for professionals who work in areas with high risk of explosion such as chemical, pharmaceutical, power, oil and gas, and fire rescue.

Materials

Body	Lens	Shroud	Switch Type
EXL	Polycarbonate	Xenoy	Twist On/Off Lens Shroud

Clip	Contact, Spring & Retainer	O-Ring	Night Vision Film
ABS	Stainless Steel	Ethylene Propylene	N/A

Configuration

Cat. #	Description
2000Z1	SabreLite™ 2000Z1

SabreLite™ 2000 Zone 1 Flashlight Accessories

Cat. #	Description
2004Z1	SabreLite^a 2000 Zone 1 Lamp Module

Approvals

- II 2G Ex e ib IIC T4 (Energizer), 150°C (Panasonic Plus, Duracell)
 Certificate: ITS09ATEX26181X