

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION , 19 .

© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.


LOC				DIST				P				F				ZONE				LTR				REVISED & REDRAWN PER 0720-0303-93				DATE				APPRO			
6				14																								8-30-93				gph BB			

REVISIONS

DESCRIPTION

DATE


APPRO



METRIC

DIMENSIONS LISTED IN mm [INCHES]

- NOTE:
1. WIRE INSULATION DIA "A" 6.48[.255] MAX
 2. WIRE INSULATION DIA "B" 8.51[.335] MAX



55.14 [2.171]
53.19 [2.094]

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C		DO NOT SCALE PRINT. UNLESS SPECIFIED TOLERANCES ON: 2 PLG DEC # 0.20(.008) 3 PLG DEC # - ANGLES # -		DR 8-30-93 S.S. GULLEN		QTY 100		LOOSE PC		324658					
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 600 V MAX		CIRCUULAR MIL AREA: 6.64-10.54mm² (13,100-20,800)		MATERIAL COPPER PER ASTM B-152 MILON, COLOR RED		FINISH TIN PLATE PER MIL-T-10727		PACKAGE TYPE		PART NO			
FOR APPLICATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		STRANDED		PRODUCT SPEC		NAME		SPLICE, BUTT, SINGLE TO MULTIPLE, TERMINAL, WIRE SIZE: 8 AWG		SIZE		CAGE CODE		DRAWING NO	
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE COMPANY HAS NO RESPONSIBILITY FOR REVISIONS OR CORRECTIONS FOR THE CURRENT EDITION.		APPLICATION SPEC		WEIGHT		SCALE		B		00779		C-324658	

AMP 1400-15 REV 3-92

10 JAN 1994 15:04:32 AMP10744 <UJ128A>DEPT1132>AMP10744>U. TERMINAL-SPLICE-CUST

CUSTOMER DRAWING