

more than you expect



Design Kit for Swift™ Regulator

more than you expect



SMT Power-Chokes for Swift™ Regulators

744 312 025 L: 0.25 µH RDC: 2.10 mΩ I: 16.0 A	744 550 22 L: 2.20 µH RDC: 0.07 Ω I: 2.3 A	744 560 25 L: 2.5 µH RDC: 0.012 Ω I: 5.5 A	744 561 22 L: 22.0 µH RDC: 0.095 Ω I: 2.0 A	744 571 0 L: 10.0 µH RDC: 17.2 mΩ I: 6.5 A	744 572 0 L: 100.0 µH RDC: 168.0 mΩ I: 2.0 A	744 770 06 L: 6.1 µH RDC: 17.6 mΩ I: 6.6 A
744 315 067 L: 0.67 µH RDC: 1.45 mΩ I: 30.0 A	744 550 33 L: 3.30 µH RDC: 0.08 Ω I: 2.0 A	744 560 33 L: 3.3 µH RDC: 0.015 Ω I: 5.0 A	744 570 33 L: 3.3 µH RDC: 7.8 mΩ I: 9.0 A	744 571 22 L: 22.0 µH RDC: 39.4 mΩ I: 4.0 A	744 770 01 L: 1.2 µH RDC: 7.0 mΩ I: 9.8 A	744 770 07 L: 7.6 µH RDC: 20.0 mΩ I: 5.9 A
744 315 120 L: 1.20 µH RDC: 2.90 mΩ I: 22.0 A	744 551 0 L: 10.0 µH RDC: 0.16 Ω I: 1.1 A	744 560 47 L: 4.7 µH RDC: 0.019 Ω I: 4.5 A	744 570 47 L: 4.7 µH RDC: 8.8 mΩ I: 8.5 A	744 571 33 L: 33.0 µH RDC: 58.4 mΩ I: 3.4 A	744 770 02 L: 2.4 µH RDC: 11.5 mΩ I: 8.0 A	744 770 10 L: 10.0 µH RDC: 21.6 mΩ I: 5.4 A
744 318 180 L: 1.8 µH RDC: 3.5 mΩ I: 20.0 A	744 551 15 L: 15.0 µH RDC: 0.23 Ω I: 0.9 A	744 560 68 L: 6.8 µH RDC: 0.034 Ω I: 3.4 A	744 570 56 L: 5.6 µH RDC: 12.4 mΩ I: 7.8 A	744 571 47 L: 47.0 µH RDC: 91.2 mΩ I: 2.8 A	744 770 03 L: 3.5 µH RDC: 13.5 mΩ I: 7.5 A	744 770 115 L: 15.0 µH RDC: 27.0 mΩ I: 4.5 A
744 318 270 L: 2.70 µH RDC: 4.30 mΩ I: 16.0 A	744 551 22 L: 22.0 µH RDC: 0.37 Ω I: 0.7 A	744 561 0 L: 10.0 µH RDC: 0.045 Ω I: 2.9 A	744 570 68 L: 6.8 µH RDC: 14.2 mΩ I: 7.5 A	744 571 68 L: 68.0 µH RDC: 112.0 mΩ I: 2.4 A	744 770 04 L: 4.7 µH RDC: 15.8 mΩ I: 6.8 A	744 771 215 L: 150.0 µH RDC: 246.0 mΩ I: 1.0 A

Würth Elektronik eiSos GmbH & Co. KG
EMC & Inductive Solutions
 Max-Eyth Str. 1
 D-74638 Waldenburg
 Tel. +49 (0) 79 42 945-0
 Fax +49 (0) 79 42 945-400
 eiSos@we-online.de



Get more Info's on Texas Instruments Power
 Management Devices @ www.ti.com/sc/power-w

Please check datasheets on
www.we-online.com for Specifications.
 © 2002
 Würth Elektronik eiSos GmbH & Co. KG
 EMC & Inductive Solutions

www.we-online.com