

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		G	REVISED PER ECR-13-008204	10DEC2013	KH	TM

D

C

B



A

D



C

B

A



- 1 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN-LEAD IN TIN-LEAD PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 2 WIRE RANGE: 0.5-2mm² [20-14 AWG]. INSULATION RANGE: 3.30-5.08 [.130-.200] DIA.
- 3 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 4 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN IN TIN PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 5 SUPERSEDED BY 1-770248-0



5	GOLD	4	0.30	[.012]	BRASS	1-770248-0
	GOLD	1	0.30	[.012]	BRASS	-770248-2-
	PRE-TIN		0.30	[.012]	BRASS	770248-1
	FINISH				MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	21MAY03	TE Connectivity		
			CHK	21MAY03			
			APVD	21MAY03			
			PRODUCT SPEC				
DIMENSIONS: mm [INCHES]			TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
			0 PLC	± -	PIN, LOOSE PIECE, UNIVERSAL MATE-N-LOK(TM) II		
			1 PLC	± -			
			2 PLC	± -			
			3 PLC	± -			
MATERIAL			4 PLC	± -	SIZE		
SEE TABLE			FINISH	SEE TABLE	CAGE CODE		
					DRAWING NO		
					RESTRICTED TO		
					A2 00779 C=770248		
					CUSTOMER DRAWING		
					SCALE 4:1 SHEET 1 of 1 REV G		