


Glass Passivated General Purpose Plastic Rectifier



FEATURES

- Power pack
- Glass passivated chip junction
- Low forward voltage drop
- High forward surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 245 °C (for TO-263AB package)
- Solder dip 275 °C max. 10 s, per JESD 22-B106 (for TO-220AC and ITO-220AC package)
- AEC-Q101 qualified
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

TYPICAL APPLICATIONS

For use in general purpose rectification of power supplies, inverters, converters and freewheeling diodes application.

MECHANICAL DATA

Case: TO-220AC, ITO-220AC, TO-263AB
Molding compound meets UL 94 V-0 flammability rating
Base P/N-E3 - RoHS-compliant, commercial grade
Base P/NHE3 - RoHS-compliant, AEC-Q101 qualified
Terminals: Matte tin plated leads, solderable per J-STD-002 and JESD 22-B102
E3 suffix meets JESD 201 class 1A whisker test, HE3 suffix meets JESD 201 class 2 whisker test

Polarity: As marked

Mounting Torque: 10 in-lbs maximum

PRIMARY CHARACTERISTICS

$I_{F(AV)}$	8.0 A
V_{RRM}	50 V to 1000 V
I_{FSM}	125 A
V_F	1.1 V
$T_J \text{ max.}$	150 °C
Package	TO-220AC, ITO-220AC, TO-263AB
Diode variation	Single

MAXIMUM RATINGS ($T_A = 25 \text{ °C}$ unless otherwise noted)

PARAMETER	SYMBOL	NS8AT	NS8BT	NS8DT	NS8GT	NS8JT	NS8KT	NS8MT	UNIT
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V_{DC}	50	100	200	400	600	800	1000	V
Maximum average forward rectified current at $T_C = 100 \text{ °C}$	$I_{F(AV)}$	8.0							A
Peak forward surge current 8.3 ms single sine-wave superimposed on rated load	I_{FSM}	125							A
Operating junction and storage temperature range	T_J, T_{STG}	- 55 to + 150							°C
Isolation voltage (ITO-220AC only) from terminal to heatsink $t = 1 \text{ min}$	V_{AC}	1500							V



ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)											
PARAMETER	TEST CONDITIONS		SYMBOL	NS8AT	NS8BT	NS8DT	NS8GT	NS8JT	NS8KT	NS8MT	UNIT
Maximum instantaneous forward voltage	8.0 A	T _J = 25 °C	V _F ⁽¹⁾	1.1							V
Maximum DC reverse current at rated DC blocking voltage		T _J = 25 °C	I _R	10							μA
		T _J = 100 °C		100							
Typical junction capacitance	4.0 V, 1 MHz		C _J	55							pF

Note

⁽¹⁾ Pulse test: 300 μs pulse width, 1 % duty cycle

THERMAL CHARACTERISTICS ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)					
PARAMETER	SYMBOL	NSXT	NSFXT	NSBXT	UNIT
Typical thermal resistance from junction to case	$R_{\theta JC}$	3.0	5.0	3.0	$^{\circ}\text{C/W}$

ORDERING INFORMATION (Example)					
PACKAGE	PREFERRED P/N	UNIT WEIGHT (g)	PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
TO-220AC	NS8JT-E3/45	1.80	45	50/tube	Tube
ITO-220AC	NSF8JT-E3/45	1.95	45	50/tube	Tube
TO-263AB	NSB8JT-E3/45	1.77	45	50/tube	Tube
TO-263AB	NSB8JT-E3/81	1.77	81	800/reel	Tape and reel
TO-220AC	NS8JT-E3/45 ⁽¹⁾	1.80	45	50/tube	Tube
ITO-220AC	NSF8JT-E3/45 ⁽¹⁾	1.95	45	50/tube	Tube
TO-263AB	NSB8JT-E3/45 ⁽¹⁾	1.77	45	50/tube	Tube
TO-263AB	NSB8JT-E3/81 ⁽¹⁾	1.77	81	800/reel	Tape and reel

Note

⁽¹⁾ AEC-Q101 qualified



RATINGS AND CHARACTERISTICS CURVES ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)




Fig. 1 - Forward Current Derating Curve




Fig. 4 - Typical Reverse Characteristics




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current




Fig. 5 - Typical Junction Capacitance Per Leg








Fig. 3 - Typical Instantaneous Forward Characteristics

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[NS8AT/45](#) [NS8AT-E3/45](#) [NS8ATHE3/45](#) [NS8BT/45](#) [NS8BT-E3/45](#) [NS8BTHE3/45](#) [NS8DT/45](#) [NS8DT-E3/45](#)
[NS8DTHE3/45](#) [NS8GT/45](#) [NS8GT-E3/45](#) [NS8GTHE3/45](#) [NS8JT/45](#) [NS8JT-E3/45](#) [NS8JTHE3/45](#) [NS8KT/45](#)
[NS8KT-E3/45](#) [NS8KTHE3/45](#) [NS8MT/45](#) [NS8MT-E3/45](#) [NS8MTHE3/45](#) [NSB8AT/31](#) [NSB8AT/45](#) [NSB8AT/81](#)
[NSB8AT-E3/31](#) [NSB8AT-E3/45](#) [NSB8AT-E3/81](#) [NSB8BT/81](#) [NSB8BT-E3/31](#) [NSB8BT-E3/45](#) [NSB8BT-E3/81](#)
[NSB8DT/31](#) [NSB8DT/81](#) [NSB8DT-E3/31](#) [NSB8DT-E3/45](#) [NSB8DT-E3/81](#) [NSB8GT/31](#) [NSB8GT/81](#) [NSB8GT-E3/31](#)
[NSB8GT-E3/81](#) [NSB8JT/31](#) [NSB8JT/45](#) [NSB8JT/81](#) [NSB8JT-E3/31](#) [NSB8JT-E3/45](#) [NSB8JT-E3/81](#) [NSB8KT/31](#)
[NSB8KT/81](#) [NSB8KT-E3/31](#) [NSB8KT-E3/45](#) [NSB8KT-E3/81](#) [NSB8MT/81](#) [NSB8MT-E3/45](#) [NSB8MT-E3/81](#)
[NSF8BT-E3/45](#) [NSF8DT-E3/45](#) [NSF8GT-E3/45](#) [NSF8JT-E3/45](#) [NSF8KT/45](#) [NSF8KT-E3/45](#) [NSB8BT/31](#)
[NSB8BT/45](#) [NSB8DT/45](#) [NSB8KT/45](#) [NSB8MT/45](#) [NSF8MT-E3/45](#) [NSB8ATHE3/45](#) [NSB8ATHE3/81](#)
[NSB8BTHE3/45](#) [NSB8BTHE3/81](#) [NSB8DTHE3/45](#) [NSB8DTHE3/81](#) [NSB8GTHE3/45](#) [NSB8GTHE3/81](#)
[NSB8JTHE3/45](#) [NSB8JTHE3/81](#) [NSB8KTHE3/45](#) [NSB8KTHE3/81](#) [NSB8MTHE3/45](#) [NSB8MTHE3/81](#)
[NSF8BTHE3/45](#) [NSF8DTHE3/45](#) [NSF8GTHE3/45](#) [NSF8JTHE3/45](#) [NSF8KTHE3/45](#) [NSF8MTHE3/45](#)