






WAFER: 15% GLASS FILLED POLYESTER
TO UL 94V-0.
COLOUR: BLACK.

PINS: (0.650)/.0255 SQ.
BRASS WIRE.
PLATED AS PER
SHEETS 2 TO 6.



NOTES
2. RECOMMENDED PCB THICKNESS: 1.6MM
3. PRODUCT SPECIFICATION: PS-99020-0001



REVISE PIN DIM
EC NO: S2012-0325
DRWN:SKANG
CHKD:ATSEE
APPR:MLONG
REV
M2

QUALITY SYMBOLS
F_A=0
F_B=0
F_P=0

GENERAL TOLERANCES (UNLESS SPECIFIED)
mm INCH
4 PLACES ± --- ± ---
3 PLACES ± --- ± ---
2 PLACES ± 0.05 ± .002
1 PLACE ± --- ± ---
ANGULAR ± ---°
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS


DIMENSION STYLE
MM ONLY
DRAWN BY DB DATE 16/07/87
CHECKED BY DB DATE 1987/07/16
APPROVED BY DB DATE 1987/07/16
MATERIAL NO.
SEE TABLE
SIZE A3
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SCALE NTS
DESIGN UNITS METRIC
THIRD ANGLE PROJECTION
C-GRID III
DUAL ROW RIGHT
ANGLE HEADER
MOLEX INCORPORATED
SDA-90122
SHEET NO. 1 OF 6

CKT SIZE	DIM. " A "		DIM. " B " ^(+0.20 -0.35 +0.008 -0.014)		CKT SIZE	DIM. " A "		DIM. " B " ^(±0.20 ± .008)	
2X 1	—————		(2.54) .100		2X21	(50.80) 2.000	(53.34) 2.100		
2X 2	(2.54)	.100	(5.08)	.200	2X22	(53.34) 2.100	(55.88)	2.200	
2X 3	(5.08)	.200	(7.62)	.300	2X23	(55.88) 2.200	(58.42)	2.300	
2X 4	(7.62)	.300	(10.16)	.400	2X24	(58.42) 2.300	(60.96)	2.400	
2X 5	(10.16)	.400	(12.70)	.500	2X25	(60.96) 2.400	(63.50)	2.500	
2X 6	(12.70)	.500	(15.24)	.600	2X26	(63.50) 2.500	(66.04)	2.600	
2X 7	(15.24)	.600	(17.78)	.700	2X27	(66.04) 2.600	(68.58)	2.700	
2X 8	(17.78)	.700	(20.32)	.800	2X28	(68.58) 2.700	(71.12)	2.800	
2X 9	(20.32)	.800	(22.86)	.900	2X29	(71.12) 2.800	(73.66)	2.900	
2X10	(22.86)	.900	(25.40)	1.000	2X30	(73.66) 2.900	(76.20)	3.000	
2X11	(25.40)	1.000	(27.94)	1.100	2X31	(76.20) 3.000	(78.74)	3.100	
2X12	(27.94)	1.100	(30.48)	1.200	2X32	(78.74) 3.100	(81.28)	3.200	
2X13	(30.48)	1.200	(33.02)	1.300	2X33	(81.28) 3.200	(83.82)	3.300	
2X14	(33.02)	1.300	(35.56)	1.400	2X34	(83.82) 3.300	(86.36)	3.400	
2X15	(35.56)	1.400	(38.10)	1.500	2X35	(86.36) 3.400	(88.90)	3.500	
2X16	(38.10)	1.500	(40.64)	1.600	2X36	(88.90) 3.500	(91.44)	3.600	
2X17	(40.64)	1.600	(43.18)	1.700	2X37	(91.44) 3.600	(93.98)	3.700	
2X18	(43.18)	1.700	(45.72)	1.800	2X38	(93.98) 3.700	(96.52)	3.800	
2X19	(45.72)	1.800	(48.26)	1.900	2X39	(96.52) 3.800	(99.06)	3.900	
2X20	(48.26)	1.900	(50.80)	2.000	2X40	(99.06) 3.900	(101.60)	4.000	

NOTES

1. FOR ASSY NUMBERS WITH FINISH OPTIONS
AND DIM'S C & D SEE SHEETS 2 TO 6.



	10	9		8		7		6		5		4		3		2		1	
F		CIRCUIT SIZE		PLATING TYPE A PART NO.		PLATING TYPE E PART NO.		PLATING TYPE F PART NO.											
		2 X 1		90122-0121		90122-0761		90122-0921											
		2 X 2		▲ -0122		▲ -0762		▲ -0922											
		2 X 3		-0123		-0763		-0923											
		2 X 4		-0124		-0764		-0924											
		2 X 5		-0125		-0765		-0925											
		2 X 6		-0126		-0766		-0926											
		2 X 7		-0127		-0767		-0927											
		2 X 8		-0128		-0768		-0928											
		2 X 9		-0129		-0769		-0929											
E	DIM C (±0.20) ±.008 (6.75) .266	2 X 10		-0130		-0770		-0930											
		2 X 11		-0131		-0771		-0931											
		2 X 12		-0132		-0772		-0932											
		2 X 13		-0133		-0773		-0933											
		2 X 14		-0134		-0774		-0934											
		2 X 15		-0135		-0775		-0935											
		2 X 16		-0136		-0776		-0936											
		2 X 17		-0137		-0777		-0937											
		2 X 18		-0138		-0778		-0938											
		2 X 19		-0139		-0779		-0939											
D	DIM D (±0.25) ±.010 (2.90) .114	2 X 20		-0140		-0780		-0940											
		2 X 21		-0141		-0781		-0941											
		2 X 22		-0142		-0782		-0942											
		2 X 23		-0143		-0783		-0943											
		2 X 24		-0144		-0784		-0944											
		2 X 25		-0145		-0785		-0945											
		2 X 26		-0146		-0786		-0946											
		2 X 27		-0147		-0787		-0947											
		2 X 28		-0148		-0788		-0948											
		2 X 29		-0149		-0789		-0949											
C		2 X 30		-0150		-0790		-0950											
		2 X 31		-0151		-0791		-0951											
		2 X 32		-0152		-0792		-0952											
		2 X 33		-0153		-0793		-0953											
		2 X 34		-0154		-0794		-0954											
		2 X 35		-0155		-0795		-0955											
		2 X 36		-0156		-0796		-0956											
		2 X 37		-0157		-0797		-0957											
		2 X 38		-0158		-0798		-0958											
		2 X 39		▼ -0159		▼ -0799		▼ -0959											
B		2 X 40		90122-0160		90122-0800		90122-0960											
A	NOTES: FOR PLATING VARIATIONS SEE ENG.STD. SDES-99000-0003.																		
</																			

	10	9	8	7	6	5	4	3	2	1	
F		CIRCUIT SIZE	PLATING TYPE A PART NO.	PLATING TYPE E PART NO.	PLATING TYPE F PART NO.		CIRCUIT SIZE	PLATING TYPE A PART NO.	PLATING TYPE E PART NO.	PLATING TYPE F PART NO.	F
		2 X 1	90122-0041	90122-0681	90122-0841		2 X 1	90122-0081	90122-0721	90122-0881	
		2 X 2	▲ -0042	▲ -0682	▲ -0842		2 X 2	▲ -0082	▲ -0722	▲ -0882	
		2 X 3	-0043	-0683	-0843		2 X 3	-0083	-0723	-0883	
		2 X 4	-0044	-0684	-0844		2 X 4	-0084	-0724	-0884	
		2 X 5	-0045	-0685	-0845		2 X 5	-0085	-0725	-0885	
		2 X 6	-0046	-0686	-0846		2 X 6	-0086	-0726	-0886	
		2 X 7	-0047	-0687	-0847		2 X 7	-0087	-0727	-0887	
		2 X 8	-0048	-0688	-0848		2 X 8	-0088	-0728	-0888	
		2 X 9	-0049	-0689	-0849		2 X 9	-0089	-0729	-0889	
		2 X 10	-0050	-0690	-0850		2 X 10	-0090	-0730	-0890	
		2 X 11	-0051	-0691	-0851		2 X 11	-0091	-0731	-0891	
		2 X 12	-0052	-0692	-0852		2 X 12	-0092	-0732	-0892	
		2 X 13	-0053	-0693	-0853		2 X 13	-0093	-0733	-0893	
		2 X 14	-0054	-0694	-0854		2 X 14	-0094	-0734	-0894	
		2 X 15	-0055	-0695	-0855		2 X 15	-0095	-0735	-0895	
		2 X 16	-0056	-0696	-0856		2 X 16	-0096	-0736	-0896	
		2 X 17	-0057	-0697	-0857		2 X 17	-0097	-0737	-0897	
		2 X 18	-0058	-0698	-0858		2 X 18	-0098	-0738	-0898	
		2 X 19	-0059	-0699	-0859		2 X 19	-0099	-0739	-0899	
		2 X 20	-0060	-0700	-0860		2 X 20	-0100	-0740	-0900	
		2 X 21	-0061	-0701	-0861		2 X 21	-0101	-0741	-0901	
		2 X 22	-0062	-0702	-0862		2 X 22	-0102	-0742	-0902	
		2 X 23	-0063	-0703	-0863		2 X 23	-0103	-0743	-0903	
		2 X 24	-0064	-0704	-0864		2 X 24	-0104	-0744	-0904	
		2 X 25	-0065	-0705	-0865		2 X 25	-0105	-0745	-0905	
		2 X 26	-0066	-0706	-0866		2 X 26	-0106	-0746	-0906	
		2 X 27	-0067	-0707	-0867		2 X 27	-0107	-0747	-0907	
		2 X 28	-0068	-0708	-0868		2 X 28	-0108	-0748	-0908	
		2 X 29	-0069	-0709	-0869		2 X 29	-0109	-0749	-0909	
		2 X 30	-0070	-0710	-0870		2 X 30	-0110	-0750	-0910	
		2 X 31	-0071	-0711	-0871		2 X 31	-0111	-0751	-0911	
		2 X 32	-0072	-0712	-0872		2 X 32	-0112	-0752	-0912	
		2 X 33	-0073	-0713	-0873		2 X 33	-0113	-0753	-0913	
		2 X 34	-0074	-0714	-0874		2 X 34	-0114	-0754	-0914	
		2 X 35	-0075	-0715	-0875		2 X 35	-0115	-0755	-0915	
		2 X 36	-0076	-0716	-0876		2 X 36	-0116	-0756	-0916	
		2 X 37	-0077	-0717	-0877		2 X 37	-0117	-0757	-0917	
		2 X 38	-0078	-0718	-0878		2 X 38	-0118	-0758	-0918	
		2 X 39	▼ -0079	▼ -0719	▼ -0879		2 X 39	▼ -0119	▼ -0759	▼ -0919	
		2 X 40	90122-0080	90122-0720	90122-0880		2 X 40	90122-0120	90122-0760	90122-0920	
E		DIM C (± 0.20) $\pm .008$ (5.75) .226					DIM C (± 0.20) $\pm .008$ (5.75) .226				E
D		DIM D (± 0.25) $\pm .010$ (2.90) .114					DIM D (± 0.25) $\pm .010$ (4.50) .177				D
C											C
B											B

NOTES:
FOR PLATING VARIATIONS SEE
ENG.STD. SDES-99000-0003.

REVISE PIN DIM EC NO: S2012-0325 2011/10/21 DRWN:SKANG CHKD:ATSEE 2011/10/31 APPR:MLONG 2011/10/31			DESCRIPTION	QUALITY SYMBOLS FA=0 FE=0 FP=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		mm			INCH	DRAWN BY		DATE		TITLE C-GRID III DUAL ROW RIGHT ANGLE HEADER			
4 PLACES		± ---			± ---	DB		16/07/87					
3 PLACES		± ---			± ---	CHECKED BY		DATE		MOLEX INCORPORATED			
2 PLACES		± 0.05			± .002	DB		1987/07/16					
1 PLACE		± ---			± ---	APPROVED BY		DATE		SDA-90122			
		ANGULAR ± ---°			DB		1987/07/16						
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		3 OF 6			
M2		REV		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

	10		9		8		7		6		5		4		3		2		1		
F	CIRCUIT SIZE		PLATING TYPE A PART NO.		PLATING TYPE E PART NO.		PLATING TYPE F PART NO.													F	
		2 X 1	90122-0161		90122-0801		90122-0961														
		2 X 2	▲ -0162	▲	-0802	▲	-0962														
		2 X 3	-0163		-0803		-0963														
		2 X 4	-0164		-0804		-0964														
		2 X 5	-0165		-0805		-0965														
		2 X 6	-0166		-0806		-0966														
		2 X 7	-0167		-0807		-0967														
		2 X 8	-0168		-0808		-0968														
		2 X 9	-0169		-0809		-0969														
		2 X 10	-0170		-0810		-0970														
		2 X 11	-0171		-0811		-0971														
		2 X 12	-0172		-0812		-0972														
		2 X 13	-0173		-0813		-0973														
		2 X 14	-0174		-0814		-0974														
		E	DIM C (±0.20) ±.008 (6.75) .266	2 X 15	-0175		-0815		-0975												
2 X 16	-0176				-0816		-0976														
2 X 17	-0177				-0817		-0977														
2 X 18	-0178				-0818		-0978														
2 X 19	-0179				-0819		-0979														
2 X 20	-0180				-0820		-0980														
2 X 21	-0181				-0821		-0981														
2 X 22	-0182				-0822		-0982														
2 X 23	-0183				-0823		-0983														
2 X 24	-0184				-0824		-0984														
2 X 25	-0185				-0825		-0985														
2 X 26	-0186				-0826		-0986														
2 X 27	-0187				-0827		-0987														
2 X 28	-0188				-0828		-0988														
2 X 29	-0189				-0829		-0989														
D	DIM D (±0.25) ±.010 (4.50) .177			2 X 30	-0190		-0830		-0990												
		2 X 31	-0191		-0831		-0991														
		2 X 32	-0192		-0832		-0992														
		2 X 33	-0193		-0833		-0993														
		2 X 34	-0194		-0834		-0994														
		2 X 35	-0195		-0835		-0995														
		2 X 36	-0196		-0836		-0996														
		2 X 37	-0197		-0837		-0997														
		2 X 38	-0198		-0838		-0998														
		2 X 39	▼ -0199	▼	-0839	▼	-0999														
		2 X 40	90122-0200		90122-0840		90122-1000														
		C																			C
B																			B		
A																			A		
NOTES: FOR PLATING VARIATIONS SEE ENG.STD. SDES-99000-0003.		REVISE PIN DIM EC NO: S2012-0325 2011/10/24 DRWN:SKANG CHKD:ATSEE 2011/10/31 APPR:MLONG 2011/10/31			QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		C-GRID III DUAL ROW RIGHT ANGLE HEADER MOLEX INCORPORATED SDA-90122 4 OF 6								
							mm	INCH	DRAWN BY DB	DATE 16/07/87	TITLE										
							4 PLACES	±---	±---	CHECKED BY	DATE										
							3 PLACES	±---	±---	DB	1987/07/16										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		ANGULAR ±---°		APPROVED BY DB	DATE 1987/07/16	MATERIAL NO.		DOCUMENT NO.	SHEET NO.												
		SEE TABLE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
		SIZE A3																			

fb_frame_A3_P_AM.T
Rev. F 2009/06/18

986

9

8

7

6

5

4

3

2

1

	10		9		8		7		6		5		4		3		2		1				
F			CIRCUIT SIZE		PLATING TYPE B PART NO.		PLATING TYPE C PART NO.		PLATING TYPE D PART NO.		PLATING TYPE G PART NO.			CIRCUIT SIZE		PLATING TYPE B PART NO.		PLATING TYPE C PART NO.		PLATING TYPE D PART NO.		PLATING TYPE G PART NO.	F
			2 X 1		90122-0281		90122-0441		90122-0601		90122-1081			2 X 1		90122-0201		90122-0361		90122-0521		90122-1001	
			2 X 2		▲ -0282		▲ -0442		▲ -0602		▲ -1082			2 X 2		▲ -0202		▲ -0362		▲ -0522		▲ -1002	
			2 X 3		-0283		-0443		-0603		-1083			2 X 3		-0203		-0363		-0523		-1003	
			2 X 4		-0284		-0444		-0604		-1084			2 X 4		-0204		-0364		-0524		-1004	
			2 X 5		-0285		-0445		-0605		-1085			2 X 5		-0205		-0365		-0525		-1005	
			2 X 6		-0286		-0446		-0606		-1086			2 X 6		-0206		-0366		-0526		-1006	
			2 X 7		-0287		-0447		-0607		-1087			2 X 7		-0207		-0367		-0527		-1007	
			2 X 8		-0288		-0448		-0608		-1088			2 X 8		-0208		-0368		-0528		-1008	
			2 X 9		-0289		-0449		-0609		-1089			2 X 9		-0209		-0369		-0529		-1009	
			2 X 10		-0290		-0450		-0610		-1090			2 X 10		-0210		-0370		-0530		-1010	
			2 X 11		-0291		-0451		-0611		-1091			2 X 11		-0211		-0371		-0531		-1011	
			2 X 12		-0292		-0452		-0612		-1092			2 X 12		-0212		-0372		-0532		-1012	
			2 X 13		-0293		-0453		-0613		-1093			2 X 13		-0213		-0373		-0533		-1013	
			2 X 14		-0294		-0454		-0614		-1094			2 X 14		-0214		-0374		-0534		-1014	
			2 X 15		-0295		-0455		-0615		-1095			2 X 15		-0215		-0375		-0535		-1015	
			2 X 16		-0296		-0456		-0616		-1096			2 X 16		-0216		-0376		-0536		-1016	
			2 X 17		-0297		-0457		-0617		-1097			2 X 17		-0217		-0377		-0537		-1017	
			2 X 18		-0298		-0458		-0618		-1098			2 X 18		-0218		-0378		-0538		-1018	
			2 X 19		-0299		-0459		-0619		-1099			2 X 19		-0219		-0379		-0539		-1019	
			2 X 20		-0300		-0460		-0620		-1100			2 X 20		-0220		-0380		-0540		-1020	
			2 X 21		-0301		-0461		-0621		-1101			2 X 21		-0221		-0381		-0541		-1021	
			2 X 22		-0302		-0462		-0622		-1102			2 X 22		-0222		-0382		-0542		-1022	
			2 X 23		-0303		-0463		-0623		-1103			2 X 23		-0223		-0383		-0543		-1023	
			2 X 24		-0304		-0464		-0624		-1104			2 X 24		-0224		-0384		-0544		-1024	
			2 X 25		-0305		-0465		-0625		-1105			2 X 25		-0225		-0385		-0545		-1025	
			2 X 26		-0306		-0466		-0626		-1106			2 X 26		-0226		-0386		-0546		-1026	
			2 X 27		-0307		-0467		-0627		-1107			2 X 27		-0227		-0387		-0547		-1027	
			2 X 28		-0308		-0468		-0628		-1108			2 X 28		-0228		-0388		-0548		-1028	
			2 X 29		-0309		-0469		-0629		-1109			2 X 29		-0229		-0389		-0549		-1029	
			2 X 30		-0310		-0470		-0630		-1110			2 X 30		-0230		-0390		-0550		-1030	
			2 X 31		-0311		-0471		-0631		-1111			2 X 31		-0231		-0391		-0551		-1031	
			2 X 32		-0312		-0472		-0632		-1112			2 X 32		-0232		-0392		-0552		-1032	
			2 X 33		-0313		-0473		-0633		-1113			2 X 33		-0233		-0393		-0553		-1033	
			2 X 34		-0314		-0474		-0634		-1114			2 X 34		-0234		-0394		-0554		-1034	
			2 X 35		-0315		-0475		-0635		-1115			2 X 35		-0235		-0395		-0555		-1035	
			2 X 36		-0316		-0476		-0636		-1116			2 X 36		-0236		-0396		-0556		-1036	
			2 X 37		-0317		-0477		-0637		-1117			2 X 37		-0237		-0397		-0557		-1037	
			2 X 38		-0318		-0478		-0638		-1118			2 X 38		-0238		-0398		-0558		-1038	
			2 X 39		▼ -0319		▼ -0479		▼ -0639		▼ -1119			2 X 39		▼ -0239		▼ -0399		▼ -0559		▼ -1039	
			2 X 40		90122-0320		90122-0480		90122-0640		90122-1120			2 X 40		90122-0240		90122-0400		90122-0560		90122-1040	

DIM
C (± 0.20)
 $\pm .008$
(6.75)
.266

DIM
D (± 0.25)
 $\pm .010$
(2.90)
.114

DIM
C (± 0.20)
 $\pm .008$
(5.75)
.226

DIM
D (± 0.25)
 $\pm .010$
(2.90)
.114

NOTES:
FOR PLATING VARIATIONS SEE
ENG.STD. SDES-99000-0003.

REVISE PIN DIM EC NO: S2012-0325 DRWN:SKANG CHKD:ATSEE APPR:MLONG 2011/10/21 2011/10/31 2011/10/31	DESCRIPTION REV	QUALITY SYMBOLS 	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
					DRAWN BY DB	DATE 16/07/87	TITLE C-GRID III DUAL ROW RIGHT ANGLE HEADER					
					CHECKED BY DB	DATE 1987/07/16						
					APPROVED BY DB	DATE 1987/07/16						molex MOLEX INCORPORATED
					ANGULAR ±---°		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SDA-90122		5 OF 6	
							SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

	10		9		8		7		6		5		4		3		2		1		
F			CIRCUIT SIZE		PLATING TYPE B PART NO.		PLATING TYPE C PART NO.		PLATING TYPE D PART NO.		PLATING TYPE G PART NO.		CIRCUIT SIZE		PLATING TYPE B PART NO.		PLATING TYPE C PART NO.		PLATING TYPE D PART NO.		PLATING TYPE G PART NO.
			2 X 1	90122-0241	90122-0401	90122-0561	90122-1041	2 X 1	90122-0321	90122-0481	90122-0641	90122-1121									
E	DIM C ^{(±0.20) ±.008} (5.75) .226		2 X 2	▲	-0242	▲	-0402	▲	-0562	▲	-1042	2 X 2	▲	-0322	▲	-0482	▲	-0642	▲	-1122	
			2 X 3		-0243		-0403		-0563		-1043	2 X 3		-0323		-0483		-0643		-1123	
			2 X 4		-0244		-0404		-0564		-1044	2 X 4		-0324		-0484		-0644		-1124	
			2 X 5		-0245		-0405		-0565		-1045	2 X 5		-0325		-0485		-0645		-1125	
			2 X 6		-0246		-0406		-0566		-1046	2 X 6		-0326		-0486		-0646		-1126	
			2 X 7		-0247		-0407		-0567		-1047	2 X 7		-0327		-0487		-0647		-1127	
			2 X 8		-0248		-0408		-0568		-1048	2 X 8		-0328		-0488		-0648		-1128	
			2 X 9		-0249		-0409		-0569		-1049	2 X 9		-0329		-0489		-0649		-1129	
			2 X 10		-0250		-0410		-0570		-1050	2 X 10		-0330		-0490		-0650		-1130	
			2 X 11		-0251		-0411		-0571		-1051	2 X 11		-0331		-0491		-0651		-1131	
			2 X 12		-0252		-0412		-0572		-1052	2 X 12		-0332		-0492		-0652		-1132	
			2 X 13		-0253		-0413		-0573		-1053	2 X 13		-0333		-0493		-0653		-1133	
			2 X 14		-0254		-0414		-0574		-1054	2 X 14		-0334		-0494		-0654		-1134	
			2 X 15		-0255		-0415		-0575		-1055	2 X 15		-0335		-0495		-0655		-1135	
			2 X 16		-0256		-0416		-0576		-1056	2 X 16		-0336		-0496		-0656		-1136	
			2 X 17		-0257		-0417		-0577		-1057	2 X 17		-0337		-0497		-0657		-1137	
D	DIM D ^{(±0.25) ±.010} (4.50) .177		2 X 18		-0258		-0418		-0578		-1058	2 X 18		-0338		-0498		-0658		-1138	
			2 X 19		-0259		-0419		-0579		-1059	2 X 19		-0339		-0499		-0659		-1139	
			2 X 20		-0260		-0420		-0580		-1060	2 X 20		-0340		-0500		-0660		-1140	
			2 X 21		-0261		-0421		-0581		-1061	2 X 21		-0341		-0501		-0661		-1141	
			2 X 22		-0262		-0422		-0582		-1062	2 X 22		-0342		-0502		-0662		-1142	
			2 X 23		-0263		-0423		-0583		-1063	2 X 23		-0343		-0503		-0663		-1143	
			2 X 24		-0264		-0424		-0584		-1064	2 X 24		-0344		-0504		-0664		-1144	
			2 X 25		-0265		-0425		-0585		-1065	2 X 25		-0345		-0505		-0665		-1145	
			2 X 26		-0266		-0426		-0586		-1066	2 X 26		-0346		-0506		-0666		-1146	
			2 X 27		-0267		-0427		-0587		-1067	2 X 27		-0347		-0507		-0667		-1147	
			2 X 28		-0268		-0428		-0588		-1068	2 X 28		-0348		-0508		-0668		-1148	
			2 X 29		-0269		-0429		-0589		-1069	2 X 29		-0349		-0509		-0669		-1149	
			2 X 30		-0270		-0430		-0590		-1070	2 X 30		-0350		-0510		-0670		-1150	
			2 X 31		-0271		-0431		-0591		-1071	2 X 31		-0351		-0511		-0671		-1151	
			2 X 32		-0272		-0432		-0592		-1072	2 X 32		-0352		-0512		-0672		-1152	
			2 X 33		-0273		-0433		-0593		-1073	2 X 33		-0353		-0513		-0673		-1153	
C			2 X 34		-0274		-0434		-0594		-1074	2 X 34		-0354		-0514		-0674		-1154	
			2 X 35		-0275		-0435		-0595		-1075	2 X 35		-0355		-0515		-0675		-1155	
			2 X 36		-0276		-0436		-0596		-1076	2 X 36		-0356		-0516		-0676		-1156	
			2 X 37		-0277		-0437		-0597		-1077	2 X 37		-0357		-0517		-0677		-1157	
			2 X 38		-0278		-0438		-0598		-1078	2 X 38		-0358		-0518		-0678		-1158	
			2 X 39	▼	-0279	▼	-0439	▼	-0599	▼	-1079	2 X 39	▼	-0359	▼	-0519	▼	-0679	▼	-1159	
			2 X 40		90122-0280	90122-0440	90122-0600	90122-1080	2 X 40		90122-0360	90122-0520	90122-0680	90122-1160							
			B																		

DIM
C (± 0.20)
 $\pm .008$
(5.75)
.226

DIM
D (± 0.25)
 $\pm .010$
(4.50)
.177

DIM
C (± 0.20)
 $\pm .008$
(6.75)
.266

DIM
D (± 0.25)
 $\pm .010$
(4.50)
.177

NOTES:
FOR PLATING VARIATIONS SEE
ENG.STD. SDES-99000-0003.

REVISE PIN DIM EC NO: S2012-0325 DRWN:SKANG CHKD:ATSEE APPR:MLONG 2011/10/31 2011/10/31 2011/10/31	QUALITY SYMBOLS $F_A=0$ $F_B=0$ $F_P=0$	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY DB	DATE 16/07/87	TITLE C-GRID III DUAL ROW RIGHT ANGLE HEADER MOLEX INCORPORATED SDA-90122 6 OF 6			
		4 PLACES	± ---	± ---	CHECKED BY DB	DATE 1987/07/16				
		3 PLACES	± ---	± ---	APPROVED BY DB	DATE 1987/07/16				
			2 PLACES	± 0.05	± .002	MATERIAL NO.		DOCUMENT NO.		
	1 PLACE	± ---	± ---	SEE TABLE						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						