

PRODUCT NUMBER
20020002-XXXXXXLF

20020002-



PITCH

G: 5.00 mm
H: 5.08 mm

POLES

02: 2 poles
03: 3 poles
04: 4 poles

24: 24 poles

LF : DENOTED RoHS COMPATIBLE

1 : STANDARD PRODUCT
W/ BOX PACKING

SCREW CODE

CODE	SCREW TYPE	AVAILABILITY
A	-/+	ON REQUEST ONLY
B	-	STANDARD

ALL FLANGE SCREWS ARE ONLY AVAILABLE IN +/- COMBINATION SCREW TYPES.

HOUSING CODE

CODE	COLOR	AVAILABILITY
1	GREEN(RAL 6018/T)	STANDARD
2	BLACK	ON REQUEST ONLY
3	GREY(RAL 7004/P)	ON REQUEST ONLY
4	BLUE(RAL 5015/A)	ON REQUEST ONLY


NOTES:

1. MATERIALS
 - 1-1 HOUSING: THERMALPLASTIC RESIN, UL 94V-0 RATED.
 - 1-2 SCREW: STEEL, ZINC PLATED.
 - 1-3 CLAMP: COPPER ALLOY, NICKEL PLATED.
 - 1-4 TERMINAL: COPPER ALLOY, TIN PLATED.
2. PRODUCT SPECIFICATION REFER TO FCI GS-12-625.
3. PRODUCT PACKING SPECIFICATION REFER TO FCI GS-14-1394.
4. FCI, SAFETY CERTIFICATE LOGO AND SERIES NAME TO BE SHOWN ON PRODUCT SURFACE.
5. THE PRODUCTS WHERE THE PART NUMBER END IN "LF" MEET THE EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

mat'l. code				surface		tolerance		projection	product family	TERMINAL BLOCK
ltr	ecn	no	dr	date	tolerances unless otherwise specified		MM	scale	title	TERMINAL BLOCK
A	T10-0082	WL	080510		angles	± 0.5				
B	T10-0158	WL	100410		$X \pm 0.3$					
C	T-005908	WL	091311		$X' \pm 1^{\circ}$	$X \pm 0.1$				
					dr	WENDY CHEN 051410				
					engr	JASON HSU 051410				
					chr	GARY HSIEH 051410				
					appd	JOSEPH HSIA 051410				
sheet	revision	C	C	C						
index	sheet	1	2	3						






PRODUCT NUMBER	SERIES NAME	PITCH
20020002-GXXXXXXLF	01-500	5.00 mm



N= Number of poles

Dim L	N*5.0 [.197]
Dim B	(N-1)*5.0 [.197]
Dim C	(N+2)*5.0 [.197]
Dim D	(N+1)*5.0 [.197]


Poles	Tolerance
2P-7P	$\pm 0.15 [.006]$
8P-12P	$\pm 0.25 [.010]$
13P-18P	$\pm 0.30 [.012]$
19P-24P	$\pm 0.40 [.016]$



mat'l. code				surface	tolerance	projection	product family
ltr	ecn	no	dr	ASME Y14.5	ASME Y14.5		TERMINAL BLOCK
C				tolerances unless otherwise specified			
				angles $\pm 0.5^\circ$	$X \pm 0.5$	MM	
				$X \pm 0.3^\circ$	$X.X \pm 0.3$	[INCH]	
				$X \pm 1^\circ$	$X.XX \pm 0.1$	scale	
			dr	WENDY CHEN	051410		
			engr	JASON HSU	051410		
			chr	GARY HSIEH	051410		
			appd	JOSEPH HSIA	051410		
sheet	revision						
index	sheet						






PRODUCT NUMBER	SERIES NAME	PITCH
20020002-HXXXXXXLF	01-508	5.08 mm



N= Number of poles

Dim L	$N*5.08[.200]$
Dim B	$(N-1)*5.08[.200]$
Dim C	$(N+2)*5.08[.200]$
Dim D	$(N+1)*5.08[.200]$

Poles	Tolerance
2P-7P	$\pm 0.15[.006]$
8P-12P	$\pm 0.25[.010]$
13P-18P	$\pm 0.30[.012]$
19P-24P	$\pm 0.40[.016]$



mat'l. code				surface	tolerance	projection	product family
ltr	ecn	no	dr	ASME Y14.5	ASME Y14.5		TERMINAL BLOCK
C				tolerances unless otherwise specified			
				angles	$X.0\pm 0.5$		
					$X.X\pm 0.3$	MM	
					$X.XX\pm 0.1$	[INCH]	
			dr	WENDY CHEN	051410		
			engr	JASON HSU	051410		
			chr	GARY HSIEH	051410		
			appd	JOSEPH HSIA	051410		
sheet index		revision sheet					

