



Wiring Components Division

Material & Color Availability Chart

CABLE TIES

Available Styles

- **PAN-TY® Cable Ties** - Clamp Ties, Marker and Flag Ties, Push Mount Ties, Lashing Ties, Releasable Ties
- **SUPER-GRIP® Cable Ties**
- **DOME-TOP® Barb Ty Cable Ties** - Clamp Ties, Marker and Flag Ties, Push Mount Ties, **DURA-TY™** Cable Ties
- **Parallel-Entry Ties** - **CONTOUR-TY™** Cable Ties, **HYPER-V™** In-Line Cable Ties, **BELT-TY™** In-Line Cable Ties, **IN-LINE** Cable Ties, Elastomeric Cable Ties
- **Hook and Loop Cable Ties** - **TAK-TY®** Cable Ties (Cinch Ties, 15' & 75' Rolls, Strip Ties, Loop Ties, UL Listed Strip & Loop Ties), **TAK-TAPE™** Rolls, **TAK-TY®** Stacked Strips, **ULTRA-CINCH™** Cable Ties
- **STA-STRAP® Cable Ties** - Clamp Ties, Marker Ties
- **Specialty Ties** - Cable Marker Strap, Double Hose Clamp, Double Loop, Triple Loop, Locking Stud Mounted, Releasable Stud Mounted Ladder Ties, Bow-Ty, Chassis/Panel Mount Ties

CONTACTS

Customer Service Phone: 800-777-3300 • Fax: 708-532-1811 • Email: info@panduit.com • Website: www.panduit.com

Technical Support Phone: 888-506-5400 • Fax: 708-532-9044

Part Number System for *PAN-TY*® Cable Ties

PLT

2

S

—

C

Type

PLT = Locking Tie
PRT = Releasable Tie
PLC = Locking Clamp
PLF = Locking Flag
PLM = Locking Marker
PLP = Locking Push Mount
PLWP = Locking Wing Push Mount
PRLWP = Releasable Ladder Wing Push Mt.
PRWP = Releasable Wing Push Mount
PLUP = Locking Umbrella Push Mount

Size

Approx.
Maximum
Bundle
Dia. (In)

Cross Section

SM = Subminiature
M = Miniature
I = Intermediate
S = Standard
LH = Light-Heavy
H = Heavy
EH = Extra-Heavy

Screw Hole Size

(Clamp Ties Only)
—S4 = #4 (M2.5)
—S6 = #6 (M3)
—S8 = #8 (M4)
—S10 = #10 (M5)
—S25 = 1/4 (M6)

Package Size

Q = 25
L = 50
C = 100
TL = 250
D = 500
M = 1000
VMR = 2 reels/2500 ea
XMR = 2 reels/5000 ea

Mat'l / Color

See
below

Material and Color Chart

Material	Color	PANDUIT Suffix
Nylon 6.6	Natural	✓
Weather Resistant Nylon 6.6	Black	0
Weather Resistant Nylon 6.6 (meets Mil. Spec.)	Black	00
Nylon 6.6	Brown	1
Nylon 6.6	Red	2
Nylon 6.6	Orange	3
Nylon 6.6	Yellow	4Y
Nylon 6.6	Green	5
Nylon 6.6	Blue	6
Nylon 6.6	Purple	7
Nylon 6.6	Gray	8
Nylon 6.6	White	10
Nylon 6.6	Telephone Gray	14
Nylon 6.6	Black	20
Heat Stabilized Nylon 6.6	Black	30

Material	Color	PANDUIT Suffix
Heat Stabilized Nylon 6.6	Natural	39
Nylon 6.6	Fluorescent Orange	53
Nylon 6.6	Fluorescent Yellow	54
Nylon 6.6	Fluorescent Green	55
Nylon 6.6	Fluorescent Pink	59
Flame Retardant Nylon 6.6	Black	60
Flame Retardant Nylon 6.6	Natural (Ivory)	69
PEEK (Polyetheretherketone)	Translucent Brown	71
TEFZEL [■]	Aqua Blue	76
Metal Detectable	Blue	86
Weather Resistant Polypropylene	Black	100
Polypropylene	Green	109
Nylon 12	Black	120
Heat Stabilized Weather Resistant Nylon 6.6	Black	300
HALAR [▲]	Maroon	702Y

✓ Denotes *PANDUIT* Natural Nylon 6.6 (no suffix).

[■]TEFZEL is a registered trademark of E. I. du Pont de Nemours and Company.

[▲]HALAR is a registered trademark of Solvay Solexis, Inc.

Part Number Availability List

Standard Packaging			Bulk Packaging		
Part Number	Natural Nylon 6.6	Material/Color Suffix	Part Number	Natural Nylon 6.6	Material/Color Suffix
PLC1M-S4-C	✓	0	PLC1M-S4-M	✓	0, 30
PLC1.5I-S8-C	✓	0	PLC1.5I-S8-M	✓	0, 30
PLC2S-S6-C	✓	0	PLC2S-S6-M	✓	0
PLC2S-S10-C	✓	0, 14	PLC2S-S10-M	✓	0, 20, 30
PLC3S-S10-C	✓	0	PLC3S-S10-M	✓	0
PLC4S-S10-C	✓	0	PLC4S-S10-M	✓	0, 30
PLC2H-S25-L	✓		PLC2H-S25-TL	✓	0, 30
PLC4H-S25-L	✓	0	PLC4H-S25-TL	✓	0, 30
PLF1M-C	✓	0	PLF1M-M	✓	0, 2, 3, 4Y, 6, 10, 69
PLF1MA-C	✓	3, 4Y	PLF1MA-M	✓	0, 2, 3, 4Y, 5, 6, 10
PLF1MB-C	✓		PLF1MB-M	✓	
			PLF1MC-M	✓	3
PLM1M-C	✓	0	PLM1M-M	✓	0, 1, 2, 3, 4Y, 5, 6, 7, 8, 10, 69
PLM2M-C	✓		PLM2M-M	✓	0, 4Y, 6
PLM2S-C	✓	0, 4Y	PLM2S-D	✓	0, 2, 3, 4Y, 5, 6, 8
PLM4S-C	✓		PLM4S-D	✓	0, 2, 4Y, 6
PL2M2S-L	✓	0	PL2M2S-D	✓	0, 4Y, 10

Standard Packaging			Bulk Packaging		
Part Number	Natural Nylon 6.6	Material/Color Suffix	Part Number	Natural Nylon 6.6	Material/Color Suffix
PL3M2S-L	✓		PL3M2S-D	✓	0, 4Y
PLP1.5I-C	✓		PLP1.5I-M	✓	0, 30
			PLP1S-M	✓	0, 30
			PLP1.5S-M	✓	
PLP2S-C	✓		PLP2S-M	✓	0, 30
PLT.6SM-C	✓	0	PLT.6SM-M	✓	0, 30
PLT.7M-C	✓		PLT.7M-M	✓	0, 30
PLT1M-C	✓	0, 00, 1, 2, 3, 4Y, 5, 6, 7, 8, 10, 14, 30, 76, 86, 186, 702Y	PLT1M-M	✓	0, 00, 1, 2, 3, 4Y, 5, 6, 7, 8, 10, 14, 20, 30, 53, 54, 55, 59, 60, 69, 76, 100, 109, 300, 702Y
			PLT1M-XMR	✓	0, 1, 2, 3, 4Y, 5, 6, 7, 8, 10, 30
PLT1.5M-C	✓	0	PLT1.5M-M	✓	0, 00, 1, 2, 3, 4Y, 5, 6, 7, 8, 10, 14, 20, 30
			PLT1.5M-XMR	✓	0, 00, 30
PLT2M-C	✓	0	PLT2M-M	✓	0, 1, 2, 3, 4Y, 5, 6, 7, 8, 10, 20, 30, 69
PLT1.5I-C	✓	0, 1, 2, 3, 4Y, 5, 6, 7, 8, 10, 20, 30	PLT1.5I-M	✓	0, 00, 1, 2, 3, 4Y, 5, 6, 7, 8, 10, 20, 30, 69, 100, 109, 120, 300
PLT2I-C	✓	0, 14, 30, 76, 86, 186	PLT2I-M	✓	0, 00, 1, 2, 3, 4Y, 5, 6, 7, 8, 10, 14, 20, 30, 53, 54, 55, 59, 69, 76, 300
PLT2.5I-C	✓	0	PLT2.5I-M	✓	0, 20
PLT3I-C	✓	0, 14	PLT3I-M	✓	0, 2, 3, 4Y, 5, 6, 8, 10, 14, 20, 30
PLT4I-C	✓	0, 14	PLT4I-M	✓	0, 2, 5, 6, 14, 20, 30
PLT1S-C	✓	0	PLT1S-M	✓	0, 30, 38, 300
PLT1.5S-C	✓	0	PLT1.5S-M	✓	0, 30
PLT2S-C	✓	0, 00, 1, 2, 3, 4Y, 5, 6, 7, 8, 10, 20, 30, 71, 76, 86, 186, 702Y	PLT2S-M	✓	0, 00, 1, 2, 3, 4Y, 5, 6, 7, 8, 10, 20, 30, 38, 39, 53, 54, 55, 59, 60, 69, 71, 76, 100, 109, 120, 300, 702Y
			PLT2S-VMR	✓	0, 30
PLT2.5S-C	✓	0	PLT2.5S-M	✓	0, 30
PLT3S-C	✓	0, 00, 2, 20, 30, 76, 86, 186, 702Y	PLT3S-M	✓	0, 00, 1, 2, 3, 4Y, 5, 6, 7, 8, 10, 20, 30, 53, 54, 55, 59, 76, 100, 109, 702Y
			PLT3S-VMR	✓	30
PLT4S-C	✓	0, 00, 2, 3, 4Y, 5, 6, 8, 20, 30, 76, 86, 186	PLT4S-M	✓	0, 00, 1, 2, 3, 4Y, 5, 6, 7, 8, 10, 14, 20, 30, 69, 76, 100, 109, 120, 300
PLT4.5S-C	✓	0	PLT4.5S-M	✓	0
PLT5S-C	✓	0	PLT5S-M	✓	0, 2, 3, 4Y, 5, 6, 8, 30
PLT6LH-L	✓	0	PLT6LH-C	✓	0
PLT7LH-L	✓	0	PLT7LH-C	✓	0, 30
PLT8LH-L	✓	0	PLT8LH-C	✓	0, 120
PLT8LH-Q		0			
PLT9LH-L	✓	0	PLT9LH-C	✓	0, 30
PLT10LH-L	✓		PLT10LH-C	✓	
PLT2H-L	✓	0	PLT2H-TL	✓	0, 2, 4Y, 6, 30, 100, 109, 300
PLT2.5H-L	✓	0	PLT2.5H-TL	✓	0
PLT3H-L	✓	0, 76, 86, 186	PLT3H-TL	✓	0, 30, 76, 100, 109
PLT4H-L	✓	0, 00, 76, 86, 186	PLT4H-TL	✓	0, 00, 1, 2, 3, 4Y, 5, 6, 10, 20, 30, 69, 76, 100, 109, 120, 300
PLT4H-C	✓	0			
PLT5H-L	✓	0	PLT5H-C	✓	0, 30
PLT6H-L	✓	0	PLT6H-C	✓	0, 30
PLT8H-L	✓	0	PLT8H-C	✓	0, 00, 30
PLT8H-L	✓	0			
PLT13H-Q	✓	0	PLT13H-C	✓	0, 3
PLT2EH-Q		0	PLT2EH-C	✓	0
			PLT3EH-NB-C		0
PLT5EH-Q	✓	0	PLT5EH-C	✓	0
			PLT5EH-NB-C		0
PLT6EH-Q	✓	0	PLT6EH-C	✓	0
			PLT6EH-NB-C		0
PLT8EH-Q		0	PLT8EH-C	✓	0
PLT10EH-Q		0	PLT10EH-C	✓	0
PLT12EH-Q		0	PLT12EH-C	✓	0

Standard Packaging			Bulk Packaging		
Part Number	Natural Nylon 6.6	Material/Color Suffix	Part Number	Natural Nylon 6.6	Material/Color Suffix
			PLUP40S-D		30
			PLUP40SE-D	✓	30
PLWP1M-C	✓		PLWP1M-D	✓	0, 30
PLWP1.5I-C	✓		PLWP1.5I-D	✓	30
PLWP1S-C	✓	0	PLWP1S-D	✓	0, 20, 30
			PLWP1SA-D	✓	
			PLWP1SB-D	✓	
			PLWP1.5S-D	✓	30
			PLWP1.5SA-D	✓	
PLWP2S-C	✓	0	PLWP2S-D	✓	0, 30
			PLWP2SA-D	✓	
			PLWP2SB-D	✓	
			PLWP2H-TL	✓	0, 30
			PLWP3H-TL	✓	0
			PLWP30SC-D		30
			PLWP40SC-D		30
			PLWP40SD-D		30
			PLWP50SC-D		30
			PLWP50SE-D		30
			PRLWP30S-D		30
			PRLWP50S-D		30
PRT1S-C	✓	0	PRT1S-M	✓	0
PRT1.5S-C	✓	0	PRT1.5S-M	✓	0, 30
PRT2S-C	✓	0	PRT2S-M	✓	0, 2, 3, 4Y, 6, 7
PRT3S-C	✓	0	PRT3S-M	✓	0
PRT4S-C	✓	0	PRT4S-M	✓	0, 2, 3, 4Y, 6
PRT2H-L	✓	0	PRT2H-TL	✓	0
PRT3H-L	✓	0	PRT3H-TL	✓	0
PRT4H-L	✓	0	PRT4H-TL	✓	0
PRT2EH-Q		0	PRT2EH-C	✓	0, 100
PRT5EH-Q	✓	0	PRT5EH-C	✓	0, 100
PRT6EH-Q	✓	0	PRT6EH-C	✓	0, 100
PRT8EH-Q		0	PRT8EH-C	✓	0, 100
PRT10EH-Q		0	PRT10EH-C	✓	0
PRT12EH-Q		0	PRT12EH-C	✓	0
PRWP1S-C	✓		PRWP1S-D	✓	0
			PRWP1SA-D	✓	
			PRWP1SB-D	✓	
			PRWP1.5S-D	✓	0, 20, 30
			PRWP2S-D	✓	0
			PRWP2H-TL	✓	

Part Number System for *SUPER-GRIP®* Cable Ties

SG	200	S	—	C
<u>Type</u>	<u>Size</u>	<u>Cross Section</u>	<u>Package Size</u>	<u>Material / Color</u>
SG = Locking Tie	Approx. Length (mm)	M = Miniature I = Intermediate S = Standard LH = Light-Heavy H = Heavy	L = 50 C = 100 TL = 250 M = 1000	See below

Material and Color Chart

Material	Color	PANDUIT Suffix
Nylon 6.6	Natural	✓
Weather Resistant Nylon 6.6	Black	0
Heat Stabilized Nylon 6.6	Black	30

✓ Denotes *PANDUIT* Natural Nylon 6.6 (no suffix).

Part Number Availability List

Standard Packaging			Bulk Packaging		
Part Number	Natural Nylon 6.6	Material/Color Suffix	Part Number	Natural Nylon 6.6	Material/Color Suffix
SG100M-C	✓	0	SG100M-M	✓	0
SG150I-C	✓	0	SG150I-M	✓	0
SG200S-C	✓	0	SG200S-M	✓	0, 30
SG250S-C	✓	0			
SG300S-C	✓	0	SG300S-M	✓	0, 30
SG370S-C	✓	0	SG370S-M	✓	0
SG350LH-L	✓	0	SG350LH-TL	✓	0, 30
SG450H-L	✓	0	SG450H-C	✓	0

Part Number System for *DOME-TOP®* Barb Ty & *DURA-TY™* Cable Ties

BT	2	S	—	C	Material / Color
Type	Size	Cross Section	Screw Hole Size (Clamp Ties Only)	Package Size	
BT = Locking Tie	Approx.	M = Miniature	—S4 = #4 (M2.5)	Q = 25	See below
BC = Clamp Tie	Maximum	I = Intermediate	—S6 = #6 (M3)	L = 50	
BF = Flag Tie	Bundle	S = Standard	—S8 = #8 (M4)	C = 100	
BM = Marker Tie	Dia. (In)	LH = Light-Heavy	—S10 = #10 (M5)	TL = 250	
BP = Push Mount Tie		H = Heavy	—S25 = 1/4 (M6)	D = 500	
BW = Wing Push Mount Tie		EH = Extra-Heavy		M = 1000	
DT = Locking Tie				LR = 50' Reel	

Material and Color Chart

Material	Color	PANDUIT Suffix
Nylon 6.6	Natural	✓
Weather Resistant Nylon 6.6	Black	0
Nylon 6.6	Brown	1
Nylon 6.6	Red	2
Nylon 6.6	Orange	3
Nylon 6.6	Yellow	4Y
Nylon 6.6	Green	5
Nylon 6.6	Blue	6
Nylon 6.6	Purple	7

Material	Color	PANDUIT Suffix
Nylon 6.6	Gray	8
Nylon 6.6	White	10
Nylon 6.6	Telephone Gray	14
Nylon 6.6	Black	20
Heat Stabilized Nylon 6.6	Black	30
Heat Stabilized Nylon 6.6	Natural	39
Flame Retardant Nylon 6.6	Natural (Ivory)	69
Weather Resistant Acetal	Black	*
Heat Stabilized Weather Resistant Nylon 6.6	Black	300

✓ Denotes *PANDUIT* Natural Nylon 6.6 (no suffix).

* Denotes *DURA-TY™* Weather Resistant Acetal material (no suffix).

Part Number Availability List

Standard Packaging			Bulk Packaging		
Part Number	Natural Nylon 6.6	Material/Color Suffix	Part Number	Natural Nylon 6.6	Material/Color Suffix
			BC1M-S4-M	✓	0
			BC2M-S4-M	✓	0
			BC1.5I-S8-M	✓	0
BC2S-S10-C	✓	0	BC2S-S10-D	✓	0
			BC3S-S10-D	✓	0
BC4S-S10-C	✓	0	BC4S-S10-D	✓	0, 30
BC4LH-S25-L	✓	0	BC4LH-S25-TL	✓	0
BF1M-C	✓		BF1M-M	✓	0
BF2M-C	✓		BF2M-M	✓	0
BM1M-C	✓		BM1M-M	✓	0
BM2M-C	✓		BM2M-M	✓	0
BM2S-C	✓		BM2S-D	✓	0
BM4S-C	✓		BM4S-D	✓	0
			BP2S-D		0
BT1M-C	✓	0, 30	BT1M-M	✓	0, 1, 2, 3, 4Y, 5, 6, 7, 8, 10, 30, 39, 69, 300
			BT1M-XMR	✓	0, 30
BT1.5M-C	✓	0	BT1.5M-M	✓	0, 30, 69
			BT1.5M-XMR	✓	0, 30, 69
BT2M-C	✓	0	BT2M-M	✓	0, 2, 3, 4Y, 5, 6, 8, 30
BT4M-C	✓	0	BT4M-M	✓	0
BT1.5I-C	✓	0	BT1.5I-M	✓	0, 1, 2, 3, 4Y, 5, 6, 7, 8, 10, 30, 39
BT2I-C	✓	0	BT2I-M	✓	0, 30, 69, 300
BT3I-C	✓	0	BT3I-M	✓	0, 14, 30

Standard Packaging			Bulk Packaging		
Part Number	Natural Nylon 6.6	Material/Color Suffix	Part Number	Natural Nylon 6.6	Material/Color Suffix
BT4I-C	✓	0	BT4I-M	✓	0, 14
BT2S-C	✓	0	BT2S-M	✓	0, 1, 2, 3, 4Y, 5, 6, 7, 8, 10, 20, 30, 39, 69, 300
BT3S-C	✓	0, 2	BT3S-M	✓	0, 30, 39, 69, 300
BT4S-C	✓	0	BT4S-M	✓	0, 2, 3, 4Y, 5, 6, 7, 8, 10, 30, 39, 300
BT2LH-L	✓	0	BT2LH-TL	✓	0, 300
BT3LH-L	✓	0	BT3LH-TL	✓	0
BT4LH-L	✓	0	BT4LH-TL	✓	0, 30, 39, 69, 300
BT5LH-L	✓	0	BT5LH-C	✓	0, 300
BT6LH-L	✓	0	BT6LH-C	✓	0, 69, 300
BT7LH-L	✓	0	BT7LH-C	✓	0
BT8LH-L	✓	0	BT8LH-C	✓	0, 300
BT9LH-L	✓	0	BT9LH-C	✓	0, 300
			BW1.5I-D	✓	
			BW2S-D	✓	0
			B2M2S-D	✓	0
			B3M2S-TL	✓	0
			B4M2S-TL	✓	0
DTHEH-Q0		*			
DTHH-Q0		*			
DTKEH-0		*			
DTKH-0		*			
DTREH-LR0		*			
DTRH-LR0		*			
DT4EH-L0		*			
DT8EH-Q0		*			
DT14EH-L0		*	DT14EH-C0		*
DT15EH-L0		*			
DT28EH-C0		*			
DT44EH-C0		*			

Part Number System for *CONTOUR-TY®* and *BELT-TY™* Cable Ties

CBR	2	S	—	M	
<u>Type</u>	<u>Size</u>	<u>Cross Section</u>		<u>Package Size</u>	<u>Material/Color</u>
CBR = Locking Tie ILT = Locking Tie	Approx. Maximum Bundle Dia. (In)	M = Miniature I = Intermediate S = Standard HS = Heavy-Standard LH = Light-Heavy		C = 100 TL = 250 D = 500 M = 1000	See below

Part Number System for *IN-LINE* and *Hyper-V™* Cable Ties

IT	9	100	—	C	
<u>Type</u>	<u>Width</u>	<u>Size</u>		<u>Package Size</u>	<u>Material/Color</u>
HV = Locking Tie IT = Locking Tie	Approx. Width (mm)	Approx. Max. Bundle Dia. (mm)		C = 100	See below

Part Number System for *Elastomeric* Cable Ties

ERT	2	M	—	C	
<u>Type</u>	<u>Size</u>	<u>Cross Section</u>		<u>Package Size</u>	<u>Material/Color</u>
ERT = Elastomeric Releasable Tie	Approx. Max. Bundle Dia. (In)	M = Miniature		C = 100	See below

Material and Color Chart

Material	Color	PANDUIT Suffix	Material	Color	PANDUIT Suffix
Nylon 6.6	Natural	✓	Nylon 6.6	Ultraviolet Red	UV2
Weather Resistant Nylon 6.6	Black	0	Nylon 6.6	Ultraviolet Bright Red	UV2A
Nylon 6.6	Brown	1	Nylon 6.6	Ultraviolet Yellow	UV4Y
Nylon 6.6	Red	2	Nylon 6.6	Ultraviolet Butterscotch	UV4A
Nylon 6.6	Orange	3	Nylon 6.6	Ultraviolet Green	UV5A
Nylon 6.6	Yellow	4Y	Nylon 6.6	Ultraviolet Hunter Green	UV5B
Nylon 6.6	Green	5	Nylon 6.6	Ultraviolet Dark Blue	UV6
Nylon 6.6	Blue	6	Nylon 6.6	Ultraviolet Light Blue	UV6A
Nylon 6.6	Purple	7	Nylon 6.6	Ultraviolet Cobalt Blue	UV6B
Nylon 6.6	Gray	8	Nylon 6.6	Ultraviolet Purple	UV7A
Nylon 6.6	White	10	Nylon 6.6	Ultraviolet Gray	UV8
TPU	Black	20	Nylon 6.6	Ultraviolet Teal	UV11
Heat Stabilized Nylon 6.6	Black	30	Nylon 6.6	Ultraviolet Magenta	UV16B
Heat Stabilized Nylon 6.6	Natural	39	Nylon 6.6	Ultraviolet Tan	UV18
Flame Retardant Nylon 6.6	Natural (Ivory)	69			

✓ Denotes *PANDUIT* Natural Nylon 6.6 (no suffix).

Part Number Availability List

Standard Packaging			Bulk Packaging		
Part Number	Natural Nylon 6.6	Material/Color Suffix	Part Number	Natural Nylon 6.6	Material/Color Suffix
			CBR1M-M	✓	0, 30
			CBR1.5M-M	✓	0
			CBR2M-M	✓	0, 1, 2, 3, 4Y, 5, 6, 7, 10
			CBR1.5I-M	✓	0, 30
			CBR3I-M	✓	0, 1, 2, 3, 4Y, 5, 6, 7, 8, 10
			CBR4I-M	✓	0
			CBR2S-M	✓	0, 30, 39
			CBR3S-M	✓	0, 30, 69
			CBR4S-M	✓	0, 30
			CBR2HS-D	✓	0
			CBR4LH-TL	✓	0, 30
			CBR6LH-C	✓	0, 30
			ERT2M-C		20
			ERT3M-C		20
			ERT4.5M-C		20
			HV965-C		0
			HV9100-C		0
			HV9150-C		0
			HV9250-C		0
ILT2S-C	✓	0	ILT2S-M	✓	0
ILT3S-C	✓	0	ILT3S-M	✓	0
ILT4S-C	✓	0	ILT4S-M	✓	0
			ILT4LH-TL	✓	0
			ILT6LH-C	✓	0
			IT940-C		0
			IT965-C		0
			IT9100-C		0, UV2,4Y,6,6A,7A,8,16B
			IT9115-C		0, UV2,2A,4Y,4A,5A,5B, 6,6A,6B,7A, 8,11,16B, 18

Part Number System for STA-STRAP® Cable Ties

SST

1

M

—

C

Type

SST = Locking Tie
SSC = Clamp Tie
SSM = Marker Tie

Size

Approx.
Maximum
Bundle
Dia. (In)

Cross Section

M = Miniature
I = Intermediate
S = Standard
H = Heavy
HH = Heavy Head

Screw Hole Size

(Clamp Ties Only)
—S6 = #6 (M3)
—S10 = #10 (M5)
—S25 = ¼ (M6)

Package Size

L = 50
C = 100
D = 500
M = 1000

Material/Color

See below

Material and Color Chart

Material	Color	PANDUIT Suffix
Nylon 6.6	Natural	✓
Weather Resistant Nylon 6.6	Black	0
Nylon 6.6	Red	2

Material	Color	PANDUIT Suffix
Nylon 6.6	Black	20
Heat Stabilized Nylon 6.6	Black	30

✓ Denotes PANDUIT Natural Nylon 6.6 (no suffix).

Part Number Availability List

Standard Packaging			Bulk Packaging		
Part Number	Natural Nylon 6.6	Material/Color Suffix	Part Number	Natural Nylon 6.6	Material/Color Suffix
SSC2S-S6-C	✓		SSC2S-S6-M	✓	0
SSC2S-S10-C	✓		SSC2S-S10-M	✓	0, 30
SSC4S-S10-C	✓		SSC4S-S10-M	✓	0
SSC4H-S25-L	✓		SSC4H-S25-D	✓	0
SSM2S-C	✓		SSM2S-D	✓	0
			SSM4S-D	✓	
SST1M-C	✓	0	SST1M-M	✓	0, 20, 30
SST1.5M-C	✓		SST1.5M-M	✓	0, 20, 30
SST1.5I-C	✓		SST1.5I-M	✓	0
SST2I-C	✓		SST2I-M	✓	0
SST3I-C	✓	0	SST3I-M	✓	0
SST4I-C	✓		SST4I-M	✓	0
			SST1.5S-M	✓	0
SST2S-C	✓	0	SST2S-M	✓	0, 20, 30
SST3S-C	✓	0	SST3S-M	✓	0, 20, 30
SST4S-C	✓	0	SST4S-M	✓	0, 2, 30
			SST2H-D	✓	0
			SST2HH-D		30
SST4H-L	✓	0	SST4H-D	✓	0, 30
			SST4HH-D		30
SST8H-L	✓	0	SST8H-D	✓	0, 30

Part Number System for Specialty Cable Ties

PLST	4	H	S25	—	TL	300
<u>Type</u>	<u>Size</u>	<u>Cross Section</u>	<u>Stud Size</u>	<u>Package Size</u>	<u>Material/Color</u>	
CM4S = Cable Marker Strap	Approx.	S = Standard	—S25 = M6	L = 50	See below	
PLB = Locking Bow Tie	Maximum	H = Heavy	—SC = 5mm	C = 100		
PL3B = Triple Loop Tie	Bundle	EH = Extra-Heavy	—S14 = 5mm	TL = 250		
DHC = Double Hose Clamp	Dia. (In)			D = 500		
PLST = Locking Stud Mounted Tie				M = 1000		
PRST = Releasable Stud Mount Ladder Style						
SSB = STA-STRAP® BOW-TY™ Tie						
SSPM = STA-STRAP® Panel Mount						

Material and Color Chart

Material	Color	PANDUIT Suffix	Material	Color	PANDUIT Suffix
Nylon 6.6	Natural	✓	Heat Stabilized Nylon 6.6	Black	30
Weather Resistant Nylon 6.6	Black	0	Heat Stabilized Weather Resistant Nylon 6.6	Black	300
Nylon 6.6	Red	2			
Nylon 6.6	Gray	8			

✓ Denotes PANDUIT Natural Nylon 6.6 (no suffix).

Part Number Availability List

Standard Packaging			Bulk Packaging		
Part Number	Natural Nylon 6.6	Material/Color Suffix	Part Number	Natural Nylon 6.6	Material/Color Suffix
CM4S-L		2, 8			
			DHC1.12X1.75-D		0
PLB2S-C	✓	0	PLB2S-M	✓	0, 30
PLB3S-C	✓	0	PLB3S-M	✓	0, 30
PLB4S-C	✓		PLB4S-M	✓	0, 30, 39
			PLB4H-TL	✓	0, 30, 39
			PLB5EH-C		0
			PL3B5EH-C		0
			PLST4HS25-TL		300
			PLST30SC-D		30
			PLST50SC-D		30
			PRST30S-S14-M		30
			PRST40SC-D		30
SSB2S-C	✓		SSB2S-M	✓	0, 30
SSPM2.5H-L		300	SSPM2.5H-TL		300
SSPM2.5HP-L		300	SSPM2.5HP-TL		300
SSPM4H-L		300	SSPM4H-TL		300
SSPM4HP-L		300	SSPM4HP-TL		300
			SSPM4HLP-TL		300

Part Number System for *TAK-TY*® Hook & Loop Cable Ties

HLT	2	I	—	X	0
<u>Type</u>	<u>Size</u>	<u>Cross Section</u>		<u>Package Size</u>	<u>Color</u>
HL = Hook and Loop	Approx.	I = Intermediate		C = 100	See below
HLB = Hook and Loop Brick Pack	Maximum	S = Standard		X = 10	
HLC = HL Cinch Tie	Bundle			15R = 15' Roll	
HLM = HL Miniature	Dia. (In)			20R = 20' Roll	
HLT = HL Loop Tie				35R3 = 35' Rolls (3)	
HLTP = HL Loop Tie Plenum-Rated				35RX = 35' Rolls (10)	
HLS = HL Strip Tie				75R = 75' Roll	
HLSP = HL Strip Tie Plenum-Rated					
TTS = <i>TAK-TAPE</i> ™ Roll					

Part Number System for *ULTRA-CINCH*™ Hook & Loop Cable Ties

UGCT	E	3	S	—	X	0
<u>Type</u>	<u>Mount</u>	<u>Size</u>	<u>Cross Section</u>		<u>Package Size</u>	<u>Color</u>
UCT = Cinch Tie	E = End Mount	Approx.	I = Intermediate		X = 10	See below
UGCT = Grommet Cinch Tie	C = Center Mount	Maximum	S = Standard			
		Bundle				
		Dia. (In)				

Color Chart

Color	PANDUIT Suffix	Color	PANDUIT Suffix
Black	0	Blue	6
Red	2	Gray	8
Orange	3	White	10
Yellow	4	Maroon	12
Green	5		

Part Number Availability List

Standard Packaging	
Part Number	Color Suffix
HLB2S-C	0, 2, 3, 4, 5, 6, 8, 10
HLC3S-X	0
HLC5S-X	0
HLM-15R	0, 2, 3, 4, 5, 6, 8, 10
HLS-15R	0, 2, 3, 4, 5, 6, 8, 10
HLS-75R	0, 2, 3, 4, 5, 6, 8, 10
HLS1.5S-X	0, 2, 3, 4, 5, 6, 8, 10
HLS3S-X	0, 2, 3, 4, 5, 6, 8, 10
HLS5S-X	0, 2, 3, 4, 5, 6, 8, 10
HLSP1.5S-X	0, 12
HLSP3S-X	0, 12
HLSP5S-X	0, 12
HLT2I-X	0, 2, 3, 4, 5, 6, 8, 10
HLT3I-X	0, 2, 3, 4, 5, 6, 8, 10
HLTP2I-X	0, 12
HLTP3I-X	0, 12
HLWM1.5S-X	0
HLWM3S-X	0
TTS-20R	0
TTS-35RX	0
TTS-35R3	0
UCT3S-X	0, 2, 3, 4, 5, 6, 8, 10
UCT5S-X	0, 2, 3, 4, 5, 6, 8, 10
UGCTC3S-X	0, 2, 3, 4, 5, 6, 8, 10
UGCTC5S-X	0, 2, 3, 4, 5, 6, 8, 10
UGCTE3S-X	0, 2, 3, 4, 5, 6, 8, 10
UGCTE5S-X	0, 2, 3, 4, 5, 6, 8, 10