

specifications

Type LD2P10 non-metallic two channel, one-piece tamper resistant latch design, adhesive backed, hinged cover surface raceway shall be used to route, protect and conceal low voltage data, voice, fiber optic and power cabling. The raceway shall be listed as suitable for use in applications having up to 600V between conductors by Underwriters Laboratories, Inc. per Standard 5A and by Canadian Standards Associations per C22.2 No. 62.1-03 when installed per instructions. The raceway include a full complement of bend radius control (BRC) fittings consisting of, but not limited to: elbows, (internal and external), couplings for joining raceway sections, blank end fittings for closing open ends of the raceway, entrance end fittings, reducer fittings, tee fittings, and an optional raceway installation tool. The BRC fittings shall incorporate a minimum of 1" bend radius as recommended for Category 6 UTP and fiber optic cabling in TIA/EIA 569-B. This non-metallic surface raceway shall be manufactured in two standard lengths from impact resistant material with a flammability rating of UL94V-0. The non-metallic raceway finish shall be pure color, resist scratches and dents and not peel or corrode. The raceway shall be available in four standard colors and shall be optimized for use with **PANDUIT® PAN-NET®** Network Cabling Systems.



technical information

Material:	Rigid PVC
Flammability:	UL94V-0
Voltage rating:	UL-5A 600VAC; CSA C22.2 No. 62.1-03 600V
Approvals:	UL Listed 95425 (raceway); UL Listed E116129 (fittings)
NEC:	Article 388
Color:	Off White (IW), Electrical Ivory (EI), International Gray (IG), White (WH)
CSI spec form:	LP-CSISPEC-LD2P10-1

key features and benefits

Multi-channel system	Allows end user to purchase one raceway to route both data and power cabling
Available 1" bend radius control fittings	Meets TIA/EIA standard and many warranty requirements
One-piece hinged design	Cables can be laid into the raceway, which prevents damage to cables during installation
Adhesive backing for temporary mounting	Installations are easier and faster, reducing the total installed cost
Highly tamper resistant	Provides maximum security for communication cabling and maximum safety for power cabling
Non-metallic construction	Lightweight, which reduces installer fatigue and reduces labor required to install the raceway; solid color throughout will not chip, peel, rust or corrode; easy to cut with standard saws and saw blades, which reduces the need for special cutting devices
Available in four colors	Matches a wide variety of colors for various applications

applications

PAN-WAY® LD2P10 Profile Raceway is a one-piece multi-channel channel raceway which provides solutions for routing both

power and data cabling along perimeter walls. LD2P10 profile raceway is available with multi-channel fittings.

www.panduit.com


PAN-WAY® LD2P10 Raceway	
Raceway:	LD2P10IW**-A
LD2P10 Raceway Fittings	
Coupler fitting:	CFX10IW-X
Inside corner fitting:	ICFX10IW-X
Outside corner fitting:	OCFX10IW-X
Right angle fitting:	RAFX10IW-X
Tee fitting:	TFXD10IW-X
End cap fitting:	ECFX10IW-X
Entrance end fitting:	EEFXIW
Raceway installation tool:	LDW10-V

** Insert raceway length of 6', 8', or 10'
All parts listed in Off White (IW) color. To order other colors substitute Electrical Ivory (EI), International Gray (IG), and White (WH).


PAN-WAY® LD2P10 Surface Raceway System

Wire Fill

Open Channel 40% Cable Fill Capacity	
Cable Type	# of Cables
12 AWG	11
Cat 6 cables	3 left channel 4 right channel
Cat 5e cables	4 left channel 5 right channel
2 strand Fiber Optic cable	7 left channel 8 right channel




LD2P Raceway




LD2P10


Fittings




CFX




ICFX




OCFX




RAFX




TFXD



ECFX



EEFX



LDW-V

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
Phone: 44.208.601.7200

PANDUIT ASIA PACIFIC PTE. LTD.
Republic of Singapore
Phone: 65.6379.6700

PANDUIT JAPAN
Tokyo, Japan
Phone: 81.3.3767.7011

PANDUIT LATIN AMERICA
Jalisco, Mexico
Phone: 52.333.666.2501

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
Phone: 61.3.9794.9020

For a copy of PANDUIT product warranties, log on to www.panduit.com/warranty



For more information or to request a catalog

800-777-3300

cs@panduit.com

www.panduit.com

Copyright © PANDUIT Corp. All rights reserved.

Printed in U.S.A.

WW-SRSP07

05/2004

replaces SA117N277-LP