




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		F	REVISED PER ECR-12-013219	08JAN13	KH	KR



- 1 MATING TAB THK IS 0.81 ± 0.025 [.032 $\pm$.001]
- 2 WIRE SIZE IS [#22-#18] AWG.
- 3 INSULATION RANGE IS 2.03-3.05 [.080-.120] DIA.
- 4 PREPRODUCTION - FASR REQ



0.002032 [.000080] MIN TIN			521437-2		
-			4 521437-1		
TERMINAL FINISH			PART NO.		
DWN	JR RUTH	22OCT01	TE Connectivity		
CHK	J HUMMEL	22OCT01			
APVD	J HUMMEL	22OCT01	NAME ASSEMBLY, RECEPTACLE, ULTRA-POD, 2.79 [.110] SERIES		
PRODUCT SPEC					
108-1285		SIZECAGE CODEDRAWING NORESTRICTED TO			
APPLICATION SPEC					
114-2124		A200779C=521437-			
WEIGHT					
-					
CUSTOMER DRAWING			SCALE 6:1SHEET 1 of 1REV F		

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm [INCHES]	
	0 PLC $\pm$ -
	1 PLC $\pm$ -
	2 PLC $\pm$ 0.25 [.010]
	3 PLC $\pm$ -
	4 PLC $\pm$ -
	ANGLES $\pm$ -
MATERIAL	FINISH
TERM - BRASS	SEE TABLE
HSG - 6/6 NYLON, V0	HSG - WHITE