


13	12	11	10	9	8	7	6	5	4	3	2	1
POLES	MATERIAL NO.	ENG. NO.	AMPS	LENGTH								
3	1300640065	CC3030A48M020	32	2M +89-0MM (6'7"+3.50-0)								
4	1300640187	CC4030A48M020	32	2M +89-0MM (6'7"+3.50-0)								



SPECS:
OVERMOLD: GRAY PVC
INSERT: BLACK PVC
COUPLING NUT: ANODIZED ALUMINUM
CABLE: #10AWG GRAY PVC
DUAL RATED UL TC/OPEN WIRING & STOOV
ELECTRICAL: 600V AC/DC

UPDATED PROFILE EC NO: IPG2014-1160 B DRWNGGUSTAFSON 2013/12/26 CHKD:VOU 2014/01/15 APPR:BMWOODMAN 2014/05/12	DESCRIPTION	REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 1:2	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION		
					mm	INCH	DRAWN BY B.RUPERT	DATE 01/12/10	TITLE QUICK CHANGE FEMALE/MALE STRAIGHT 3 & 4 POLE AS PORTABLES MOLEX INCORPORATED			
				4 PLACES ± ---	± ---	CHECKED BY B.WOODMAN	DATE 01/12/10					
				3 PLACES ± ---	±.005	APPROVED BY JFMURPHY	DATE 2010/01/15					
				2 PLACES ± ---	±.010							
				1 PLACE ± ---	±.020							
				ANGULAR ±1/2°								
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		DOCUMENT NO. SD-130064-065			SHEET NO. 1 OF 1	
						SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					