

Features :


- Universal AC input / Full range
- AC input active surge current limiting
- Built-in active PFC function, PF>0.95
- Protections: Short circuit / Overload / Over voltage/Over temperature
- Forced air cooling by built-in DC Fan
- Built-in remote ON-OFF function for CH3,CH4 and the whole unit
- Isolate output
- Built-in remote sense function(CH3,CH4)
- Built-in external voltage control function(CH3,CH4)
- Built-in output current monitor signal(CH3,CH4)

SPECIFICATION

MODEL		QP-1000			
OUTPUT	OUTPUT NUMBER	CH1	CH2	CH3	CH4
	DC VOLTAGE	12V	5V	24V	24V
	RATED CURRENT	8.4A	6A	12.5A	25A
	CURRENT RANGE	0 ~ 8.4A	0 ~ 6A	0 ~ 12.5A	0 ~ 25A
	RATED POWER (convection)	130.8W(max.)		300W	
		1000W(max.)			
	RIPPLE & NOISE (max.) Note.2	120mVp-p	80mVp-p	100mVp-p	200mVp-p
	VOLTAGE ADJ. RANGE	10.8 ~ 13.2V	4.5 ~ 5.5V	21.5 ~ 26.5V	21.5 ~ 26.5V
	REMOTE PROGRAMMING (PV)	CH3,CH4 10% ~ 120% adjustable by 0.5 ~ 6VDC external control			
	VOLTAGE TOLERANCE Note.3	±2.0%	±2.0%	±1.0%	±1.0%
	LINE REGULATION	±0.5%	±0.5%	±0.5%	±0.5%
	LOAD REGULATION	±1.0%	±1.0%	±1.0%	±1.0%
SETUP, RISE TIME	1500ms, 50ms/230VAC 1500ms, 50ms/115VAC at full load				
HOLD UP TIME (Typ.)	16ms/230VAC 16ms/115VAC at full load				
INPUT	VOLTAGE RANGE Note.5	90 ~ 264VAC 127 ~ 370VDC			
	FREQUENCY RANGE	47 ~ 63Hz			
	POWER FACTOR	PF ≥ 0.95/230VAC PF ≥ 0.97/115VAC at full load			
	EFFICIENCY(Typ.)	86%			
	AC CURRENT (Typ.)	12A/115VAC 6A/230VAC			
	INRUSH CURRENT (Typ.)	COLD START 25A/115VAC 40A/230VAC			
LEAKAGE CURRENT	<2mA / 240VAC				
PROTECTION	OVERLOAD	105 ~ 135% rated output power			
		CH1, CH2 : Protection type : Shut down o/p voltage, re-power on to recover			
		CH3, CH4 : Protection type : Constant current limiting, unit will shut down after 3 sec., re-power on to recover			
	OVER VOLTAGE	13.8 ~ 16.2V	5.75 ~ 6.75V	30 ~ 34.8V	30~ 34.8V
	OVER TEMPERATURE	Protection type : Shut down o/p voltage, re-power on to recover			
FUNCTION	REMOTE CONTROL	Turn ON/OFF CH3,CH4 and the whole power supply RC+/RC-: Short , Power ON ; RC+/RC-: Open , Power OFF			
	CURRENT MONITOR	Signal provides an output of 0 ~ 5V which applies over 10 ~ 100% of rated load.			
	OUTPUT VOLTAGE EXTERNAL CONTROL	Please see the Function Manual			
	ENVIRONMENT	WORKING TEMP.	-20 ~ +70℃ (Refer to output load derating curve)		
WORKING HUMIDITY		20 ~ 90% RH non-condensing			
STORAGE TEMP., HUMIDITY		-40 ~ +85℃, 10 ~ 95% RH			
TEMP. COEFFICIENT		±0.03%/℃ (0 ~ 45℃)			
VIBRATION		10 ~ 500Hz, 5G 10min./1cycle, period for 60min. each along X, Y, Z axes			
SAFETY & EMC (Note 4)	SAFETY STANDARDS	Design refer to UL60950-1, TUV EN60950-1			
	WITHSTAND VOLTAGE	I/P-O/P:3KVAC I/P-FG:1.5KVAC O/P-FG:0.5KVAC			
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms/500VDC / 25℃ / 70% RH			
	EMI CONDUCTION & RADIATION	Compliance to EN55022 (CISPR22)			
	HARMONIC CURRENT	Compliance to EN61000-3-2,-3			
	EMS IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11; ENV50204, EN55024, EN61000-6-2, EN61204-3			
OTHERS	MTBF	K hrs min. MIL-HDBK-217F (25℃)			
	DIMENSION	278*177.8*63.5mm (L*W*H)			
	PACKING	Kg			

Mechanical Specification

Case No. Unit:mm



AC Input Terminal Pin No. Assignment (TB1)

Pin No.	Assignment
1	FG $\perp$
2	AC/N
3	AC/L

DC Output Terminal Pin No. Assignment (TB2)

Pin No.	Assignment	Pin No.	Assignment
1,2	+V4	7	-V2
3,4	-V4	8	+V2
5	+V1	9	+V3
6	-V1	10	-V3

Control Pin No. Assignment(CN1) for CH3: HRS DF11-8DP-2DS or equivalent

Pin No.	Assignment	Pin No.	Assignment	Mating Housing	Terminal
1	+S	5	PV	HRS DF11-8DS or equivalent	HRS DF11-**SC or equivalent
2	-S	6	Im		
3	+RC	7,8	G		
4	PS				

+S : +Remote Sensing
 -S : -Remote Sensing
 +RC : +Remote OF/OFF
 PS : Reference Voltage Terminal

PV : Voltage Control
 Im : Output Current Monitor
 G : GND

Control Pin No. Assignment(CN2): HRS DF11-4DP-2DS or equivalent

Pin No.	Assignment	Mating Housing	Terminal
1	VCC	HRS DF11-4DS or equivalent	HRS DF11-**SC or equivalent
2	+RC		
3,4	COM		

+RC : +Remote OF/OFF
 VCC : 12V/0.1A auxiliary output for remote control


Control Pin No. Assignment(CN3) for CH4: HRS DF11-8DP-2DS or equivalent

Pin No.	Assignment	Pin No.	Assignment	Mating Housing	Terminal
1	+S	5	PV	HRS DF11-8DS or equivalent	HRS DF11-**SC or equivalent
2	-S	6	Im		
3	+RC	7,8	G		
4	PS				


+S : +Remote Sensing
 -S : -Remote Sensing
 +RC : +Remote OF/OFF
 PS : Reference Voltage Terminal

PV : Voltage Control
 Im : Output Current Monitor
 G : GND


Block Diagram



Derating Curve



Output Derating VS Input Voltage




Function Manual

1.Remote ON/OFF


The PSU by using the "Remote ON/OFF" function

A. For CH3 (CN1) or CH4 (CN3)



Between +RC(pin3) and G(pin7,8)	Output Status
SW ON (Short)	ON
SW OFF (Open)	OFF

B. For CH1 ~ CH4 (CN2)



Between +RC(pin1) and COM(pin2,4)	Output Status
SW ON (Short)	ON
SW OFF (Open)	OFF

2.External Voltage Control by CH3,CH4

