

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.


© COPYRIGHT

By

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	P2	REVISED PER ECO-11-004820	11MAR11	RK	HMR
	P3	REVISED PER ECR-16-016660	02DEC2016	RS	DR

AMP WIRE RANGE	Listed	LR7189 Certified
12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED



- 1
- 2
- 3
- 4
- 5
- STAMP AMP 12-10* APPROX AS SHOWN.
- WIRE INSULATION DIA: $\phi 3.81-6.35$ [$\phi .150-.250$].
- TONGUE MATERIAL THK: $0.99^{+0.05}$ [$.039^{+.002}$].
- MATERIAL: BODY - CU PER ASTM B152
SLEEVE - PVC, COLOR - YELLOW.
- APPLIES FROM EDGE OF METAL WIRE BARREL TO
CENTER OF STUD HOLE.

50	LOOSE PC,BOX	8-34852-2
2000	ON TAPE, REEL	2-34852-1
500	LOOSE PIECE	34852
QTY.	PACKAGE TYPE	PART NUMBER

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

FOR APPLICATION
TOOLING INFORMATION

FOR ORDER ENTRY

PRODUCT INFORMATION CENTER
1-800-522-6752

TOOLING ASSISTANCE CENTER
1-800-722-1111

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
105°C [221°F]

VOLTAGE RATING:
600 V MAX. FOR BUILDING WIRE
1000 V FOR FIXTURES & SIGNS

CIRCULAR MIL AREA:
2.62-6.64mm² [5,180-13,100]
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
4

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.20[.008]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH
TIN PER ASTM B545

DWN DK SCHRUM 08/06/92
CHK RE HERSEY 11/10/92
APVD M BARNABA 11/10/92
PRODUCT SPEC
APPLICATION SPEC
114-2161
WEIGHT -

TE Connectivity

NAME
TERMINAL, RING TONGUE, PLASTI-GRIP
WIRE SIZE 12-10 AWG

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-34852

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
4:1

SHEET
1 OF 1

REV
P3