


Technical drawing of a circular component with two mounting tabs. The drawing shows a central circular hole with a diameter of 5.6 mm, labeled "Ø5.6 SOUND EMISSION HOLE". The outer diameter of the main body is 23 mm, labeled "Ø23". The two mounting tabs at the top and bottom have a diameter of 2.7 mm, labeled "Ø2.7 ± 0.1 (2)". The total height of the component is 28 mm, labeled "28 ± 0.2". The drawing is identified as "UL1095".

©2003, Projects Unlimited Inc.

Technical drawing of a black cylindrical component. The drawing includes a side view with dimensions: a total height of 33, a top flange width of 2.5, and a main body diameter of 17. A 3D perspective view shows the component with a red and black cable attached to its side.



1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
3. THIS PART IS RoHS 2002/95/EC COMPLIANT.

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS, TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.	SIZE	Designed by	Date	Checked by	Date	Approved by	Date	Drawn Date
	A3	J.A.F.	10/26/2005	E.P.	10/26/2005	B.R.	10/26/2005	5/2/2010
		 pui audio ™ inc. a projects unlimited company			AI-2337-TF-LW115-R			
Indicator					Edition	Sheet		
AI-2337-TF-LW115-R.idw							-	1 / 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AI-2337-TF-LW115-R](#)