

LOC	DIST	REVISIONS				
EH	00	P	LTR	DESCRIPTION	DATE	DWN
		R2		REVISED PER ECO-12-021923	18DEC2012	GG


- 1

DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- 2

MATERIAL: POLYESTER FILM 0.025 [.010] THICK.
2 LAYERS EACH SIDE.
COPPER WIRE- 0.23 [.009] THICK x 15.24 [.600] WIDE.
SHIELD- PVC, 0.025 [.010] THICK.
- 3

CABLE MARKED WITH "AMP INC PN 553079
TYPE FCC UL CSA 12 AWG, CU 300V, 20 AMP 60° C"
IN COLOR SPECIFIED FOR CONTINUOUS LENGTH OF ROLL AS SHOWN.
- 4

CAUTION: THE UNDERCARPET CABLE MAY NOT BE USED OUTDOORS OR IN WET LOCATIONS; WHERE THE CABLE WOULD BE SUBJECT TO CORROSIVE VAPORS; IN ANY HAZARDOUS (CLASSIFIED) LOCATION; OR IN RESIDENTIAL, SCHOOL, AND HOSPITAL BUILDINGS.



30.7	[100]	3-553079-4
15.5	[50]	3-553079-3
76.5	[250]	3-553079-1
9.14	[30]	1-553079-7
LENGTH PER REEL - M [FEET]		PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. HALL 31AUG2005	TE Connectivity	
		CHK R. SPEER 31AUG2005		
DIMENSIONS: mm(INCHES)		APVD R. SPEER 31AUG2005	NAME	
		PRODUCT SPEC	CABLE, FLAT, 3 CONDUCTOR, 12 AWG, POWER, UNDERCARPET	
		108-6038	-	
		114-6008	SIZE	
		WEIGHT	A1 00779 C=553079	
		FINISH	CUSTOMER DRAWING	
			SCALE	
			SHEET 1 OF 1	
			REV R2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-553079-3](#) [3-553079-4](#)