



Product: [9542](#) 

RS232, #24-20c, SR-PVC, O/A Foil, PVC Jkt, CMG

Product Description

Computer EIA RS-232 Cable, 24 AWG stranded (7x32) tinned copper conductors, semi-rigid PVC insulation, overall Beldfoil® shield (100% coverage), 24 AWG stranded tinned copper drain wire, PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
24	7x32	TC - Tinned Copper	20

Conductor Count:20

Insulation

Material	Nominal Wall Thickness
S-R PVC - Semi-Rigid Polyvinyl Chloride	0.011 in

Color Chart

Number	Color
1	Black
2	White
3	Red
4	Green
5	Orange
6	Blue
7	White/Black
8	Red/Black
9	Green/Black
10	Orange/Black
11	Blue/Black
12	Black/White
13	Red/White
14	Green/White
15	Blue/White
16	Black/Red
17	White/Red
18	Orange/Red
19	Blue/Red
20	Red/Green

Color Chart 2

Number
13

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
------	----------	---------------------	--------------	--------------------	---------------	------------------------------

Tape	Alum / Poly	Beldfoil®	100 %	TC - Tinned Copper	24	7x32
------	-------------	-----------	-------	--------------------	----	------

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.314 in	0.032 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
25 Ohm/1000ft	18 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
30 pF/ft	55 pF/ft

Current

Max. Recommended Current [A]
1.75 Amps per conductor @ 25°C A

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temp Rating:	80°C (UL AWM Style 2464)
Operating Temp Range:	-30°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	64 lbs/1000ft
Max Recommended Pulling Tension:	110 lbs
Min Bend Radius During Installation:	13 in
Min Bend Radius/Minor Axis:	3.25 in

Standards

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
UL AWM Style:	2464 (300 V 80°C)
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading
CSA Flammability:	FT4
ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
9542 060100	Chrome	Reel	100 ft	612825255574
9542 0601000	Chrome	Reel	1,000 ft	612825255581
9542 060500	Chrome	Reel	500 ft	612825255598
9542 0605000	Chrome	Reel	5,000 ft	612825255604
9542 060U500	Chrome	UnReel	500 ft	612825255567

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.279 Revision Date: 04-08-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.