







	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1																	
	PART NO.	CKT SIZE	DIM "A"	DIM "B"	DIM "C"	DIM "D" REF	DIM "E"																														
M	75730-0104	4	13.78/1.543	12.00/1.472	3.06/120	7.06/278	1.60/062 TO 2.44/096	NOTES: 1. MATERIALS: - HOUSING: LCP, 30% GLASS FILLED, 94V-0, COLOR: BLACK - TERMINAL: COPPER ALLOY PLATING: - 2.50 μm/100 μm MIN TIN OVER - 125 μm/50 μm MIN NICKEL OVERALL 2. PRODUCT SPEC: PS-75730 3. MODULE IS DESIGNED FOR SOLDERING TO THE PCB 4. MODULE IS RoHS COMPLIANT 5. BOW, FLATNESS AND CAMBER SPECIFICATIONS ARE 0.25/010 PER INCH 6. PARTS TO BE PACKAGED PER MOLEX PACKAGING SPEC PK-75730-118													M																
	75730-0105	5	17.78/1.700	16.00/1.630																																	
	75730-0106	6	21.78/1.857	20.00/1.787																																	
	75730-0107	7	25.78/1.015	24.00/1.945																																	
L	75730-0108	8	29.78/1.172	28.00/1.102																	L																
	75730-0109	9	33.78/1.330	32.00/1.260																																	
	75730-0110	10	37.78/1.487	36.00/1.417																																	
	75730-0111	11	41.78/1.645	40.00/1.575																																	
	75730-0112	12	45.78/1.802	44.00/1.732																																	
K	75730-0113	13	49.78/1.960	48.00/1.890																	K																
	75730-0114	14	53.78/2.117	52.00/2.047																																	
	75730-0115	15	57.78/2.275	56.00/2.205																																	
	75730-0116	16	61.78/2.433	60.00/2.362																																	
	75730-0117	17	65.78/2.590	64.00/2.520																																	
J	75730-0118	18	69.78/2.747	68.00/2.677																	J																
	75730-0119	19	73.78/2.905	72.00/2.835																																	
	75730-0120	20	77.78/3.062	76.00/2.992																																	
	75730-0121	21	81.78/3.220	80.00/3.150																																	
	75730-0122	22	85.78/3.377	84.00/3.307																																	
I	75730-0123	23	89.78/3.535	88.00/3.465																	I																
	75730-0124	24	93.78/3.692	92.00/3.622																																	
	75730-0150	MIXED CL	83.78/3.298	82.00/3.228																																	
					(A9)																																
H	75730-0204	4	13.78/1.543	12.00/1.472	3.81/150	7.82/308	3.18/125														H																
	75730-0205	5	17.78/1.700	16.00/1.630																																	
	75730-0206	6	21.78/1.857	20.00/1.787																																	
	75730-0207	7	25.78/1.015	24.00/1.945																																	
G	75730-0208	8	29.78/1.172	28.00/1.102																	G																
	75730-0209	9	33.78/1.330	32.00/1.260																																	
	75730-0210	10	37.78/1.487	36.00/1.417																																	
	75730-0211	11	41.78/1.645	40.00/1.575																																	
	75730-0212	12	45.78/1.802	44.00/1.732																																	
F	75730-0213	13	49.78/1.960	48.00/1.890																	F																
	75730-0214	14	53.78/2.117	52.00/2.047																																	
	75730-0215	15	57.78/2.275	56.00/2.205																																	
	75730-0216	16	61.78/2.433	60.00/2.362																																	
	75730-0217	17	65.78/2.590	64.00/2.520																																	
E	75730-0218	18	69.78/2.747	68.00/2.677																	E																
	75730-0219	19	73.78/2.905	72.00/2.835																																	
	75730-0220	20	77.78/3.062	76.00/2.992																																	
	75730-0221	21	81.78/3.220	80.00/3.150																																	
	75730-0222	22	85.78/3.377	84.00/3.307																																	
D	75730-0223	23	89.78/3.535	88.00/3.465																	D																
	75730-0224	24	93.78/3.692	92.00/3.622																																	
	75730-0250	MIXED CL	83.78/3.298	82.00/3.228																																	
	75730-0251	MIXED CL	83.78/3.298	82.00/3.228																																	
					(A9)																																
C																					C																
B																					B																
A																					A																
REMOVE -0147 EC NO: UCP2012-2242 DRAWN: BANDURA 2012/01/17 CHKD: APPR: APATEL 2013/12/19 REV		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION		DRAWN BY		DATE		TITLE		SHEET NO.																	
A9		▽=0		4 PLACES ± --- ± ---		MM/IN		1:1		METRIC		⊙		ADRNATNOL		2005/05/03		ASSEMBLY VRM HEADER FOR BOARD TO BOARD		1 OF 4																	
		▽=0		3 PLACES ± --- ± .005										CHECKED BY		DATE																					
		▽=0		2 PLACES ± 0.13 ± .010										APATEL		2005/05/03																					
				1 PLACE ± 0.25 ± ---										APPROVED BY		DATE																					
				ANGULAR ±1/2°										APATEL		2005/05/03																					
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										MATERIAL NO.				DOCUMENT NO.																			
														SEE CHART				SD-75730-118																			
														SIZE				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			

20 19 18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1



VRM BOARD LAYOUT



MOTHER BOARD LAYOUT



SEE SHEET 1 EC NO: UCP2012-2242 DRAWN BY: DRWMBANDURA CHKD: CHKO: APPR: APATEL REV: A9	2012/01/17 2013/12/19	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION		
						MM/IN		4:1	METRIC			
						DRAWN BY	DATE	TITLE			ASSEMBLY VRM HEADER FOR BOARD TO BOARD	
						CHECKED BY	DATE					
						APPROVED BY	DATE					
						APATEL	2005/05/03	MOLEX MOLEX INCORPORATED				
		ANGULAR AR ±1/2°		MATERIAL NO.		DOCUMENT NO.		SHEET NO.				
		DRAFT WHERE APPLICABLE		SEE CHART		SD-75730-118		2 OF 4				
		MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

19 18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1

20 19 18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1

M

L

K

J

I

H

G

F



E

D


C

B


A



VRM BOARD LAYOUT




MOTHER BOARD LAYOUT



SEE SHEET 1 EC NO: UCP2012-2242 DRAWN BY: DRWMBANDURA CHKD: CHYD APPR: APATEL REV: A9	DESCRIPTION 2012/01/17 2013/12/19	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± .005 2 PLACES ± 0.13 ± .010 1 PLACE ± 0.25 ± --- ANGULAR ±1/2°	DIMENSION STYLE MM/IN SCALE 4:1 DESIGN UNITS METRIC THIRD ANGLE PROJECTION	DRAWN BY ADRNOL DATE 2005/05/03 CHECKED BY DATE 2005/05/03 APPROVED BY DATE 2005/05/03 MATERIAL NO. SD-75730-118 DOCUMENT NO. SD-75730-118 SHEET NO. 3 OF 4	ASSEMBLY VRM HEADER FOR BOARD TO BOARD MOLEX INCORPORATED

19 18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1



VRM BOARD LAYOUT

MOTHER BOARD LAYOUT

75730-0251 SHOWN
18 CIRCUIT
MIXED LAYOUT

SEE SHEET 1 EC NO: UCP2012-2242 DRAWN BY: ADRA DATE: 2012/01/17 CHKD: APATEL DATE: 2013/12/19 APPR: APATEL DATE: 2013/12/19 REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	ASSEMBLY VRM HEADER FOR BOARD TO BOARD MOLEX INCORPORATED		
		4 PLACES	±	mm	±	INCH	DRAWN BY ADRA			TOL 2005/05/03	
		3 PLACES	±		±	.005	CHECKED BY APATEL			DATE 2005/05/03	
		2 PLACES	±	0.13	±	.010	APPROVED BY APATEL			DATE 2005/05/03	
		1 PLACE	±	0.25	±		MATERIAL NO. SD-75730-118			DOCUMENT NO. 4 OF 4	
		ANGULAR ± 1/2°				SEE CHART				SD-75730-118	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SIZE D				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	