

$\phi 172$ mm

San Ace 172



General Specifications

- Material Frame: Aluminum, Impeller: Plastics (Flammability: UL94V-1)
- Expected Life Refer to specifications (L10:Survival rate:90% at 60°C ,
rated voltage, and continuously run in a free air state)
- Lead Wire ⊕red ⊖black or blue (Sensor) yellow
- Storage Temperature -30°C to +70°C (Non-condensing)


$\phi 172$ mm × 147mm × 25mm (Mass : 500g) **9E type** **Sidecut type**

Specifications The following nos. have pulse sensors.


Model No.	Rated Voltage [V]	Operating Voltage Range [V]	Rated Current [A]	Rated Input [W]	Rated Speed [min ⁻¹]	Max. Airflow [m ³ /min] [CFM]	Max. Static Pressure [Pa] [inchH ₂ O]	SPL [dB(A)]	Operating Temperature [°C]	Expected Life [h]
109E4712M401	12	10.2 to 13.8	1.3	15.6	2,800	5.2 183	92 0.369	51	-20 to +60	40,000/60°C
109E4712L401			1.0	12.0	2,500	4.6 162	73 0.293	48		
109E4724H401	24	20.4 to 27.6	1.0	24.0	3,400	6.4 226	135 0.542	57		
109E4724F401			0.79	19.0	3,100	5.8 204	112 0.450	54		
109E4724M401			0.58	13.9	2,800	5.2 183	92 0.369	51		
109E4724L401			0.44	10.6	2,500	4.6 162	73 0.293	48		
109E4748S401	48	40.8 to 55.2	0.62	29.8	3,650	6.8 240	156 0.627	58		
109E4748H401			0.52	25.0	3,400	6.4 226	135 0.542	57		
109E4748F401			0.40	19.2	3,100	5.8 204	112 0.450	54		
109E4748M401			0.32	15.4	2,800	5.2 183	92 0.369	51		
109E4748L401			0.25	12.0	2,500	4.6 162	73 0.293	48		

Other sensor specifications are available as options. Please refer to the index (pp. 495 to 496).

Dimensions (unit: mm)



Reference Dimensions of Mounting Holes and Vent Opening (unit: mm)



Options (unit: mm)

Finger Guards

Model : 109-319E Surface treatment : Nickel-chrome plating (silver)
: 109-319H : Cation electropainting (black)


Color

Model : 109-320 Surface treatment : Nickel-chrome plating (silver)



Color

Finger guards 109-319E, 109-319H, and 109-320 should be mounted with two holes as in the drawing and do not use any other holes.






Inlet side, Outlet side



Outlet side



Airflow - Static Pressure Characteristics

**109E4748S401**
109E4724H401
109E4748H401

109E4724F401
109E4748F401

109E4712M401
109E4724M401
109E4748M401

109E4712L401
109E4724L401
109E4748L401

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sanyo Denki:

[109E5712F501](#) [109E5712F502](#) [109E5712H501](#) [109E5712H502](#) [109E5712K501](#) [109E5712K502](#) [109E5712M501](#)
[109E5712M502](#) [109E5712M5D01](#) [109E5712Y501](#) [109E5712Y502](#) [109E5724C501](#) [109E5724C502](#)
[109E5724C5D01](#) [109E5724F501](#) [109E5724F502](#) [109E5724H501](#) [109E5724H502](#) [109E5724H5D01](#) [109E5724K501](#)
[109E5724K502](#) [109E5724K5D01](#) [109E5724M501](#) [109E5724M502](#) [109E5748C501](#) [109E5748C502](#)
[109E5748F501](#) [109E5748F502](#) [109E5748H501](#) [109E5748H502](#) [109E5748H5D01](#) [109E5748K501](#) [109E5748K502](#)
[109E5748M501](#) [109E5748M502](#)