



LAY-OUT
P.C.B.-HOLE
(FRONT SIDE)



PERFORMANCE CHARACTERISTICS

- CURRENT RATING : 1.5A AT 20°C (FULLY LOADED)
1 A AT 70°C (FULLY LOADED)
- RATED VOLTAGE : 500 V AC (CONT /CONT)
- OPERATING TEMPERATURE : -55°C TO 125°C
- CONTACT RESISTANCE 20 mΩ MAX
- INSERTION FORCE : 0.75N MAX/CONT
- EXTRACTION FORCE : 0.15N MIN/CONT
- INSULATION RESISTANCE : 10⁴ mΩ MIN

NOTES

1. " " LEAD FREE INDICATOR :LF=LEAD FREE
- PERFORMANCE LEVEL INDICATOR
(REF DWG NO.BSC .201844.003)
2. THIS PRODUCT IS CSA APPROVED.
THIS PRODUCT IS UL RECOGNIZED.
3. FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING :BS.A.201572.001
4. THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008

rev	ecn no	dr	date
A	CONVERSION REVISION 00	KN	14-09-01
B	104-0109	ALEX E	27-11-04
C	DG05-0278	Kason	02-08-05
D	DG10-0110	NZ	2010.9.3
-	-	-	-
-	-	-	-

Material			Spec ref			
Mat code			✓ tolerance IDEC±0.2 IDEC 2DEC±0.1 2DEC ANGLES±1° HOEKEN	projection	MM ←————→	
Heat treat						
Plating/Finish						
Dr	W.Panis	27-01-95	size A4		Scale 2.000	
Eng			Product family		MILLIPICS	
Chr			Model Name		ECN	
Appr			Model Revision		REL Level	
		title		dwg no		Rev.
		MILLIPACS 2/TYPE B/SHIELDED		BSC201907005		D
Pro/E file		catalog no		CUSTOMER DRAWING		sheet 1 of 1
		HM2S02PE5101----				