


BSS 131

SIPMOS® Small-Signal Transistor

- N channel
- Enhancement mode
- Logic Level
- $V_{GS(th)} = 0.8...2.0V$



Pin 1	Pin 2	Pin 3
G	S	D

Type	V_{DS}	I_D	$R_{DS(on)}$	Package	Marking
BSS 131	240 V	0.1 A	16 Ω	SOT-23	SRs

Type	Ordering Code	Tape and Reel Information
BSS 131	Q62702-S565	E6327
BSS 131	Q67000-S229	E6433

Maximum Ratings

Parameter	Symbol	Values	Unit
Drain source voltage	V_{DS}	240	V
Drain-gate voltage	V_{DGR}	240	
$R_{GS} = 20\text{ k}\Omega$			
Gate source voltage	V_{GS}	± 20	
ESD Sensitivity (HBM) as per MIL-STD 883		Class 1	
Continuous drain current	I_D	0.1	A
$T_A = 26\text{ }^\circ\text{C}$			
DC drain current, pulsed	I_{Dpuls}	0.4	
$T_A = 25\text{ }^\circ\text{C}$			
Power dissipation	P_{tot}	0.36	W
$T_A = 25\text{ }^\circ\text{C}$			

Maximum Ratings

Parameter	Symbol	Values	Unit
Chip or operating temperature	T_j	-55 ... + 150	°C
Storage temperature	T_{stg}	-55 ... + 150	
Thermal resistance, chip to ambient air	R_{thJA}	≤ 350	K/W
Thermal resistance, chip-substrate- reverse side ¹⁾	R_{thJSR}	≤ 285	
DIN humidity category, DIN 40 040		E	
IEC climatic category, DIN IEC 68-1		55 / 150 / 56	

1) For package mounted on aluminium 15 mm x 16.7 mm x 0.7 mm

Electrical Characteristics, at $T_j = 25^\circ\text{C}$, unless otherwise specified

Parameter	Symbol	Values			Unit
		min.	typ.	max.	

Static Characteristics

Drain- source breakdown voltage $V_{GS} = 0\text{ V}$, $I_D = 0.25\text{ mA}$, $T_j = 25^\circ\text{C}$	$V_{(BR)DSS}$	240	-	-	V
Gate threshold voltage $V_{GS} = V_{DS}$, $I_D = 1\text{ mA}$	$V_{GS(th)}$	0.8	1.4	2	
Zero gate voltage drain current $V_{DS} = 240\text{ V}$, $V_{GS} = 0\text{ V}$, $T_j = 25^\circ\text{C}$	I_{DSS}	-	0.1	1	μA
$V_{DS} = 240\text{ V}$, $V_{GS} = 0\text{ V}$, $T_j = 125^\circ\text{C}$		-	2	60	
$V_{DS} = 130\text{ V}$, $V_{GS} = 0\text{ V}$, $T_j = 25^\circ\text{C}$		-	-	30	nA
Gate-source leakage current $V_{GS} = 20\text{ V}$, $V_{DS} = 0\text{ V}$	I_{GSS}	-	1	10	nA
Drain-Source on-state resistance $V_{GS} = 10\text{ V}$, $I_D = 0.1\text{ A}$	$R_{DS(on)}$	-	12	16	Ω
$V_{GS} = 4.5\text{ V}$, $I_D = 0.1\text{ A}$		-	15	26	

Electrical Characteristics, at $T_j = 25^\circ\text{C}$, unless otherwise specified

Parameter	Symbol	Values			Unit
		min.	typ.	max.	

Dynamic Characteristics


Transconductance $V_{DS} \geq 2 * I_D * R_{DS(on)max}$, $I_D = 0.1\text{ A}$	g_{fs}	0.06	0.14	-	S
Input capacitance $V_{GS} = 0\text{ V}$, $V_{DS} = 25\text{ V}$, $f = 1\text{ MHz}$	C_{iss}	-	60	80	pF
Output capacitance $V_{GS} = 0\text{ V}$, $V_{DS} = 25\text{ V}$, $f = 1\text{ MHz}$	C_{oss}	-	8	12	
Reverse transfer capacitance $V_{GS} = 0\text{ V}$, $V_{DS} = 25\text{ V}$, $f = 1\text{ MHz}$	C_{rss}	-	3.5	5	
Turn-on delay time $V_{DD} = 30\text{ V}$, $V_{GS} = 10\text{ V}$, $I_D = 0.26\text{ A}$ $R_{GS} = 50\ \Omega$	$t_{d(on)}$	-	5	8	ns
Rise time $V_{DD} = 30\text{ V}$, $V_{GS} = 10\text{ V}$, $I_D = 0.26\text{ A}$ $R_{GS} = 50\ \Omega$	t_r	-	8	12	
Turn-off delay time $V_{DD} = 30\text{ V}$, $V_{GS} = 10\text{ V}$, $I_D = 0.26\text{ A}$ $R_{GS} = 50\ \Omega$	$t_{d(off)}$	-	12	16	
Fall time $V_{DD} = 30\text{ V}$, $V_{GS} = 10\text{ V}$, $I_D = 0.26\text{ A}$ $R_{GS} = 50\ \Omega$	t_f	-	15	20	

Electrical Characteristics, at $T_j = 25^\circ\text{C}$, unless otherwise specified

Parameter	Symbol	Values			Unit
		min.	typ.	max.	
Reverse Diode					
Inverse diode continuous forward current $T_A = 25\text{ }^{\circ}\text{C}$	I_S	-	-	0.1	A
Inverse diode direct current,pulsed $T_A = 25\text{ }^{\circ}\text{C}$	I_{SM}	-	-	0.4	
Inverse diode forward voltage $V_{GS} = 0\text{ V}$, $I_F = 0.2\text{ A}$, $T_j = 25\text{ }^{\circ}\text{C}$	V_{SD}	-	0.8	1.2	V

Power dissipation


$$P_{\text{tot}} = f(T_A)$$



Drain current


$$I_D = f(T_A)$$

parameter: $V_{GS} \geq 10 \text{ V}$




Safe operating area $I_D = f(V_{DS})$

parameter : $D = 0.01$, $T_c = 25^\circ\text{C}$



Drain-source breakdown voltage


$$V_{(BR)DSS} = f(T_j)$$



Typ. output characteristics

$$I_D = f(V_{DS})$$


parameter: $t_p = 80 \mu s$, $T_j = 25^\circ C$



Typ. drain-source on-resistance


$$R_{DS(on)} = f(I_D)$$

parameter: $t_p = 80 \mu s$, $T_j = 25^\circ C$




Typ. transfer characteristics $I_D = f(V_{GS})$

parameter: $t_p = 80 \mu s$



Typ. forward transconductance $g_{fs} = f(I_D)$


parameter: $t_p = 80 \mu s$,



Drain-source on-resistance

$$R_{DS(on)} = f(T_j)$$


parameter: $I_D = 0.1 \text{ A}$, $V_{GS} = 10 \text{ V}$



Gate threshold voltage

$$V_{GS(th)} = f(T_j)$$


parameter: $V_{GS} = V_{DS}$, $I_D = 1 \text{ mA}$



Typ. capacitances

$$C = f(V_{DS})$$

parameter: $V_{GS} = 0 \text{ V}$, $f = 1 \text{ MHz}$



Forward characteristics of reverse diode

$$I_F = f(V_{SD})$$

parameter: T_j , $t_p = 80 \mu\text{s}$

